

AMP LATCH D/P ASSY ✓ ACTIVE

[AMP-LATCH](#) | [AMP-LATCH DIL-PLUG](#)


TE Part # 1-216791-6

TE Internal #: 1-216791-6

[View on TE.com >](#)



[Connectors](#) > [PCB Connectors](#) > [Wire-to-Board Connectors](#) > [FFC, FPC & Ribbon Connectors](#) > [Ribbon Cable Connectors](#)



Connector System: **Wire-to-Board**

Number of Positions: **16**

Centerline (Pitch): **2.54 mm [.1 in]**

PCB Mount Retention: **With**

PCB Mount Retention Type: **Boardlock**

Features

Product Type Features

Product Type	Connector
Header Type	Shrouded
Connector System	Wire-to-Board
Row-to-Row Spacing	2.54 mm[.1 in]
Connector Style	Plug
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	16
PCB Mount Orientation	Vertical
Number of Rows	2

Contact Features

Contact Mating Area Plating Material	Tin
Contact Current Rating (Max)	1 A

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
Termination Method to Wire & Cable	Insulation Displacement Crimp (IDC)

Mechanical Attachment

PCB Mount Retention	With
PCB Mount Retention Type	Boardlock



Mating Connector Lock	With
Mating Connector Lock Type	Latch
Connector Mounting Type	Board Mount

Housing Features

Housing Color	Gray
Centerline (Pitch)	2.54 mm[.1 in]

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JAN 2018 (181)
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Also in the Series | AMP-LATCH DIL-PLUG



Ribbon Cable Connectors
(28)


Customers Also Bought




TE Part #1-216791-0
AMP LATCH D/P ASSY




TE Part #166995-2
20DP CRIMP PIN



TE Part #215927-1
HD MIXED 7C2 RC.ASS




TE Part #2-216791-6
26P LATCH DIL-STECK



TE Part #640311-5
MINI AMP-IN 22-18 AWG
POST TIN PLTD



TE Part #969047-3
MODU CRIMP CONTACT



TE Part #1-216791-4
AMP LATCH D/P ASSY



TE Part #5-1437356-1
171-14G100M=14P 28A



TE Part #926209-2
LOCKING CLIP HSG.



TE Part #969129-3
MODU CRIMP KONTAKT

Documents

Product Drawings

[AMP LATCH D/P ASSY](#)

English

CAD Files

[Customer View Model](#)

[ENG_CVM_CVM_1-216791-6_B.3d_stp.zip](#)

AMP LATCH D/P ASSY

TE Part # 1-216791-6
TE Internal #: 1-216791-6



English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-216791-6_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-216791-6_B.3d_igs.zip](#)

English