


40 V, 3 A power Schottky rectifier



Features

- Very small conduction losses
- Negligible switching losses
- Low forward voltage drop
- Low thermal resistance
- Extremely fast switching
- Surface mount package
- Avalanche rated
- **ECOPACK2** component

Applications

- Telecom power supply
- Set-top box power supply
- TV power supply
- Battery charger

Description

Single chip Schottky rectifier suited for switch mode power supplies and high frequency DC to DC converters.

Packaged in SMA Flat Notch, SMB, SMB Flat, SMC and DPAK, the **STPS340** is ideal for surface mounting and used in low voltage, high frequency inverters, free wheeling and polarity protection applications.

| Product status | |
|-----------------|--------|
| STPS340 | |
| Product summary | |
| Symbol | Value |
| $I_{F(AV)}$ | 3 A |
| V_{RRM} | 40 V |
| $T_{j(max.)}$ | 150 °C |
| $V_{F(typ.)}$ | 0.52 V |

1 Characteristics

Table 1. Absolute ratings (limiting values at 25 °C, unless otherwise specified)

| Symbol | Parameter | Value | Unit | | |
|--------------|---|--|---------------------------------|-----|---|
| V_{RRM} | Repetitive peak reverse voltage | 40 | V | | |
| $I_{F(RMS)}$ | Forward rms current | 6 | A | | |
| $I_{F(AV)}$ | Average forward current, $\delta = 0.5$, square wave | SMA Flat Notch | $T_L = 105\text{ °C}$ | 3 | A |
| | | SMB | $T_L = 95\text{ °C}$ | | |
| | | SMB Flat | $T_L = 115\text{ °C}$ | | |
| | | SMC | $T_L = 105\text{ °C}$ | | |
| | | DPAK | $T_C = 135\text{ °C}$ | | |
| I_{FSM} | Surge non repetitive forward current | SMA Flat Notch | $t_p = 10\text{ ms sinusoidal}$ | 105 | A |
| | | All others | | 75 | A |
| P_{ARM} | Repetitive peak avalanche power | $t_p = 10\text{ }\mu\text{s}, T_j = 125\text{ °C}$ | 90 | W | |
| T_{stg} | Storage temperature range | -65 to +150 | °C | | |
| T_j | Maximum operating junction temperature ⁽¹⁾ | +150 | °C | | |

1. $(dP_{tot}/dT_j) < (1/R_{th(j-a)})$ condition to avoid thermal runaway for a diode on its own heatsink.

Table 2. Thermal resistance parameter

| Symbol | Parameter | Max. value | Unit | |
|---------------|------------------|----------------|------|------|
| $R_{th(j-l)}$ | Junction to lead | SMA Flat Notch | 20 | °C/W |
| | | SMB | 25 | |
| | | SMB Flat | 15 | |
| | | SMC | 20 | |
| $R_{th(j-c)}$ | Junction to case | DPAK | 5.5 | |

For more information, please refer to the following application note :

- AN5088 : Rectifiers thermal management, handling and mounting recommendations

Table 3. Static electrical characteristics

| Symbol | Parameter | Test conditions | Min. | Typ. | Max. | Unit | |
|-------------|-------------------------|-----------------------|--------------------|------|------|------|---------------|
| $I_R^{(1)}$ | Reverse leakage current | $T_j = 25\text{ °C}$ | $V_R = V_{RRM}$ | - | | 20 | μA |
| | | $T_j = 125\text{ °C}$ | | - | 2 | 10 | mA |
| $V_F^{(1)}$ | Forward voltage drop | $T_j = 25\text{ °C}$ | $I_F = 3\text{ A}$ | - | | 0.63 | V |
| | | $T_j = 125\text{ °C}$ | | - | 0.52 | 0.57 | |
| | | $T_j = 25\text{ °C}$ | $I_F = 6\text{ A}$ | - | | 0.84 | |
| | | $T_j = 125\text{ °C}$ | | - | 0.63 | 0.72 | |

1. Pulse test: $t_p = 380\text{ }\mu\text{s}$, $\delta < 2\%$

To evaluate the conduction losses, use the following equation:

$$P = 0.42 \times I_{F(AV)} + 0.050 \times I_{F(RMS)}^2$$

For more information, please refer to the following application notes related to the power losses :

- AN604: Calculation of conduction losses in a power rectifier
- AN4021: Calculation of reverse losses on a power diode

1.1 Characteristics (curves)

Figure 1. Average forward power dissipation versus average forward current




Figure 2. Average forward current versus ambient temperature ($\delta = 0.5$) (SMB, SMC, DPAK)




Figure 3. Average forward current versus ambient temperature ($\delta = 0.5$, SMB Flat)




Figure 4. Normalized avalanche power derating versus pulse duration ($T_j = 125\text{ °C}$)




Figure 5. Relative variation of thermal impedance junction to ambient versus pulse duration (SMB)




Figure 6. Relative variation of thermal impedance junction to lead versus pulse duration (SMB flat)




Figure 7. Relative variation of thermal impedance junction to ambient versus pulse duration (SMC)




Figure 8. Relative variation of thermal impedance junction to case versus pulse duration (DPAK)




Figure 9. Reverse leakage current versus reverse voltage applied (typical values)




Figure 10. Junction capacitance versus reverse voltage applied (typical values)




Figure 11. Forward voltage drop versus forward current




Figure 12. Thermal resistance junction to ambient versus copper surface under each lead (SMA Flat Notch)




Figure 13. Thermal resistance junction to ambient versus copper surface under each lead (SMB)




Figure 14. Thermal resistance junction to ambient versus copper surface under each lead (SMB flat)




Figure 15. Thermal resistance junction to ambient versus copper surface under each lead (SMC)





Figure 16. Thermal resistance junction to ambient versus copper surface under tab (DPAK)



2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

2.1 SMA Flat Notch package information

- Epoxy meets UL94, V0
- Cooling method: by conduction (C)
- Band indicates cathode

Figure 17. SMA Flat Notch package outline





Table 4. SMA Flat Notch package mechanical data

| Ref. | Dimensions | | | | | |
|------|-------------|------|------|-----------------------------|-------|-------|
| | Millimeters | | | Inches (for reference only) | | |
| | Min. | Typ. | Max. | Min. | Typ. | Max. |
| A1 | 0.90 | | 1.10 | 0.035 | | 0.044 |
| A1 | | 0.05 | | | 0.002 | |
| b | 1.25 | | 1.65 | 0.049 | | 0.065 |
| C | 0.15 | | 0.40 | 0.005 | | 0.016 |
| D | 2.25 | | 2.90 | 0.088 | | 0.115 |
| E | 5.00 | | 5.35 | 0.196 | | 0.211 |
| E1 | 3.95 | | 4.60 | 0.155 | | 0.182 |
| G | | 2.00 | | | 0.079 | |
| G1 | | 0.85 | | | 0.033 | |
| L | 0.75 | | 1.20 | 0.029 | | |
| L1 | | 0.45 | | | 0.018 | |
| L2 | | 0.45 | | | 0.018 | |
| L3 | | 0.05 | | | 0.002 | |
| V | | | 8° | | | 8° |
| V1 | | | 8° | | | 8° |

Figure 18. SMA Flat Notch recommended footprint in mm (inches)



2.2 SMB package information

- Epoxy meets UL94, V0
- Lead-free package

Figure 19. SMB package outline





Table 5. SMB package mechanical data

| Ref. | Dimensions | | | |
|------|-------------|------|-----------------------------|-------|
| | Millimeters | | Inches (for reference only) | |
| | Min. | Max. | Min. | Max. |
| A1 | 1.90 | 2.45 | 0.074 | 0.097 |
| A2 | 0.05 | 0.20 | 0.001 | 0.008 |
| b | 1.95 | 2.20 | 0.076 | 0.087 |
| c | 0.15 | 0.40 | 0.005 | 0.016 |
| D | 3.30 | 3.95 | 0.129 | 0.156 |
| E | 5.10 | 5.60 | 0.200 | 0.221 |
| E1 | 4.05 | 4.60 | 0.159 | 0.182 |
| L | 0.75 | 1.50 | 0.029 | 0.060 |

Figure 20. SMB recommended footprint



2.3 SMB Flat package information

- Epoxy meets UL94, V0
- Lead-free package

Figure 21. SMB Flat package outline





Table 6. SMB Flat mechanical data

| Ref. | Dimensions | | | | | |
|------|-------------|------|------|--------|-------|-------|
| | Millimeters | | | Inches | | |
| | Min. | Typ. | Max. | Min. | Typ. | Max. |
| A | 0.90 | | 1.10 | 0.035 | | 0.044 |
| b | 1.95 | | 2.20 | 0.076 | | 0.087 |
| c | 0.15 | | 0.40 | 0.005 | | 0.016 |
| D | 3.30 | | 3.95 | 0.129 | | 0.156 |
| E | 5.10 | | 5.60 | 0.200 | | 0.221 |
| E1 | 4.05 | | 4.60 | 0.159 | | 0.182 |
| L | 0.75 | | 1.50 | 0.029 | | 0.060 |
| L1 | | 0.40 | | | 0.016 | |
| L2 | | 0.60 | | | 0.024 | |

Figure 22. Footprint recommendations, dimensions in mm (inches)



2.4 SMC package information

- Epoxy meets UL94, V0

Figure 23. SMC package outline





Table 7. SMC package mechanical data

| Ref. | Dimensions | | | |
|------|-------------|------|-----------------------------|--------|
| | Millimeters | | Inches (for reference only) | |
| | Min. | Max. | Min. | Max. |
| A1 | 1.90 | 2.45 | 0.0748 | 0.0965 |
| A2 | 0.05 | 0.20 | 0.0020 | 0.0079 |
| b | 2.90 | 3.20 | 0.1142 | 0.1260 |
| c | 0.15 | 0.40 | 0.0059 | 0.0157 |
| D | 5.55 | 6.25 | 0.2185 | 0.2461 |
| E | 7.75 | 8.15 | 0.3051 | 0.3209 |
| E1 | 6.60 | 7.15 | 0.2598 | 0.2815 |
| E2 | 4.40 | 4.70 | 0.1732 | 0.1850 |
| L | 0.75 | 1.50 | 0.0295 | 0.0591 |


Figure 24. SMC recommended footprint



2.5 DPAK package information

- Epoxy meets UL 94,V0
- Cooling method: by conduction (C)

Figure 25. DPAK package outline




Note: This package drawing may slightly differ from the physical package. However, all the specified dimensions are guaranteed.

Table 8. DPAK package mechanical data

| Ref. | Dimensions | | | |
|------|-------------|-------|-----------------------------|-------|
| | Millimeters | | Inches (for reference only) | |
| | Min. | Max. | Min. | Max. |
| A | 2.18 | 2.40 | 0.085 | 0.094 |
| A1 | 0.90 | 1.10 | 0.035 | 0.043 |
| A2 | 0.03 | 0.23 | 0.001 | 0.009 |
| b | 0.64 | 0.90 | 0.025 | 0.035 |
| b4 | 4.95 | 5.46 | 0.194 | 0.215 |
| c | 0.46 | 0.61 | 0.018 | 0.024 |
| c2 | 0.46 | 0.60 | 0.018 | 0.023 |
| D | 5.97 | 6.22 | 0.235 | 0.244 |
| D1 | 4.95 | 5.60 | 0.194 | 0.220 |
| E | 6.35 | 6.73 | 0.250 | 0.265 |
| E1 | 4.32 | 5.50 | 0.170 | 0.216 |
| e | 2.286 typ. | | 0.090 typ. | |
| e1 | 4.40 | 4.70 | 0.173 | 0.185 |
| H | 9.35 | 10.40 | 0.368 | 0.409 |
| L | 1.0 | 1.78 | 0.039 | 0.070 |
| L2 | | 1.27 | | 0.050 |
| L4 | 0.60 | 1.02 | 0.023 | 0.040 |
| V2 | -8° | +8° | -8° | +8° |

Figure 26. DPAK recommended footprint (dimensions in mm)



The device must be positioned within $\oplus 0.05$ AB

3 Ordering information

Table 9. Ordering information

| Order code | Marking | Package | Weight | Base qty. | Delivery mode |
|-------------|---------|----------------|---------|-----------|---------------|
| STPS340AFN | A340 | SMA Flat Notch | 0.039 g | 10 000 | Tape and reel |
| STPS340U | U34 | SMB | 0.107 g | 2500 | Tape and reel |
| STPS340UF | FU34 | SMB Flat | 0.050 g | 5000 | Tape and reel |
| STPS340S | S34 | SMC | 0.243 g | 10 000 | Tape and reel |
| STPS340B-TR | S3 40 | DPAK | 0.320 g | 2500 | Tape and reel |

Revision history

Table 10. Document revision history

| Date | Version | Changes |
|-------------|---------|--|
| Jul-2003 | 7 | Last update. |
| Feb-2005 | 8 | Layout update. No content change. |
| 08-Feb-2007 | 9 | Reformatted to current standard. Added ECOPACK statement. Added SMBflat package. |
| 10-Feb-2009 | 10 | Updated ECOPACK statement. Corrected Y axis in Figure 10. |
| 23-Apr-2015 | 11 | Updated DPAK and reformatted to current standard. |
| 22-Sep-2016 | 12 | Updated DPAK package information and reformatted to current standard. |
| 08-Oct-2019 | 13 | Added Section 2.1 SMA Flat Notch package information . |

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2019 STMicroelectronics – All rights reserved