


600 W TVS in SMB





Bidirectional

Unidirectional

Features

- Peak pulse power: 600 W (10/1000 μ s) and 4 kW (8/20 μ s)
- Stand-off voltage range from 5 V to 188 V
- Unidirectional and bidirectional types
- Low leakage current: 0.2 µA at 25 °C and 1 µA at 85 °C
- Operating Ti max: 150 °C
- High power capability at T_i max.: up to 515 W (10/1000 μs)
- Lead finishing: matte tin plating

Complies with the following standards

- UL94, V0
- J-STD-020 MSL level 1
- J-STD-002, JESD 22-B102 E3 and MIL-STD-750, method 2026 solderable matte tin plated leads
- JESD-201 class 2 whisker test
- IPC7531 footprint
- JEDEC registered package outline
- IEC 61000-4-4 level 4:
 - 4 kV
 - IEC 61000-4-2, C = 150 pF R = 330 Ω exceeds level 4:
 - 30 kV (air discharge)
 - 30 kV (contact discharge)

Description

The SM6T series are designed to protect sensitive equipment against electrostatic discharges according to IEC 61000-4-2 and MIL STD 883, method 3015, and electrical overstress according to IEC 61000-4-4 and 5. This device is more generally used against surges below 600 W (10/1000 µs).

> The Planar technology makes it suitable for high-end equipment and SMPS where low leakage current and high junction temperature are required to provide reliability and stability over time.

The SM6T series are packaged in SMB.



1 Characteristics

Table 1. Absolute maximum ratings (T_{amb} = 25 °C)

| Symbol | | Parameter | Value | Unit |
|------------------|--------------------------------------|-------------------------------------------------------|-------|------|
| | | IEC 61000-4-2 (C = 150 pF, R = 330 Ω) | | |
| V _{PP} | Peak pulse voltage | Contact discharge | 30 | kV |
| | | Air discharge | 30 | |
| P _{PP} | Peak pulse power dissipation | 10/1000 μs, T _j initial = T _{amb} | 600 | W |
| T _{stg} | Storage temperature range | -65 to +150 | °C | |
| T _j | Operating junction temperature range | -55 to +150 | °C | |
| TL | Maximum lead temperature for solderi | 260 | °C | |

Figure 1. Electrical characteristics - parameter definitions





Figure 2. Pulse definition for electrical characteristics



DS0684 - Rev 13 page 2/13



Table 2. Electrical characteristics - parameter values (T_{amb} = 25 °C, unless otherwise specified)

| | Learney at Very Very at 1 (1) | | | | | 10 / 1000 μs | | | 8 / 20µs | | | _ | | |
|-------------|----------------------------------------|-------|----------------------------------------|------|------|-----------------------------------|--------------------------------|----------------|-----------------------------------|--------------------|----------------|------|-------|----------------------|
| _ | I _{RM} max at V _{RM} | | V _{BR} at I _{BR} (1) | | | V _{CL} ⁽²⁾⁽³⁾ | I _{PP} ⁽⁴⁾ | R _D | V _{CL} ⁽²⁾⁽³⁾ | IPP ⁽⁴⁾ | R _D | αΤ | | |
| Туре | 25 °C | 85 °C | | Min. | Тур. | Max. | | Max. | | Max. | Max. | | Max. | Max. |
| | μ | A | ٧ | | ٧ | | mA | V | Α | Ω | V | Α | Ω | 10 ⁻⁴ /°C |
| SM6T6V8A/CA | 20 | 50 | 5.80 | 6.45 | 6.8 | 7.14 | 10 | 10.5 | 57 | 0.059 | 14.4 | 275 | 0.027 | 5.7 |
| SM6T7V5A/CA | 20 | 50 | 6.40 | 7.13 | 7.5 | 7.88 | 10 | 11.3 | 53 | 0.065 | 15.2 | 266 | 0.027 | 6.1 |
| SM6T10A/CA | 20 | 50 | 8.55 | 9.5 | 10.0 | 10.5 | 1 | 14.5 | 41 | 0.098 | 18.6 | 215 | 0.038 | 7.3 |
| SM6T12A/CA | 0.2 | 1 | 10.2 | 11.4 | 12 | 12.6 | 1 | 16.7 | 36 | 0.114 | 21.7 | 184 | 0.049 | 7.8 |
| SM6T15A/CA | 0.2 | 1 | 12.8 | 14.3 | 15 | 15.8 | 1 | 21.2 | 28 | 0.193 | 27.2 | 147 | 0.078 | 8.4 |
| SM6T18A/CA | 0.2 | 1 | 15.3 | 17.1 | 18 | 18.9 | 1 | 25.2 | 24 | 0.263 | 32.5 | 123 | 0.111 | 8.8 |
| SM6T22A/CA | 0.2 | 1 | 18.8 | 20.9 | 22 | 23.1 | 1 | 30.6 | 20 | 0.375 | 39.3 | 102 | 0.159 | 9.2 |
| SM6T24A/CA | 0.2 | 1 | 20.5 | 22.8 | 24 | 25.2 | 1 | 33.2 | 18 | 0.444 | 42.8 | 93 | 0.189 | 9.4 |
| SM6T27A/CA | 0.2 | 1 | 23.1 | 25.7 | 27 | 28.4 | 1 | 37.5 | 16 | 0.569 | 48.3 | 83 | 0.240 | 9.6 |
| SM6T30A/CA | 0.2 | 1 | 25.6 | 28.5 | 30 | 31.5 | 1 | 41.5 | 14.5 | 0.690 | 53.5 | 75 | 0.293 | 9.7 |
| SM6T33A/CA | 0.2 | 1 | 28.2 | 31.4 | 33 | 34.7 | 1 | 45.7 | 13.1 | 0.840 | 59.0 | 68 | 0.357 | 9.8 |
| SM6T36A/CA | 0.2 | 1 | 30.8 | 34.2 | 36 | 37.8 | 1 | 49.9 | 12 | 1.01 | 64.3 | 62 | 0.427 | 9.9 |
| SM6T39A/CA | 0.2 | 1 | 33.3 | 37.1 | 39 | 41.0 | 1 | 53.9 | 11.1 | 1.16 | 69.7 | 57 | 0.504 | 10.0 |
| SM6T56A/CA | 0.2 | 1 | 47.6 | 53.2 | 56 | 58.8 | 1 | 76.6 | 7.8 | 2.28 | 100 | 40 | 1.030 | 10.0 |
| SM6T68A/CA | 0.2 | 1 | 58.1 | 64.6 | 68 | 71.4 | 1 | 92 | 6.5 | 3.17 | 121 | 33 | 1.503 | 10.4 |
| SM6T75A/CA | 0.2 | 1 | 64.1 | 71.3 | 75 | 78.8 | 1 | 103 | 5.8 | 4.17 | 134 | 30 | 1.84 | 10.5 |
| SM6T100A/CA | 0.2 | 1 | 85.5 | 95.0 | 100 | 105 | 1 | 137 | 4.4 | 7.27 | 178 | 22.5 | 3.24 | 10.6 |
| SM6T150A/CA | 0.2 | 1 | 128 | 143 | 150 | 158 | 1 | 207 | 2.9 | 16.9 | 265 | 15 | 7.13 | 10.8 |
| SM6T200A/CA | 0.2 | 1 | 171 | 190 | 200 | 210 | 1 | 274 | 2.2 | 29.1 | 353 | 11.3 | 12.7 | 10.8 |
| SM6T220A/CA | 0.2 | 1 | 188 | 209 | 220 | 231 | 1 | 328 | 2 | 48.5 | 388 | 10.3 | 15.2 | 10.8 |

^{1.} To calculate V_{BR} versus T_j : V_{BR} at T_j = V_{BR} at 25 °C x (1 + αT x (T_j - 25))

DS0684 - Rev 13 page 3/13


^{2.} To calculate V_{CL} versus T_j : V_{CL} at $T_j = V_{CL}$ at 25 °C x (1 + αT x (T_j - 25))


^{3.} To calculate V_{CL} max versus $I_{PPappli}$: $V_{CLmax} = V_{BR}$ max + RD x $I_{PPappli}$


^{4.} Surge capability given for both directions for unidirectional and bidirectional devices




1.1 Characteristics (curves)










DS0684 - Rev 13 page 4/13





Figure 7. Junction capacitance versus reverse applied voltage (unidirectional types) 10000 $T_j = 30 \text{ mV}_{RMS}$ $T_j = 25 ^{\circ}\text{C}$ SM6T6V8A 1000 SM6T15A SM6T30A 100 SM6T100A SM6T220A $V_{R}(V)$ 10 10 100 1000

Figure 8. Junction capacitance versus applied voltage (bidirectional type) C(pF) 10000 f = 1 MHz $V_{\rm osc}$ = 30 mV_{RMS} T_i = 25 °C 1000 SM6T15CA SM6T30CA 100 SM6T68CA SM6T100CA 10 SM6T220CA $V_{\mathsf{R}}(V)$ 1000

Figure 9. Leakage current versus junction temperature I_R (nA) I_R (nA)







DS0684 - Rev 13 page 5/13



2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

2.1 SMB package information

Figure 13. SMB package outline




Table 3. SMB package mechanical data

| | Dimensions | | | | | | | |
|------|------------|--------|-----------------------|--------|--|--|--|--|
| Ref. | Millir | neters | Inches ⁽¹⁾ | | | | | |
| | Min. | Max. | Min. | Max. | | | | |
| A1 | 1.90 | 2.45 | 0.0748 | 0.0965 | | | | |
| A2 | 0.05 | 0.20 | 0.0020 | 0.0079 | | | | |
| b | 1.95 | 2.20 | 0.0768 | 0.0867 | | | | |
| С | 0.15 | 0.40 | 0.0059 | 0.0157 | | | | |
| D | 3.30 | 3.95 | 0.1299 | 0.1556 | | | | |
| E | 5.10 | 5.60 | 0.2008 | 0.2205 | | | | |
| E1 | 4.05 | 4.60 | 0.1594 | 0.1811 | | | | |
| L | 0.75 | 1.50 | 0.0295 | 0.0591 | | | | |

^{1.} Values in inches are converted from mm

DS0684 - Rev 13 page 6/13



Cathode bar (unidirectional devices only)


E: ECOPACK grade
MMM: Marking
PP: Assembly location
Y: Year
WW: week


Figure 16. Package orientation in reel

Bidirectional

Taped according to EIA-481
Pocket dimensions are not on scale.
Pocket shape may vary depending on package
On bidirectional devices, marking and logo may not be always in the same direction.







DS0684 - Rev 13 page 7/13



Figure 20. Tape and reel outline

Note: Pocket dimensions are not on scale Pocket shape may vary depending on package

Table 4. Tape and reel mechanical data


| | Dimensions Millimeters | | | | | | | |
|------|-------------------------|------|------|--|--|--|--|--|
| Ref. | | | | | | | | |
| | Min. | Тур. | Max. | | | | | |
| ØD0 | 1.5 | 1.55 | 1.6 | | | | | |
| ØD1 | 1.5 | | | | | | | |
| F | 5.4 | 5.5 | 5.6 | | | | | |
| K0 | 2.64 | 2.74 | 2.84 | | | | | |
| P0 | 3.9 | 4.0 | 4.1 | | | | | |
| P1 | 7.9 | 8.0 | 8.1 | | | | | |
| P2 | 1.9 | 2.0 | 2.1 | | | | | |
| W | 11.7 | 12.0 | 12.3 | | | | | |

DS0684 - Rev 13 page 8/13



2.2 Reflow profile

Figure 21. ST ECOPACK recommended soldering reflow profile for PCB mounting



Note: Minimize air convection currents in the reflow oven to avoid component movement. Maximum soldering profile corresponds to the latest IPC/JEDEC J-STD-020.

DS0684 - Rev 13 page 9/13



3 Ordering information

Figure 22. Ordering information scheme




Table 5. Ordering information

| Order code | Marking | Package | Weight | Base qty. | Delivery mode |
|---------------|----------------------|---------|--------|-----------|---------------|
| SM6TxxxA / CA | See Table 6. Marking | SMB | 0.11 g | 2500 | Tape and reel |

DS0684 - Rev 13 page 10/13



Table 6. Marking

| Order code | Marking | Order code | Marking |
|------------|-----------------|------------|---------|
| SM6T6V8A | DE | SM6T6V8CA | LE |
| SM6T7V5A | DG | SM6T7V5CA | LG |
| SM6T10A | DP | SM6T10CA | LP |
| SM6T12A | DT | SM6T12CA | LT |
| SM6T15A | DX | SM6T15CA | LX |
| SM6T18A | EE | SM6T18CA | ME |
| SM6T22A | EK | SM6T22CA | MK |
| SM6T24A | EM | SM6T24CA | MM |
| SM6T27A | EP | SM6T27CA | MP |
| SM6T30A | ER | SM6T30CA | MR |
| SM6T33A | ET | SM6T33CA | MT |
| SM6T36A | EV | SM6T36CA | MV |
| SM6T39A | B9A EX SM6T39CA | | MX |
| SM6T56A | FL | SM6T56CA | NL |
| SM6T68A | FQ | SM6T68CA | NQ |
| SM6T75A | FS | SM6T75CA | NS |
| SM6T100A | FY | SM6T100CA | NY |
| SM6T150A | GL | SM6T150CA | OL |
| SM6T200A | GU | SM6T200CA | OU |
| SM6T220A | SM6T220A GW | | OW |

DS0684 - Rev 13 page 11/13



Revision history

Table 7. Document revision history

| Date | Version | Changes |
|-------------|---------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Aug-2001 | 4 | Previous update. |
| 15-Sep-2004 | 5 | 1. Types table parameters on page 2: IRM @ Tj = 85 °C condition added 2. IRM max values changed |
| 26-Mar-2009 | 6 | Reformatted to current standard. SMB dimensions and footprint updated. Maximum junction temperature replaced with operating junction temperature range in Table 1. |
| 25-May-2009 | 7 | Reformatted to current standard. Added standards compliance information on page 1. Added device SM6T56 to Table 3. Updated all characteristic curves. |
| 17-Sep-2009 | 8 | Document updated for low leakage current. |
| 20-Oct-2009 | 9 | Updated Figure 13. |
| 10-Jan-2018 | 10 | Updated Table 3: "Electrical characteristics parameter values (T_{amb} = 25 °C, unless otherwise specified)". |
| 03-Sep-2020 | 11 | Updated Section 1.1 Characteristics (curves). |
| 11-Sep-2020 | 12 | Minor text change. |
| 02-Jun-2021 | 13 | Updated Figure 12. |



IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2021 STMicroelectronics - All rights reserved

DS0684 - Rev 13 page 13/13