


Connectivity Solutions for Building Automation from METZ CONNECT



Connectivity Solutions for Building Automation –


from METZ CONNECT

In the race to stay ahead of the competition, demand for smaller devices as well as additional functionality continues to grow. Within the Building Automation market, new product design trends focus on integration, migration, miniaturisation, and of course, reliability. As a result, the available space on the PC board for components becomes increasingly limited. METZ CONNECT provides ideal solutions for innovative PC board connections to meet these requirements.



Benefits





- > extensive range of connections for various applications
- > solutions for different solder options: Wave, THR, SMT
- > customer specific solutions, pole printing, colour options, technical adaptations
- > T&R packaging options for automatic pick & place
- > technical adaptation to customer requirements
- > over 40 years of experience in Connectivity Solutions
- > close cooperation with our customers



PRODUCT NAME	P/N	TECHNICAL DATA	IMAGE
RT033xxHBLU	313591xx	Screw Terminal solderable Nominal Voltage 150 V Nominal Current 10 A Connecting Capacit 0,2-1,5 mm ² AWG 26-16 Center Line 3,50 mm Direction of Connection 90° Liftsystem	
RT033xxVBLU	313611xx	Screw Terminal solderable Nominal Voltage 150 V Nominal Current 10 A Connecting Capacit 0,2-1,5 mm ² AWG 26-16 Center Line 3,50 mm Direction of Connection 0° Liftsystem	
SC303xxHBNN	SC303xxHBNN	Spring clamp terminal pluggable Nominal Voltage 150 V Nominal Current 4 A Connecting Capacit 0,08-1,5 mm ² AWG 28-16 Center Line 3,50 mm Direction of Connection 90°	
SR213xxVBNC	AST213xx	Spring clamp terminal solderable (THR) Nominal Voltage 150 V Nominal Current 10 A Connecting Capacit 0,08-1,5 mm ² AWG 28-16 Center Line 3,50 m Direction of Connection 0°	
SC305xxHBNN	SC305xxHBNN	Spring clamp terminal pluggable Nominal Voltage 300 V Nominal Current 4 A Connecting Capacit 0,08-1,5 mm ² AWG 28-16 Center Line 5,00 mm Direction of Connection 90°	
SR255xxHBNC	SR255xxHBNC	Spring clamp terminal solderable (THR) Nominal Voltage 300 V Nominal Current 18 A Connecting Capacit 0,2-2,5 mm ² AWG 24-14 (solid wire) AWG 24-12 (stranded wire) Center Line 5,00 mm Direction of Connection 90°	
ST255xxHDNL	ST255xxHDNL	Spring clamp terminal solderable Nominal Voltage 300 V Nominal Current 12 A Connecting Capacit 0,2-2,5 mm ² AWG 24-14 (solid wire) AWG 24-12 (stranded wire) Center Line 5,00 mm Direction of Connection 90° Solder Pins right-angled to the left	

PRODUCT NAME	P/N	TECHNICAL DATA	IMAGE
ST255xxHDNR	ST255xxHDNR	Spring Clamp Terminal solderable Nominal Voltage 300 V Nominal Current 12 A Connecting Capacit 0,2-2,5 mm ² AWG 24-14 (solid wire) AWG 24-12 (stranded wire) Center Line 5,00 mm Direction of Connection 90° Solder Pins right-angled to the right	
RT025xxHDLL	313851xx	Screw Terminal solderable Nominal Voltage 300 V Nominal Current 20 A Connecting Capacit 0,34-2,5 mm ² AWG 20-12 Center Line 5,00 mm Direction of Connection 90° Liftsystem Solder pins right-angled to the left	
RT025xxHDLR	313861xx	Screw Terminal solderable Nominal Voltage 300 V Nominal Current 20 A Connecting Capacit 0,34-2,5 mm ² AWG 20-12 Center Line 5,00 mm Direction of Connection 90° Liftsystem Solder Pins right-angled to the right	
RP095xxRBWC	311571xx	Screw Terminal pluggable Nominal Voltage 300 V Nominal Current 5 A Connecting Capacit 0,08-2,5 mm ² AWG 28-14 Center Line 5,00 mm Direction of Connection 90° Top side pin insertion, snap-in Technique for mounting into a housing	
RP095xxBBWC	311571xx-002730	Screw Terminal pluggable Nominal Voltage 300 V Nominal Current 5 A Connecting Capacit 0,08-2,5 mm ² AWG 28-16 Center Line 5,00 mm Direction of Connection 90° Flat bottom for minimal Installation height	
RP095xxHBWC	311571xx-002740	Screw Terminal pluggable Nominal Voltage 300 V Nominal Current 5 A Connecting Capacit 0,08-2,5 mm ² AWG 28-16 Center Line 5,00 mm Direction of Connection 90° with Ridge	

PRODUCT NAME	P/N	TECHNICAL DATA	IMAGE
SP155xxHBNC	ASP155xx	Spring clamp terminal pluggable Nominal Voltage 300 V Nominal Current 6 A Connecting Capacit 0,08-1,5 mm ² AWG 28-16 Center Line 5,00 mm Direction of Connection 90° Push-button, wire entry perpendicular	
RP025xxHBWC	311071xx	Screw Terminal pluggable Nominal Voltage 300 V Nominal Current 10 A Connecting Capacit 0,08-2,5 mm ² AWG 28-12 Center Line 5,00 mm Direction of Connection 90° Wire Protector	
RP015xxVBLC	313491xx	Screw Terminal pluggable Nominal Voltage 300 V Nominal Current 16 A Connecting Capacit 0,08-2,5 mm ² AWG 28-12 Center Line 5,00 mm Direction of Connection 0° Liftsystem	
SP995xxVBNC	SP995xxVBNC	Spring clamp terminal pluggable Nominal Voltage 300 V Nominal Current 12 A Connecting Capacit 0,2-2,5 mm ² AWG 24-14 (eindrhtig) AWG 24-12 (mehrdrhtig) Center Line 5,00 mm Direction of Connection 0° Two connections per pole	
SP045xxVBNC	ASP045xx	Spring clamp terminal pluggable Nominal Voltage 300 V Nominal Current 10 A Connecting Capacit 0,08-1,5 mm ² AWG 28-16 Center Line 5,00 mm Direction of Connection 0° Eccentric lever	
RT205xxHBLU	310961xx	Screw Terminal solderable Nominal Voltage 300 V Nominal Current 20 A Connecting Capacit 0,34-2,5 mm ² AWG 22-12 Center Line 5,00 mm Direction of Connection 90° Liftsystem Double stacked	

PRODUCT NAME	P/N	TECHNICAL DATA	IMAGE
SM01W01VXNN0G1 SM01W01VXNN1G1	ASM01W0164-0G16 ASM01W0164-1G16	Spring Clamp Terminal solderable (SMT) Nominal Current 13 A Connecting Capacit 0,1-0,75 mm ² AWG 26-18 Direction of Connection 0°	
SM02V01VXNN00G1 SM02V01VXNN01G1	ASM02V0108-0G16 ASM02V0108-1G16	Spring Clamp Terminal solderable (SMT) Nominal Current 4 A Connecting Capacit 0,25-0,5 mm ² AWG 24-20 Direction of Connection 24-200°	
SM99S01VWNN01G7	SM99S01VWNN01G7	Spring Clamp Terminal solderable (SMT) Nominal Voltage 300 V Nominal Current 9 A Connecting Capacit 0,2-1,5 mm ² AWG 24-16 Direction of Connection 90° Finger Push-Button	
SR99S01VBNN00G7	SR99S01VBNN00G7	Spring clamp terminal solderable (THR) Nominal Voltage 300 V Nominal Current 9 A Connecting Capacit 0,2-1,5 mm ² AWG 24-16 Direction of Connection 90° Finger Push-Button	

Printing Options

We offer individual printing options for your terminal blocks. Figures and/or symbols in different orientations depending on the technical feasibility. Inkjet Printing, Pad Printing, and Hot Stamp Printing are available. Design your individual terminal blocks with us.



Inkjet Printing



Pad Printing



Stamp Printing

Colour Options

You can order our terminal blocks in a variety of colours. In some cases we can offer colour coding for each individual pole. This is helpful for either as an additional coding option or to enhance the overall "look" of your device. We would be pleased to advise you on the possible combinations.



METZ CONNECT GmbH is member of the following organizations and associations.



METZ CONNECT USA Inc.

200 Tornillo Way
Tinton Falls, NJ 07712
USA

Phone +1-732-389-1300
Fax +1-732-389-9066

METZ CONNECT France SAS

28, Rue Schweighaeuser
67000 Strasbourg
France

Phone +33 3886 170 73
Fax +33 3886 194 73

METZ CONNECT Zhongshan Ltd.

Ping Chang Road
Ping Pu Industrial Park
Sanxiang Town
Zhongshan City, 528463
Guangdong Province
China

Phone +86 760 86365 055
Fax +86 760 86365 050

METZ CONNECT Asia Pacific Ltd.

Suite 1803, 18/F
Chinachem Hollywood Centre,
1 Hollywood Road, Central
Hong Kong

Phone +852 26 027 300
Fax +852 27 257 522

METZ CONNECT GmbH

Im Tal 2
78176 Blumberg
Germany

Phone +49 7702 533-0
Fax +49 7702 533-189

info@metz-connect.com
www.metz-connect.com

