### MMBD2835LT1G, MMBD2836LT1G, SMMBD2835LT1G

# Monolithic Dual Switching Diodes

### **Features**

- S Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

### **MAXIMUM RATINGS (EACH DIODE)**

Rating	Symbol	Value	Unit
Reverse Voltage MMBD2835LT1G, SMMBD2835LT1G MMBD2836LT1G	V <sub>R</sub>	35 75	Vdc
Forward Current	lF	100	mAdc

#### THERMAL CHARACTERISTICS

Total Device Dissipation FR-5 Board (Note 1)  T <sub>A</sub> = 25°C Derate above 25°C	P <sub>D</sub>	225 1.8	mW mW/°C
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	556	°C/W
Total Device Dissipation Alumina Substrate, (Note 2) T <sub>A</sub> = 25°C Derate above 25°C	P <sub>D</sub>	300	mW mW/°C
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	417	°C/W
Junction and Storage Temperature	T <sub>J</sub> , T <sub>stg</sub>	-55 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

- 1. FR-5 =  $1.0 \times 0.75 \times 0.062$  in.
- 2. Alumina =  $0.4 \times 0.3 \times 0.024$  in. 99.5% alumina.




### ON Semiconductor®

www.onsemi.com



SOT-23 (TO-236AB) CASE 318-08 STYLE 12



#### **MARKING DIAGRAM**



xxx = Specific Device Code A3X = MMBD2835LT1G SMMBD2835LT1G

A2X = MMBD2836LT1G = Date Code

M = Date Code

■ = Pb-Free Package (Note: Microdot may be in either location)

\*Date Code orientation and/or overbar may vary depending upon manufacturing location.

### **ORDERING INFORMATION**

Device	Package	Shipping <sup>†</sup>		
MMBD2835LT1G	SOT-23 (Pb-Free)	3,000 / Tape & Reel		
SMMBD2835LT1G	SOT-23 (Pb-Free)	3,000 / Tape & Reel		
MMBD2836LT1G	SOT-23 (Pb-Free)	3,000 / Tape & Reel		

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


### MMBD2835LT1G, MMBD2836LT1G, SMMBD2835LT1G

### ELECTRICAL CHARACTERISTICS (T<sub>A</sub> = 25°C unless otherwise noted) (EACH DIODE)

Characteristic	Symbol	Min	Max	Unit
OFF CHARACTERISTICS	•			•
Reverse Breakdown Voltage (I <sub>R</sub> = 100 μAdc) MMBD2835LT1G, SMMBD2835LT1G MMBD2836LT1G	V <sub>(BR)</sub>	35 75	- -	Vdc
Reverse Voltage Leakage Current (Note 3)  (V <sub>R</sub> = 30 Vdc)  MMBD2835LT1G, SMMBD2835LT1G  (V <sub>R</sub> = 50 Vdc)  MMBD2836LT1G	I <sub>R</sub>	-	100 100	nAdc
Diode Capacitance (V <sub>R</sub> = 0 V, f = 1.0 MHz)	СТ	-	4.0	pF
Forward Voltage $(I_F = 10 \text{ mAdc})$ $(I_F = 50 \text{ mAdc})$ $(I_F = 100 \text{ mAdc})$	V <sub>F</sub>	- - -	1.0 1.0 1.2	Vdc
Reverse Recovery Time ( $I_F = I_R = 10 \text{ mAdc}$ , $I_{R(REC)} = 1.0 \text{ mAdc}$ ) (Figure 1)	t <sub>rr</sub>	-	4.0	ns

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 3. For each individual diode while the second diode is unbiased.






Notes: 1. A 2.0 k $\Omega$  variable resistor adjusted for a Forward Current (I<sub>F</sub>) of 10 mA.

- 2. Input pulse is adjusted so  $I_{R(peak)}$  is equal to 10 mA.
- 3.  $t_p \gg t_{rr}$

Figure 1. Recovery Time Equivalent Test Circuit

### MMBD2835LT1G, MMBD2836LT1G, SMMBD2835LT1G

### **CURVES APPLICABLE TO EACH CATHODE**






Figure 2. Forward Voltage

Figure 3. Leakage Current





Figure 4. Capacitance

### MMBD2835LT1G, MMBD2836LT1G, SMMBD2835LT1G

### PACKAGE DIMENSIONS

SOT-23 (TO-236) CASE 318-08 **ISSUE AR** 




- DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994. CONTROLLING DIMENSION: MILLIMETERS. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF THE BASE MATERIAL.
  DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH,
- PROTRUSIONS, OR GATE BURRS

	MILLIMETERS			INCHES		
DIM	MIN	NOM	MAX	MIN	NOM	MAX
Α	0.89	1.00	1.11	0.035	0.039	0.044
A1	0.01	0.06	0.10	0.000	0.002	0.004
b	0.37	0.44	0.50	0.015	0.017	0.020
С	0.08	0.14	0.20	0.003	0.006	0.008
D	2.80	2.90	3.04	0.110	0.114	0.120
E	1.20	1.30	1.40	0.047	0.051	0.055
е	1.78	1.90	2.04	0.070	0.075	0.080
L	0.30	0.43	0.55	0.012	0.017	0.022
L1	0.35	0.54	0.69	0.014	0.021	0.027
HE	2.10	2.40	2.64	0.083	0.094	0.104
T	0°	-	10°	0°	-	10°

STYLE 12:

- CATHODE
  - CATHODE
  - ANODE

### **RECOMMENDED** SOLDERING FOOTPRINT\*



**DIMENSIONS: MILLIMETERS** 

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and IN are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="https://www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner

### **PUBLICATION ORDERING INFORMATION**

### LITERATURE FULFILLMENT

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81–3–5817–1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

**ON Semiconductor:** 

MMBD2835LT1G MMBD2836LT1G SMMBD2835LT1G