

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized applications, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an equif prese



February 2014

FXLA102 Low-Voltage Dual-Supply 2-Bit Voltage Translator with Configurable Voltage Supplies and Signal Levels, 3-State Outputs, and Auto Direction Sensing

Features

- Bi-Directional Interface between Two Levels: from 1.1 V to 3. 6V
- Fully Configurable: Inputs and Outputs Track V_{CC} Level
- Non-Preferential Power-Up; Either V_{CC} May Be Powered Up First
- Outputs Switch to 3-State if Either V_{CC} is at GND
- Power-Off Protection
- Bus-Hold on Data Inputs Eliminates the Need for Pull-Up Resistors; Do Not Use Pull-Up Resistors on A or B Ports
- Control Input (/OE) Referenced to V_{CCA} Voltage
- Packaged in MicroPak[™] 8 (1.6 mm x 1.6 mm)
- Direction Control Not Necessary
- 100 Mbps Throughput when Translating Between
 1.8 V and 2.5 V
- ESD Protection Exceeds:
 - 15 kV HBM ((B Port I/O to GND) per JESD22-A114 & Mil Std 883e 3015.7)
 - 8 kV HBM ((A Port I/O to GND) per JESD22-A114 & Mil Std 883e 3015.7)
 - 2 kV CDM (per ESD STM 5.3)

Description

The FXLA102 is a configurable dual-voltage supply translator for both uni-directional and bi-directional voltage translation between two logic levels. The device allows translation between voltages as high as 3.6 V to as low as 1.1 V. The A port tracks the V_{CCA} level and the B port tracks the V_{CCB} level. This allows for bi-directional voltage translation over a variety of voltage levels: 1.2 V, 1.5 V, 1.8 V, 2.5 V, and 3.3 V.


The device remains in three-state as long as either $V_{CC}{=}0~V,$ allowing either V_{CC} to be powered up first. Internal power-down control circuits place the device in 3-state if either V_{CC} is removed.

The /OE input, when HIGH, disables both the A and B ports by placing them in a 3-state condition. The /OE input is supplied by $V_{\rm CCA}.$

The FXLA102 supports bi-directional translation without the need for a direction control pin. The two ports of the device have auto-direction sense capability. Either port may sense an input signal and transfer it as an output signal to the other port.


Ordering	Information
----------	-------------

Part Number	Top Mark	Operating Temperature Range	Package	Packing Method
FXLA102L8X	XF	-40 to 85°C	8-Lead MicroPak [™] 1.6 mm x 1.6 mm Package	5 K Units Tape and Reel



Pin Definitions

Pin #	Name	Description
1	V _{CCA}	A-Side Power Supply
2	A ₀	A Side Input or 3-State Output
3	A ₁	A Side Input or 3-State Output
4	GND	Ground
5	/OE	Output Enable Input
6	B ₁	B Side Input or 3-State Output
7	B ₀	B Side Input or 3-State Output
8	V _{CCB}	B Side Power Supply



H = HIGH Logic Level

L = LOW Logic Level

FXLA102 — Low-Voltage Dual-Supply 2-Bit Voltage Translator

Absolute Maximum Ratings

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

Symbol	Parameter	Conditions	Min.	Max.	Unit	
N/	Supply Voltage	V _{CCA}	-0.5	4.6	V	
V _{CC}	Supply Voltage	V _{CCB}	-0.5	4.6	v	
M		I/O Ports A and B	-0.5	4.6	V	
Vı	DC Input Voltage	Control Input (/OE)	-0.5	4.6	v	
		Output 3-State	-0.5	4.6		
Vo	Output Voltage ⁽²⁾	Output Active (A _n)	-0.5	V _{CCA} +0.5	V	
		Output Active (B _n)	-0.5	V _{CCB} +0.5		
I _{IK}	DC Input Diode Current	V ₁ <0V		-50	mA	
	DC Output Diada Outpat	V _O <0V		-50		
Ι _{οκ}	DC Output Diode Current	Vo>Vcc		+50	mA	
I _{OH} /I _{OL}	DC Output Source/Sink Current		-50	+50	mA	
I _{CC}	DC V _{CC} or Ground Current (per Supply	Pin)		±100	mA	
T _{STG}	Storage Temperature Range		-65	+150	°C	
PD	Power Dissipation			5	mW	
	Human Rady Madal JESD22 A114	B Port I/O to GND		15		
ESD	Human Body Model, JESD22-A114	A Port I/O to GND		8	kV	
	Charged Device Model, JESD22-C101			2		

Notes:

1. I_O absolute maximum ratings must be observed.

2. All unused inputs and input/outputs must be held at V_{CCi} or GND.

Recommended Operating Conditions

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. Fairchild does not recommend exceeding them or designing to Absolute Maximum Ratings.

Symbol	Parameter	Conditions	Min.	Max.	Unit	
V _{cc}	Power Supply	Operating V _{CCA} or V _{CCB}	1.1	3.6	V	
V		Ports A and B	0	3.6	V	
V _{IN}	Input Voltage	Control Input (/OE)	0	V _{CCA}	V	
		V_{CC} = 3.0 V to 3.6 V		±12		
		V_{CC} = 2.3 V to 2.7 V		±8		
	Dynamic Output Current I _{OH} /I _{OL}	V_{CC} = 1.65 V to 1.95 V		±5	mA	
		V_{CC} = 1.40 V to 1.65 V		±3		
		V_{CC} =1.1 V to 1.4 V		±2		
	Static Output Current	V_{CC} =1.1 V to 3.6 V		±4	μA	
TA	Operating Temperature, Free Air		-40	+85	°C	
dt/dV	Maximum Input Edge Rate	$V_{CCA/B} = 1.1$ to 3.6 V		10	ns/V	
Θ_{JA}	Thermal Resistance			280	°C/W	

Power-Up/Power-Down Sequence

FXL translators offer an advantage in that either V_{CC} may be powered up first. This benefit derives from the chip design. When either V_{CC} is at 0 V, outputs are in a high-impedance state. The control input (/OE) is designed to track the V_{CCA} supply. A pull-up resistor tying /OE to V_{CCA} should be used to ensure that bus contention, excessive currents, or oscillations do not occur during power-up or power-down. The size of the pull-up resistor is based upon the current-sinking capability of the device driving the /OE pin.

The recommended power-up sequence is:

- 1. Apply power to the first V_{CC} .
- 2. Apply power to the second V_{CC} .
- 3. Drive the /OE input LOW to enable the device.

The recommended power-down sequence is:

- 1. Drive /OE input HIGH to disable the device.
- 2. Remove power from either V_{CC} .
- 3. Remove power from other V_{CC} .

Pull-Up/Pull-Down Resistors

<u>Do not use pull-up or pull-down resistors.</u> This device has bus-hold circuits: pull-up or pull-down resistors are not recommended because they interfere with the output state. The current through these resistors may exceed the hold drive, $I_{I(HOLD)}$ and/or $I_{I(OD)}$ bus-hold currents. The bus-hold feature eliminates the need for extra resistors.

tor Corporation		

DC Electrical Characteristics

 T_A =-40 to 85°C.

Symbol	Parameter	Conditions	V _{CCA} (V)	V _{CCB} (V)	Min.	Тур.	Max.	Units	
			2.70 to 3.60		2.00				
			2.30 to 2.70		1.60				
VIHA		Data Inputs An Control Pin /OE	1.65 to 2.30	1.10 to 3.60	.65xV _{CCA}			V	
			1.40 to 1.65		$.65 x V_{CCA}$]	
	High Lovel Input Voltage		1.10 to 1.40		$.90 x V_{CCA}$				
	High-Level Input Voltage			2.70 to 3.60	2.00				
				2.30 to 2.70	1.60]	
VIHB		Data Inputs B _n	1.10 to 3.60	1.65 to 2.30	.65хV _{ссв}			V	
				1.40 to 1.65	$.65 x V_{CCB}$				
				1.10 to 1.40	.90xV _{CCB}				
			2.70 to 3.60				.80		
			2.30 to 2.70				.70		
		Data Inputs An Control Pin /OE	1.65 to 2.30	1.10 to 3.60			$.35 x V_{CCA}$	V	
			1.40 to 1.65				$.35 x V_{CCA}$		
			1.10 to 1.40				.10xV _{CCA}		
	Low-Level Input Voltage			2.70 to 3.60			.80	-	
				2.30 to 2.70			.70		
V _{ILB}		Data Inputs B _n	1.10 to 3.60	1.65 to 2.30			$.35 x V_{CCB}$	V	
				1.40 to 1.65			$.35 x V_{CCB}$	-	
				1.10 to 1.40			.10xV _{CCB}		
V _{OHA}	High-Level Output	I _{ОН} =-4 µА	1.10 to 3.60	1.10 to 3.60	V _{CCA} 40			v	
V _{OHB}	Voltage ⁽³⁾	I _{ОН} =-4µ А	1.10 to 3.60	1.10 to 3.60	V _{CCB} 40			v	
V _{OLA}	Low-Level Output	I _{OL} =4 μA	1.10 to 3.60	1.10 to 3.60			.4	N	
V _{OLB}	Voltage ⁽³⁾	I _{OL} =4 μA	1.10 to 3.60	1.10 to 3.60			.4	V	
		V _{IN} =0.80 V	3.00	3.00	75.0				
		V _{IN} =2.00 V	3.00	3.00	-75.0				
		V _{IN} =0.70 V	2.30	2.30	45.0				
		V _{IN} =1.60 V	2.30	2.30	-45.0		/-		
	Bus-Hold Input Minimum	V _{IN} =0.57 V	1.65	1.65	25.0				
I _{I(HOLD)}	Drive Current	V _{IN} =1.07 V	1.65	1.65	-25.0			μA	
		V _{IN} =0.49 V	1.40	1.40	11.0				
		V _{IN} =0.91 V	1.40	1.40	-11.0				
		V _{IN} =0.11 V	1.10	1.10		4.0			
		V _{IN} =0.99 V	1.10	1.10		-4.0			

www.fairchildsemi.com

Continued on following page...

U
\sim
XLA
-
Ξ
Ň
2
Low-
Q
Σ
5
<u> </u>
t.
Voltage Dual-Supply
¥.
L
മ
Ч.
S
σ
σ
Ś
Ņ
Π.
<u>~</u>
/ 2-Bit Voltage Tra
<
0
Ŧ
മ
Q
Ð
-
<u>a</u>
ŭ
Franslat
a
Ħ
¥
•

Т

DC Electrical Characteristics (Continued)

T_A=-40 to 85°C.

Symbol	Parameter	Conditions	V _{CCA} (V)	V _{CCB} (V)	Min.	Max.	Units	
			3.60	3.60	450.00			
	Bus-Hold Input		2.70	2.70	300.00			
I _{I(ODH)}	Overdrive High	Data Inputs A _n , B _n	1.95	1.95	200.00		μA	
	Current ⁽⁴⁾		1.60	1.60	120.00			
			1.40	1.40	80.00			
			3.60	3.60	-450.00			
	Bus-Hold Input		2.70	2.70	-300.00			
I _{I(ODL)}	Overdrive Low	Data Inputs A _n , B _n	1.95	1.95	-200.00		μA	
	Current ⁽⁵⁾		1.60	1.60	-120.00		1	
			1.40	1.40	-80.00			
կ	Input Leakage Current	Control Inputs /OE, VI=V _{CCA} or GND	1.10 to 3.60	3.60		±1.0	μA	
	Power-Off Leakage	An Port Vo=0V to 3.6 V	0	3.6		±2.0		
IOFF	Current	B _n Port V _O =0V to 3.6 V	3.60	0		±2.0	μA	
		Data Outputs A _n , B _n V _O =0 V or 3.6 V, /OE=V _{IH}	3.60	3.60		±5.0		
I _{oz}	3-State Output Leakage	Data Outputs Data Outputs A _n V _O =0 V or 3.6 V, /OE=GND	3.60	0		±5.0	μA	
		Data Outputs B _n V _O =0 V or 3.6 V, /OE=GND	0	3.60		±5.0		
I _{CCA/B}	Quiescent Supply	V _I =V _{CCI} or GND; I _O =0, /OE=GND	1.10 to 3.60	1.10 to 3.60		10.0	μA	
I _{CCZ}	Current ^(6, 7)	$V_I=V_{CCI}$ or GND; $I_O=0$, /OE=V_{IH}	1.10 to 3.60	1.10 to 3.60		10.0	μA	
		V _I =V _{CCB} or GND; I _O =0 B-to-A Direction.	0	1.10 to 3.60		-10.0	μA	
I _{CCA}	Quiescent Supply	/OE=GND	1.10 to 3.60	0		10.0	μΑ	
I _{CCB}	Current	V _I =V _{CCA} or GND; I _O =0, A-to-B Direction,	1.10 to 3.60	0		-10.0	- μΑ	
ICCB		/OE=GND	0	1.10 to 3.60		10.0	μ''	

Notes:

3. This is the output voltage for static conditions. Dynamic drive specifications are given in the Dynamic Output Electrical Characteristics table.

4. An external drive must source at least the specified current to switch LOW-to-HIGH.

5. An external drive must source at least the specified current to switch HIGH-to-LOW.

6. V_{CCI} is the V_{CC} associated with the input side.

7. Reflects current per supply, V_{CCA} or V_{CCB} .

FXLA102 — Low-Voltage Dual-Supply 2-Bit Voltage Translator

Dynamic Output Electrical Characteristic

A Port (A_n)

Output Load: C_L=15 pF, R_L \ge M Ω (C_{I/O}=4 pF), T_A=-40 to 85°C

Symbol	Parameter	V _{CCA} =3.0 V to 3.6 V		V _{CCA} =2.3 V to 2.7 V		V _{CCA} =1.65 V to 1.95 V		V _{CCA} =1.4 V to 1.6 V		V _{CCA} =1.1 V to 1.3 V	Units
		Тур.	Max.	Тур.	Max.	Тур.	Max	Тур.	Max.	Тур.	
t _{rise}	Output Rise Time A Port ⁽⁹⁾		3.0		3.5		4.0		5.0	7.5	ns
t _{fall}	Output Fall Time A Port ⁽¹⁰⁾		3.0		3.5		4.0		5.0	7.5	ns
I _{OHD}	Dynamic Output Current High ⁽⁹⁾	-11.4		-7.5		-4.7		-3.2		-1.7	mA
I _{OLD}	Dynamic Output Current Low ⁽¹⁰⁾	+11.4		+7.5		+4.7		+3.2		+1.7	mA

B Port (B_n)

Output Load: C_L=15 pF, R_L \ge M Ω (C_{I/0}=5 pF), T_A=-40 to 85°C

Symbol	Parameter	V _{CCB} =3.0 V to 3.6 V		V _{CCB} =2.3 V to 2.7 V		V _{ссв} =1.65 V to 1.95 V		V _{CCB} =1.4 V to 1.6 V		V _{CCB} =1.1 V to 1.3 V	Units
-		Тур.	Max.	Тур.	Max.	Тур.	Max	Тур.	Max.	Тур.	
t _{rise}	Output Rise Time B Port ⁽⁹⁾		3.0		3.5		4.0		5.0	7.5	ns
t _{fall}	Output Fall Time B Port ⁽¹⁰⁾		3.0		3.5		4.0		5.0	7.5	ns
I _{OHD}	Dynamic Output Current High ⁽⁹⁾	-12.0		-7.9		-5.0		-3.4		-1.8	mA
I _{OLD}	Dynamic Output Current Low ⁽¹⁰⁾	+12.0		+7.9		+5.0		+3.4		+1.8	mA

Notes:

8. Dynamic output characteristics are guaranteed, but not tested.

9. See Figure 7.

10. See Figure 8.

AC Characteristics

V_{CCA} = 3.0 V to 3.6 V, T_A=-40 to 85°C

Symbol	Parameter		=3.0 V .6 V		=2.3 V 2.7 V	V _{ссв} = to 1.	1.65 V 95 V	V _{ссв} = to 1	=1.4 V .6 V	V _{CCB} =1.1 V to 1.3 V	Units
		Min.	Max.	Min.	Max.	Min.	Max	Min.	Max.	Тур.	
	A to B	0.2	3.5	0.3	3.9	0.5	5.4	0.6	6.8	10.0	ns
t _{PLH} ,t _{PHL}	B to A	0.2	3.5	0.2	3.8	0.3	5.0	0.5	6.0	7.0	ns
t _{PZL} ,t _{PZH}	/OE to A, /OE to B		1.7		1.7		1.7		1.7	1.7	μs
t _{skew}	A Port, B Port ⁽¹¹⁾		0.5		0.5		0.5		1.0	1.0	ns

$V_{CCA} = 2.3 V$ to 2.7 V, T_A =-40 to 85°C

Symbol	Parameter		=3.0 V .6 V		=2.3 V 2.7 V	V _{CCB} = to 1.	1.65 V 95 V		=1.4 V .6 V	V _{CCB} =1.1 V to 1.3 V	Units
		Min.	Max.	Min.	Max.	Min.	Max	Min.	Max.	Тур.	
	A to B	0.2	3.8	0.4	4.2	0.5	5.6	0.8	6.9	10.5	ns
t _{PLH} ,t _{PHL}	B to A	0.3	3.9	0.4	4.2	0.5	5.5	0.5	6.5	7.0	ns
t _{PZL} ,t _{PZH}	/OE to A, /OE to B		1.7		1.7		1.7		1.7	1.7	μs
t _{SKEW}	A Port, B Port ⁽¹¹⁾		0.5		0.5		0.5		1.0	1.0	ns

V_{CCA} = 1.65 V to 1.95 V, T_A=-40 to 85°C

Symbol	Parameter		=3.0 V 5.6 V	V _{ссв} = to 2	=2.3 V .7 V	V _{CCB} = to 1.	1.65 V 95 V	V _{ссв} = to 1	=1.4 V .6 V	V _{CCB} =1.1 V to 1.3 V	Units
		Min.	Max.	Min.	Max.	Min.	Max	Min.	Max.	Тур.	
	A to B	0.3	5.0	0.5	5.5	0.8	6.7	0.9	7.5	11.0	ns
t _{PLH} ,t _{PHL}	B to A	0.5	5.4	0.5	5.6	0.8	6.7	1.0	7.0	7.0	ns
t _{PZL} ,t _{PZH}	/OE to A, /OE to B		1.7		1.7		1.7		1.7	1.7	μs
t _{skew}	A Port, B Port ⁽¹¹⁾		0.5		0.5		0.5		1.0	1.0	ns

Note:

11. Skew is the variation of propagation delay between output signals and applies only to output signals on the same port (An or Bn) and switching with the same polarity (LOW-to-HIGH or HIGH-to-LOW) (see Figure 10). Skew is guaranteed, but not tested.

AC Characteristics (Continued)

$V_{CCA} = 1.$	V _{CCA} = 1.4 V to 1.6 V, T _A =-40 to 85°C										
Symbol	Parameter	V _{CCB} =3.0 V to 3.6 V		V _{CCB} =2.3 V to 2.7 V		V _{CCB} =1.65 V to 1.95 V		V _{CCB} =1.4 V to 1.6 V		V _{CCB} =1.1 V to 1.3 V	Units
		Min.	Max.	Min.	Max.	Min.	Max	Min.	Max.	Тур.	
	A to B	0.5	6.0	0.5	6.5	1.0	7.0	1.0	8.5	11.5	ns
t _{PLH} ,t _{PHL}	B to A	0.6	6.8	0.8	6.9	0.9	7.5	1.0	8.5	9.0	ns
t _{PZL} ,t _{PZH}	/OE to A, /OE to B		1.7		1.7		1.7		1.7	1.7	μs
t _{skew}	A Port, B Port ⁽¹²⁾		1.0		1.0		1.0		1.0	1.0	ns

$V_{CCA} = 1.1 \text{ V to } 1.3 \text{ V}, T_{A} = -40 \text{ to } 85^{\circ}\text{C}$

Symbol	Parameter	V _{CCB} =3.0 V to 3.6 V	V _{CCB} =2.3 V to 2.7 V	V _{CCB} =1.65 V to 1.95 V	V _{CCB} =1.4 V to 1.6 V	V _{CCB} =1.1 V to 1.3 V	Units	
		Тур.	Тур.	Тур.	Тур.	Тур.		
	A to B	7.1	6.5	7.0	7.1	13.5	ns	
t _{PLH} ,t _{PHL}	B to A	10.3	10.5	10.8	11.3	13.5	ns	
t _{PZL} ,t _{PZH}	/OE to A, /OE to B	1.7	1.7	1.7	1.7	1.7	μs	
t _{SKEW}	A Port, B Port ⁽¹²⁾	1.0	1.0	1.0	1.0	1.0	ns	

Note:

12. Skew is the variation of propagation delay between output signals and applies only to output signals on the same port (An or Bn) and switching with the same polarity (LOW-to-HIGH or HIGH-to-LOW) (see Figure 10). Skew is guaranteed, but not tested.

Maximum Data Rate

T_A=-40 to 85°C.

V _{CCA}	V _{CCB} =3.0 V to 3.6 V	V _{CCB} =2.3 V to 2.7 V	V _{CCB} =1.65 V to 1.95 V	V _{CCB} =1.4 V to 1.6 V	V _{CCB} =1.1V to 1.3 V	Units
	Min.	Min.	Min.	Min.	Тур.	
$V_{CCA}{=}3.00$ V to 3.60 V	140	120	100	80	40	Mbps
$V_{\text{CCA}}\text{=}2.30$ V to 2.70 V	120	120	100	80	40	Mbps
$V_{CCA}{=}1.65~V$ to 1.95 V	100	100	80	60	40	Mbps
$V_{CCA}{=}1.40$ V to 1.60 V	80	80	60	60	40	Mbps
V _{CCA} =1.10 V to 1.30 V	Тур.	Тур.	Тур.	Тур.	Тур.	
VCCA-1.10 V 10 1.30 V	40	40	40	40	40	Mbps

Notes:

13. Maximum data rate is guaranteed, but not tested.

14. Maximum data rate is specified in megabits per second (see Figure 9). It is equivalent to two times the F-toggle frequency, specified in megahertz. For example, 100 Mbps is equivalent to 50 MHz.

Capacitance

Symbol	Parameter		Conditions	T _A =+25°C Typical	Units
CIN	Input Capacitance Control Pi	n (/OE)	V _{CCA} =V _{CCB} =GND	3	рF
C			V _{CCA} =V _{CCB} =3.3 V, /OE=V _{CCA}	4	ъĘ
UI/O	C _{I/O} Input / Output Capacitance	Bn	$v_{CCA} = v_{CCB} = 3.3 v$; $OE = v_{CCA}$	5	pF
C_{pd}	Power Dissipation Capacitance		$V_{CCA}=V_{CCB}=3.3 \text{ V}, V_I=0 \text{ V or } V_{CC}, f=10 \text{ MHz}$	25	pF

I/O Architecture Benefit

The FXLA102 I/O architecture benefits the end user, beyond level translation, in the following three ways:

Auto Direction without an external direction pin.

Drive Capacitive Loads. Automatically shifts to a higher current drive mode only during "Dynamic Mode" or HL / LH transitions.

Lower Power Consumption. Automatically shifts to low-power mode during "Static Mode" (no transitions), lowering power consumption.

The FXLA102 does not require a direction pin. Instead, the I/O architecture detects input transitions on both side and automatically transfers the data to the corresponding output. For example, for a given channel, if both A and B side are at a static LOW, the direction has been established as $A \rightarrow B$, and a LH transition occurs on the B port; the FXLA102 internal I/O architecture automatically changes direction from $A \rightarrow B$ to $B \rightarrow A$.

During HL / LH transitions, or "Dynamic Mode," a strong output driver drives the output channel in parallel with a weak output driver. After a typical delay of approximately 10 ns - 50 ns, the strong driver is turned off, leaving the weak driver enabled for holding the logic state of the channel. This weak driver is called the "bus hold." "Static Mode" is when only the bus hold drives the channel. The bus hold can be over ridden in the event of a direction change. The strong driver allows the FXLA102 to quickly charge and discharge capacitive transmission lines during dynamic mode. Static mode conserves power, where I_{CC} is typically < 5 µA.

Bus Hold Minimum Drive Current

Specifies the minimum amount of current the bus hold driver can source/sink. The bus hold minimum drive current (II_{HOLD}) is V_{CC} dependent and guaranteed in the DC Electrical tables. The intent is to maintain a valid output state in a static mode, but that can be overridden when an input data transition occurs.

Bus Hold Input Overdrive Drive Current

Specifies the minimum amount of current required (by an external device) to overdrive the bus hold in the event of a direction change. The bus hold overdrive (II_{ODH} , II_{ODL}) is V_{CC} dependent and guaranteed in the DC Electrical tables.

Dynamic Output Current

The strength of the output driver during LH / HL transitions is referenced on page 8, Dynamic Output Electrical Characteristics, I_{OHD} , and I_{OLD} .

Test Diagrams







Table 1. AC Test Conditions

Test	Input Signal	Output Enable Control
t _{PLH} , t _{PHL}	Data Pulses	0 V
t _{PZL}	0 V	HIGH to LOW Switch
tрzн	Vcci	HIGH to LOW Switch

Table 2. AC Load

V _{cco}	C1	R1
1.2 V± 0.1 V	15 pF	1 MΩ
1.5 V± 0.1 V	15 pF	1 MΩ
1.8 V ± 0.15 V	15 pF	1 MΩ
$2.5~\textrm{V}\pm0.2~\textrm{V}$	15 pF	1 MΩ
$3.3~\text{V}\pm0.3~\text{V}$	15 pF	1 MΩ





Notes:

- 15. Input $t_R = t_F = 2.0$ ns, 10% to 90%.
- 16. Input $t_{\text{R}} = t_{\text{F}} = 2.5$ ns, 10% to 90%, at $V_{\text{I}} = 3.0$ V to 3.6 V only.




Figure 5. 3-State Output Low Enable Time

Notes:

17. Input $t_R = t_F = 2.0$ ns, 10% to 90%.

18. Input $t_R = t_F = 2.5$ ns, 10% to 90%, at $V_I = 3.0$ V to 3.6 V only.




Figure 6. 3-State Output High Enable Time

Notes:

19. Input $t_R = t_F = 2.0$ ns, 10% to 90%.


20. Input t_{R} = t_{F} = 2.5 ns, 10% to 90%, at V_{I} = 3.0 V to 3.6 V only.


Table 3. Test Measure Points


Symbol	V _{cc}
V _M ⁽²¹⁾	V _{CCI} /2
V _{MO}	V _{CCo} /2
V _X	0.9 x V _{CCo}
V _Y	0.1 x V _{CCo}

Note:


21. $V_{CCI}=V_{CCA}$ for control pin /OE or $V_{MI}=(V_{CCA}/2)$.








$$I_{OLD} \approx (C_L + C_{I/O}) \times \frac{\Delta V_{OUT}}{\Delta t} = (C_L + C_{I/O}) \times \frac{(80\% - 20\%) \bullet V_{CCO}}{t_{FALL}}$$





Maximum Data Rate, $f = 1/t_W$

Figure 9. Maximum Data Rate





Figure 10. Output Skew Time

Note:

22. $t_{SKEW} = (t_{pHLmax} - t_{pHLmin}) \text{ or } (t_{pLHmax} - t_{pLHmin})$



http://www.fairchildsemi.com/packaging/.

Tape and Reel Specifications

Please visit Fairchild Semiconductor's online packaging area for the most recent tape and reel specifications: <u>hhttp://www.fairchildsemi.com/products/logic/pdf/micropak_tr.pdf/</u> FXLA102 — Low-Voltage Dual-Supply 2-Bit Voltage Translator

XLA102 FAIRCHILD SEMICONDUCTOR TRADEMARKS Low-Voltage Dual-Supply 2-Bit Voltage Translator The following includes registered and unregistered trademarks and service marks, owned by Fairchild Serriconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks. Svnc-Lock™ AccuPower™ AX-CAP®∗ E-PEST FRFET® 6 GENERAL® Global Power Resourcesm BitSiC™ PowerTrench[®] TinyBoost® TinyBuck® Build it Now™ GreenBridge™ PowerXS™ Green FPS™ CorePLUS™ Programmable Active Droop™ CorePOWER™ Green FPS™ e-Series™ TinyCalc™ OFET Gmax™ TinyLogic® CROSSVOLT** QSTM CTI TM **GTO™** TINYOPTOT Quiet Series™ IntelliMAX™ TinyPower™ Current Transfer Logic™ RapidConfigure™ ISOPLANAR[™] TinyPWM™ DEUXPEED TinyWire™ Dual Cool™ Making Small Speakers Sound Louder Saving our world, 1mW/W/kW at a time™ EcoSPARK[®] and Better™ TranSiC™ SignalWise™ EfficientMax™ MegaBuck™ TriFault Detect™ SmartMax™ MIČROCOUPLER™ **ESBC™** TRUECURRENT®* SMART STARTM MicroFET™ µSerDes™ Solutions for Your Success™ MicroPak™ airchild® SPM® MicroPak2™ Fairchild Semiconductor® STEALTH** MillerDrive™ UHC FACT Quiet Series™ FACT[®] FAST[®] SuperFET® MotionMax™ Ultra FRFET™ SuperSOT™-3 mWSaver® UniFET™ SuperSOT™-6 OptoHiT™ VCXTM FastvCore™ SuperSOT™-8 **OPTOLOGIC[®]** VisualMax™ FETBench™ SupreMOS[®] OPTOPLANAR® VoltagePlus™ EPSTM SyncFET™ XSTN * Trademarks of System General Corporation, used under license by Fairchild Semiconductor. DISCLAIMER FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS LIFE SUPPORT POLICY FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein: Life support devices or systems are devices or systems which, (a) are 2. A critical component in any component of a life support, device, or 1 intended for surgical implant into the body or (b) support or sustain system whose failure to perform can be reasonably expected to life, and (c) whose failure to perform when properly used in cause the failure of the life support device or system, or to affect its accordance with instructions for use provided in the labeling, can be safety or effectiveness. reasonably expected to result in a significant injury of the user ANTI-COUNTERFEITING POLICY Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.fairchildsemi.com, under Sales Support. Counterfeiting of semiconductor parts is a growing problem in the industry. All manufacturers of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed applications, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address any warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors. PRODUCT STATUS DEFINITIONS Definition of Terms Datasheet Identification Product Status Definition Datasheet contains the design specifications for product development. Specifications may change Formative / In Design Advance Information in any manner without notice Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Preliminary First Production Semiconductor reserves the right to make changes at any time without notice to improve design. Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make No Identification Needed Full Production changes at any time without notice to improve the design. Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. Obsolete Not In Production The datasheet is for reference information only. Rev. 166

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor has against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death ass

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ON Semiconductor: <u>FXLA102L8X</u>