
Product data sheet Miniature connectors



Product description

Contacts: 7, cable plug connector, cable outlet 6 - 8 mm, silver plated contacts

Area Order number M16 IP67 Series 723 09 0125 70 07



You can find the component part drawing on the next page.

Technical data

General values

Connector design Connector locking system Termination Wire gauge (mm) Wire gauge (AWG) Cable outlet Upper limit temperature Lower limit temperature cable connector bolted 0,75 mm² 20 6,0 - 8,0 mm 95 °C -40 °C

Electrical values

Rated current (40 °C) Rated voltage Rated impulse voltage Pollution degree Overvoltage category Insulating material group Volume resistivity Insulation resistance EMC compliance Degree of protection Mechanical operation

Material

Contact material Contact plating Contact body material Housing material 5 A 125 V 800 V 1 I II ≤ 5 mΩ ≥ $10^{10}\Omega$ Shielding is not possible IP67 > 500 Mating cycles

CuZn (brass) Ag (silver) PBT (UL 94 V-0) PA


Product data sheet Miniature connectors



Product description

Contacts: 7, cable plug connector, cable outlet 6 - 8 mm, silver plated contacts

Area Order number M16 IP67 Series 723 09 0125 70 07



Product data sheet Miniature connectors



Product description

Contacts: 7, cable plug connector, cable outlet 6 - 8 mm, silver plated contacts

Area Order number M16 IP67 Series 723 09 0125 70 07

Security notices

The connector must not be connected or separated under load. Non-observance and incorrect use can result in personal injury.

The connectors are designed for use in plant, control system and electrical equipment. The end user is responsible for checking whether the connectors are suitable for use in other applications.

Connectors used in electrical circuits containing hazardous life parts must only be assembled and used by or under the supervision of persons with the requisite electrotechnical training, taking the applicable regulations and standards into account.

Connectors with degree of protection IP 67 and IP 68 are not suitable for use under water. When used outdoors, the connectors must be separately protected against corrosion. For further information about IP degrees of protection refer to 'Technical support' in the Download Centre.

To lock the cable connector to the equipment connector, the threaded ring is tightened until it is 'finger-tight' (approx. 50 cNm).