

Murata Power Solutions

MTE1 Series Isolated 1W Single Output SM DC/DC Converters



- Single isolated output
- 1kVDC Isolation
- Efficiency up to 88%
- Power density 1.8W/cm³
- Wide temperature performance at full
 1 Watt load, -40°C to 85°C
- UL 94V-0 Package material
- Footprint over pins 1.37cm²
- 3.3V, 5V, 12V, 15V & 24V Input
- 3.3V, 5V, 9V, 12V & 15V Output
- Internal SMD construction
- Toroidal magnetics

SELECTION GU	IDE										
Order Code ¹	Nominal Input Voltage	Output Voltage	Output Current	Input Current at Rated Load (Typ.)	Load Regulation (Typ.)	Load Regulation (Max)	Output Ripple & Noise (Typ.)	Efficiency (Min.)	Efficiency (Typ.)	Isolation Capacitance	MTTF ²
	V	V	mA	mA	%	%	mVp-p	%	%	pF	kHrs
MTE1S0303MC	3.3	3.3	303	382	11	13.5	33	75	78	15	
MTE1S0305MC	3.3	5	200	363	8.5	11	24	79	82	16	
MTE1S0309MC	3.3	9	111	353	7	9	17	82	85	21	
MTE1S0312MC	3.3	12	83	348	6.5	8	15	83	86	20	
MTE1S0315MC	3.3	15	66	346	6	8	13	83	86	20	
MTE1S0503MC	5	3.3	303	248	9	12	24	77	79	21	
MTE1S0505MC	5	5	200	239	6.5	8	20	79	82	22	
MTE1S0506MC	5	6	TBC	236	6	7.5	20	81	83	24	
MTE1S0509MC	5	9	111	233	5	6.5	15	83	85	26	
MTE1S0512MC	5	12	83	227	5	6.5	14	84	87	29	
MTE1S0515MC	5	15	66	225	5	6.5	11	85	88	33	
MTE1S1205MC	12	5	200	97	5	7	19	81	84	34	
MTE1S1209MC	12	9	111	95	3	4.5	13	82	86	39	
MTE1S1212MC	12	12	83	93	3	4.5	12	85	88	43	
MTE1S1215MC	12	15	66	93	3	4	11	85	88	40	
MTE1S1505MC	15	5	200	79	4	5.5	15	80	83	25	
MTE1S1509MC	15	9	111	77	3	4	9	81	86	38	
MTE1S1512MC	15	12	83	76	2.5	4	10	82	87	45	
MTE1S1515MC	15	15	66	75	2.5	4	8	84	88	57	
MTE1S2405MC	24	5	200	50	4	5.5	20	79	83	21	
MTE1S2409MC	24	9	111	48	2.5	4	19	84	86	31	
MTE1S2412MC	24	12	83	48	2	3.5	19	83	87	41	
MTE1S2415MC	24	15	66	48	2	3.5	22	85	88	48	

PRODUCT OVERVIEW

The MTE1 series is a new range of surface mount, high performance 1W DC-DC converters. The MTE1 series is the new high performance version of our 1W NTE series, the MTE1 series is more efficient and offers improved regulation performance. The MTE1 series offers 1W of available output power over the full industrial temperature range of -40°C to 85°C.

The MTE1 series has a MSL rating 1, and is compatible with a peak reflow solder temperature of 245°C as per J-STD-020D.

INPUT CHARACTERISTICS						
Parameter	Conditions	Min.	Тур.	Max.	Units	
	Continuous operation, 3.3V input types	2.97	3.3	3.63		
	Continuous operation, 5V input types	4.5	5.0	5.5		
Voltage range	Continuous operation, 12V input types	10.8	12.0	13.2	V	
	Continuous operation, 15V input types	13.5	15.0	16.5		
	Continuous operation, 24V input types	21.6	24	26.4		
Reflected ripple current			5	15	mA p-p	

ISOLATION CHARACTERISTICS						
Parameter	Conditions	Min.	Тур.	Max.	Units	
Isolation voltage	Flash tested for 1 second	1000			VDC	
Resistance	Viso= 1000VDC	20			GΩ	

GENERAL CHARACTERISTICS					
Parameter	Conditions	Min.	Тур.	Max.	Units
Switching frequency	All output types		80		Hz

ABSOLUTE MAXIMUM RATINGS		
Lead temperature 1.5mm from case for 10 seconds	300°C	
Internal power dissipation	600mW	
Input voltage V _{IN} , MTE03 types	5.5V	
Input voltage V _{IN} , MTE05 types	7V	
Input voltage V _{IN} , MTE12 types	15V	
Input voltage V _{IN} , MTE15 types	18V	
Input voltage V _{IN} , MTE24 types	28V	

- $1.\ If\ components\ are\ required\ in\ tape\ and\ reel\ format\ suffix\ order\ code\ with\ -R,\ e.g.\ MTE0505MC-R.$
- Calculated using MIL-HDBK-217 FN2 calculation model with nominal input voltage at full load.
 All specifications typical at TA=25°C, nominal input voltage and rated output current unless otherwise specified.







OUTPUT CHARACTERISTICS					
Parameter	Conditions	Min.	Тур.	Max.	Units
Rated power	T _A =-40°C to 85°C			1.0	W
Voltage set point accuracy	See tolerance envelope				
Line regulation	High V _{IN} to low V _{IN}		1.1	1.2	%/%
Ripple and noise	BW=DC to 20MHz		25	70	mV p-p

TEMPERATURE CHARACTERISTICS					
Parameter	Conditions	Min.	Typ.	Max.	Units
Specification	All output types	-40		85	
Storage		-50		130	°C
Case temperature rise above ambient	All output types		12.5	20	
Cooling	Free air convection				

TECHNICAL NOTES

ISOLATION VOLTAGE

'Hi Pot Test', 'Flash Tested', 'Withstand Voltage', 'Proof Voltage', 'Dielectric Withstand Voltage' & 'Isolation Test Voltage' are all terms that relate to the same thing, a test voltage, applied for a specified time, across a component designed to provide electrical isolation, to verify the integrity of that isolation.

Murata Power Solutions MTE series of DC/DC converters are all 100% production tested at their stated isolation voltage. This is 1kVDC for 1 second.


A question commonly asked is, "What is the continuous voltage that can be applied across the part in normal operation?"

For a part holding no specific agency approvals, such as the MTE series, both input and output should normally be maintained within SELV limits i.e. less than 42.4V peak, or 60VDC. The isolation test voltage represents a measure of immunity to transient voltages and the part should never be used as an element of a safety isolation system. The part could be expected to function correctly with several hundred volts offset applied continuously across the isolation barrier; but then the circuitry on both sides of the barrier must be regarded as operating at an unsafe voltage and further isolation/insulation systems must form a barrier between these circuits and any user-accessible circuitry according to safety standard requirements.

REPEATED HIGH-VOLTAGE ISOLATION TESTING

It is well known that repeated high-voltage isolation testing of a barrier component can actually degrade isolation capability, to a lesser or greater degree depending on materials, construction and environment. The MTE series has toroidal isolation transformers, with no additional insulation between primary and secondary windings of enameled wire. While parts can be expected to withstand several times the stated test voltage, the isolation capability does depend on the wire insulation. Any material, including this enamel (typically polyurethane) is susceptible to eventual chemical degradation when subject to very high applied voltages thus implying that the number of tests should be strictly limited. We therefore strongly advise against repeated high voltage isolation testing, but if it is absolutely required, that the voltage be reduced by 20% from specified test voltage.


This consideration equally applies to agency recognized parts rated for better than functional isolation where the wire enamel insulation is always supplemeMTEd by a further insulation system of physical spacing or barriers.





1. 12V input types have typically 3% less load regulation change.


TOLERANCE ENVELOPES


The voltage tolerance envelope shows typical load regulation characteristics for this product series. The tolerance envelope is the maximum output voltage variation due to changes in output loading.

















Rohs Compliance, MSL and PSL Information



This series is compatible with RoHS soldering systems with a peak reflow solder temperature of 245°C as per J-STD-020D. The pin termination finish on this product series is Matte Tin over Nickel Preplate. The series is backward compatible with Sn/Pb soldering systems. The series has a Moisture Sensitivity Level (MSL) 1.

Samples of the product series were tested in accordance with the conditioning described for MSL level 1 in IPS/J-STD-020D. The product series passed electrical tests and visual inspection criteria.

For further information, please visit: www.murata-ps.com/rohs



APPLICATION NOTES

Minimum load


The minimum load to meet datasheet specification is 10% of the full rated load across the specified input voltage range. Lower than 10% minimum loading will result in an increase in output voltage, which may rise to typically double the specified output voltage if the output load falls to less than 5%.


Capacitive loading and start up

Typical start up times for this series, with a typical input voltage rise time of $2.2\mu s$ and output capacitance of $10\mu F$, are shown in the table below. The product series will start into a capacitance of $47\mu F$ with an increased start time, however, the maximum recommended output capacitance is $10\mu F$.

	Start-up time
	μs
MTE1S0303MC	
MTE1S0305MC	
MTE1S0309MC	
MTE1S0312MC	
MTE1S0315MC	
MTE1S0503MC	
MTE1S0505MC	
MTE1S0506MC	

	Start-up time
	μs
MTE1S0509MC	
MTE1S0512MC	
MTE1S0515MC	
MTE1S1205MC	
MTE1S1209MC	
MTE1S1212MC	
MTE1S1215MC	
MTE1S1505MC	






Output Ripple Reduction

By using the values of inductance and capacitance stated, the output ripple at the rated load is lowered to 5mV p-p max.

Component selection

Capacitor: It is required that the ESR (Equivalent Series Resistance) should be as low as possible, ceramic types are recommended. The voltage rating should be at least twice (except for 15V output), the rated output voltage of the DC/DC converter.

Inductor: The rated current of the inductor should not be less than that of the output of the DC/DC converter. At the rated current, the DC resistance of the inductor should be such that the voltage drop across the inductor is <2% of the rated voltage of the DC/DC converter. The SRF (Self Resonant Frequency) should be >20MHz.




		Capacitor		
	L, µH	SMD	Through Hole	C, µF
MTE1S0303MC				
MTE1S0305MC				
MTE1S0309MC				
MTE1S0312MC				
MTE1S0315MC				
MTE1S0503MC				
MTE1S0505MC				
MTE1S0506MC				
MTE1S0509MC				
MTE1S0512MC				
MTE1S0515MC				
MTE1S1205MC				

Inductor			Capacitor
L, µH	SMD	Through Hole	C, µF
	L, µН		









PIN CONNECTIONS Pin Function 1 -V_{IN}

3	+VIN
5	NA
7	-Vout
8	+ V оит
10	NA
12	NA
14	NA

NA - Not available for electrical connection.







TAPE & REEL SPECIFICATIONS REEL OUTLINE DIMENSIONS TAPE OUTLINE DIMENSIONS - 0.60 (0.02) MAX -Ø_(3.94) MIN 1.50 (Ø0.06) +0.004 (+0.10) -0.00 (-0.00) DIRECTION OF UNREELING (AT HUB SECTION) 16.00 (0.63) 13.00±0.25 ф Ø (0.51±0.009) 2.00 丁 1.75(0.07) 11.50 ____ (0.45) 24.00±0.30 (0.94±0.04) REEL PACKAGING DETAILS 0 TRAILER SECTION **GOODS ENCLOSURE** CARRIER TAPE START 160 (6.30) MIN **SECTION** 100 (3.94) MIN **Product Orientation** LEADER SECTION Pin 1, located nearest to carrier drive sprocket. 400 (15.75) MIN Reel Quantity: TBC

Murata Power Solutions, Inc.
11 Cabot Boulevard, Mansfield, MA 02048-1151 U.S.A. ISO 9001 and 14001 REGISTERED

Murata Power Solutions, Inc. makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patient rights. The descriptions contained herein do not imply the granting of licenses to make, use, or sell equipment constructed in accordance therewith. Specifications are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Murata:

 MTE1S0505MC-R
 MTE1S0303MC-R
 MTE1S0512MC
 MTE1S0515MC-R
 MTE1S0305MC-R
 MTE1S2415MC-R

 MTE1S2405MC-R
 MTE1S1212MC
 MTE1S1212MC-R
 MTE1S1512MC
 MTE1S1505MC

 MTE1S1509MC-R
 MTE1S0315MC-R
 MTE1S1512MC-R
 MTE1S0303MC
 MTE1S0509MC
 MTE1S0506MC-R

 MTE1S1215MC
 MTE1S2409MC-R
 MTE1S1209MC
 MTE1S1509MC
 MTE1S2412MC

 MTE1S0312MC
 MTE1S1215MC-R
 MTE1S1205MC-R
 MTE1S0309MC-R
 MTE1S1515MC-R

 MTE1S0309MC
 MTE1S0503MC-R
 MTE1S1205MC-R
 MTE1S0503MC-R
 MTE1S1515MC-R

 MTE1S0312MC-R
 MTE1S0305MC
 MTE1S1515MC-R
 MTE1S2405MC
 MTE1S1209MC-R
 MTE1S0512MC-R

 MTE1S2412MC-R
 MTE1S0509MC-R
 MTE1S0505MC
 MTE1S0505MC
 MTE1S0505MC