

November 2018



- Pletronics' SM77H Series is a quartz crystal controlled precision square wave generator with a CMOS output.
- The package is designed for high density surface mount designs.
- This is a low cost mass produced oscillator.
- Tape and Reel or cut tape packaging is available.
- 0.8 to 70 MHz
- 5 x 7 mm LCC Ceramic Package
- Enable/Disable or Standby Function
- Disable function includes low standby power mode
- Low Jitter

Pletronics Inc. certifies this device is in accordance with the RoHS 6/6 (2011/65/EC) and WEEE (2002/96/EC) directives.

Pletronics Inc. guarantees the device does not contain the following: Cadmium, Hexavalent Chromium, Lead, Mercury, PBB's, PBDE's Weight of the Device: 0.17 grams Moisture Sensitivity Level: 1 As defined in J-STD-020C Second Level Interconnect code: e4

Absolute Maximum Ratings:

Parameter	Unit
V _{cc} Supply Voltage	-0.5V to +7.0V
Vi Input Voltage	-0.5V to V _{CC} + 0.5V
Vo Output Voltage	-0.5V to V _{CC} + 0.5V
lo Output Current	+25 mA to -25 mA

Thermal Characteristics

The maximum die or junction temperature is 155°C

The thermal resistance junction to board is 30 to 50°C/Watt depending on the solder pads, ground plane and construction of the PCB.



November 2018

Part Number:

SM77	45	н	E	V	- 25.0M	-XX	
							Packaging code or blank T250 = 250 per Tape and Reel T500 = 500 per Tape and Reel T1K = 1,000 per Tape and Reel
							Frequency in MHz
							Supply Voltage V _{cc} V = 3.3V <u>+</u> 10%
							Optional Enhanced OTR Blank = Temp. range -10 to +70°C C = Temp. range -20 to +70°C E = Temp. range -40 to +85°C
							Series Model
							Frequency Stability 45 = ± 50 ppm 44 = ± 25 ppm 20 = ± 20 ppm
							Series Model

Part Marking and Marking Legend:



PLE= PletronicsFF.FFF M= Frequency in MHzYYWW or YWW or YMD= Date of Manufacture (year and week, or year-month-day)All other marking is internal factory codes

Specifications such as frequency stability, supply voltage and operating temperature range, etc. are not identified from the marking. External packaging labels and packing list will correctly identify the ordered Pletronics part number.

Code	Codes for Date Code YMD																	
Code	6	7	8	9	0	Code	Α	В	С	D	Е	F	G	Н	J	Κ	L	М
Year	2016	2017	2018	2019	2020	Month	JAN	FEB	MAR	APR	MAY	JUN	JUL	AUG	SEP	OCT	NOV	DEC
0	Code		1	2	3	4	5	6	7	8	9	Α	в	С	D	E	F	G

Code	1	2	3	4	5	6	7	8	9	Α	В	С	D	Е	F	G
Day	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
Code	H	J	К	L	М	Ν	Р	R	Т	U	V	W	Х	Y	Ζ	
Day	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	



November 2018

Electrical Specification for 3.30V ±10% over the specified temperature range

Item	Min	Мах	Unit	Condition			
Frequency Range	0.8	69.9	MHz				
Frequency Accuracy "45"	-50	+50	ppm	For all supply voltages, load changes, aging for			
"44"	-25	+25		1 year, shock, vibration and temperatures			
"20"	-20	+20					
Output Waveform	CMOS						
Output High Level	90	-	%	of V _{cc} (See load circuit)			
Output Low Level	-	10	%				
Output Symmetry	45	55	%	at 50% point of V_{cc} $$ (See load circuit)			
Jitter	-	0.6	pS RMS	12 KHz to 20 MHz from the output frequency			
	-	2.5	pS RMS	10 Hz to 1 MHz from the output frequency			
Enable/Disable Internal Pull-up	50	-	Kohm	to V _{cc}			
V disable	-	30	%	of V_{cc} applied to pin 1			
V enable	70	-	%				
Output leakage V _{OUT} = V _{CC}	-10	+10	uA	Pin 1 low, device disabled			
V _{OUT} = 0V	-10	+10	uA				
Standby Current I _{cc}	-	3	uA				
Enable time	-	2.0	mS	Time for output to reach a logic state			
Disable time	-	100	nS	Time for output to reach a high Z state			
Start up time	-	3	mS	Time for output to reach specified frequency			
Operating Temperature Range	-10	+70	°C	Standard Temperature Range			
	-20	+70	°C	Extended Temperature Range "C" Option			
	-40	+85	°C	Extended Temperature Range "E" Option			
Storage Temperature Range	-55	+125	°C				




November 2018

Electrical Specification for 3.30V ±10% over the specified temperature range

Item	Тур	Мах	Unit	Condition	
Output T_{RISE} and T_{FALL}	-	5	nS	< 35 MHz	$C_{LOAD} = 15 \text{ pF}$
	-	3	nS	<u>></u> 35 MHz	10% to 90% of V _{cc} See Load Circuit
	-	8	nS	< 35 MHz	C _{LOAD} =30 pF
	-	5	nS	<u>></u> 35 MHz	10% to 90% of V _{cc} See Load Circuit
V_{cc} Supply Current (I _{cc})	-	9	mA	< 8 MHz	C _{LOAD} = 15 pF
	-	11	mA	<u>></u> 8 MHz and < 16 MHz	
	-	17	mA	<u>></u> 16 MHz and < 35 MHz	
	-	26	mA	<u>></u> 35 MHz	
	-	12	mA	< 8 MHz	C _{LOAD} = 30 pF
	-	16	mA	<u>></u> 8 MHz and < 16 MHz	
	-	22	mA	<u>></u> 16 MHz and < 35 MHz	
	-	35	mA	<u>></u> 35 MHz	


Specifications with Pad 1 E/D open circuit

Typical phase noise plot for 5 oscillators at different output frequencies.





November 2018



Reliability: Environmental Compliance


Parameter	Condition
Mechanical Shock	MIL-STD-883 Method 2002, Condition B
Vibration	MIL-STD-883 Method 2007, Condition A
Solderability	MIL-STD-883 Method 2003
Thermal Shock	MIL-STD-883 Method 1011, Condition A

ESD Rating

Model	Minimum Voltage	Conditions			
Human Body Model	1500	MIL-STD-883 Method 3115			
Charged Device Model	1000	JESD 22-C101			

Package Labeling

Label is 1" x 2.6" (25.4mm x 66.7mm) Font is Courier New Bar code is 39-Full ASCII




Label is 1" x 2.6" (25.4mm x 66.7mm) Font is Arial

RoHS Compliant 2nd LvL Interconnect Category=e4 Max Safe Temp=260C for 10s 2X Max



November 2018

Mechanical:



Contacts (pads) :

Gold 11.8 to 39.4 µinches (0.3 to 1.0 µm) over Nickel 50 to 350 µinches (1.27 to 8.89 µm)

Pad	Function	Note
1	Output Enable/Disable	When this pin is not connected the oscillator shall operate. When this pin is logic low the output will be inhibited (high impedance state.) Recommend connecting this pin to V_{cc} if the oscillator is to be always on.
2	Ground (GND)	
3	Output	
4	Supply Voltage (V _{cc})	Recommend connecting appropriate power supply bypass capacitors as close as possible.



Layout and application information

For Optimum Jitter Performance, Pletronics recommends:


- a ground plane under the device
- no large transient signals (both current and voltage) should be routed under the device
- do not layout near a large magnetic field such as a high frequency switching power supply
- do not place near piezoelectric buzzers or mechanical fans.

6



November 2018

Reflow Cycle (typical for lead free processing)




Tape and Reel: available for quantities of 250 to 1000 per reel, cut tape for < 250


Not to scale

	Constant Dimensions Table 1										
Tape Size	D0	D1 Min	E1	P0	P2	S1 Min	T Max	T1 Max			
8mm		1.0			2.0						
12mm	1.5	1.5	1.75	4.0	<u>+</u> 0.05						
16mm	+0.1 -0.0	1.5	<u>+</u> 0.1	<u>+</u> 0.1	2.0	0.6	0.6	0.1			
24mm		1.5			<u>+</u> 0.1						

	Variable Dimensions Table 2									
Tape Size	B1 Max	E2 Min	F	P1	T2 Max	W Max	Ao, Bo & Ko			
16 mm	12.1	14.25	7.5 <u>+</u> 0.1	8.0 <u>+</u> 0.1	8.0	16.3	Note 1			

Note 1: Embossed cavity to conform to EIA-481-B





		REE	REEL DIMENSIONS									
A	inches	7.0	10.0	13.0								
	mm	177.8	254.0	330.2								
в	inches	2.50	4.00	3.75								
	mm	63.5	101.6	95.3	Tape Width							
С	mm	13	width									
D	mm	16.4 +2.0 -0.0	16.4 +2.0 -0.0	16.4 +2.0 -0.0	16.0							

Reel dimensions may vary from the above



November 2018

IMPORTANT NOTICE

Pletronics Incorporated (PLE) reserves the right to make corrections, improvements, modifications and other changes to this product at anytime. PLE reserves the right to discontinue any product or service without notice. Customers are responsible for obtaining the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to PLE's terms and conditions of sale supplied at the time of order acknowledgment.

PLE warrants performance of this product to the specifications applicable at the time of sale in accordance with PLE's limited warranty. Testing and other quality control techniques are used to the extent PLE deems necessary to support this warranty. Except where mandated by specific contractual documents, testing of all parameters of each product is not necessarily performed.

PLE assumes no liability for application assistance or customer product design. Customers are responsible for their products and applications using PLE components. To minimize the risks associated with the customer products and applications, customers should provide adequate design and operating safeguards.

PLE products are not designed, intended, authorized or warranted to be suitable for use in life support applications, weapon systems or space applications, devices or systems or other critical applications that may involve potential risks of death, personal injury or severe property or environmental damage. Inclusion of PLE products in such applications is understood to be fully at the risk of the customer. Use of PLE products in such applications requires the written approval of an appropriate PLE officer. Questions concerning potential risk applications should be directed to PLE.

PLE does not warrant or represent that any license, either express or implied, is granted under any PLE patent right, copyright, artwork or other intellectual property right relating to any combination, machine or process which PLE product or services are used. Information published by PLE regarding third-party products or services does not constitute a license from PLE to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from PLE under the patents or other intellectual property of PLE.

Reproduction of information in PLE data sheets or web site is permissible only if the reproduction is without alteration and is accompanied by associated warranties, conditions, limitations and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. PLE is not responsible or liable for such altered documents.

Resale of PLE products or services with statements different from or beyond the parameters stated by PLE for that product or service voids all express and implied warranties for the associated PLE product or service and is an unfair or deceptive business practice. PLE is not responsible for any such statements.

Contacting Pletronics Inc.

Pletronics Inc. 19013 36th Ave. West Lynnwood, WA 98036-5761 USA Tel: 425-776-1880 Fax: 425-776-2760 E-mail: <u>ple-sales@pletronics.com</u> URL: www.pletronics.com

Copyright © 2018 Pletronics Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pletronics:

SM7744HEV-1.544M SM7744HEV-1.8432M SM7744HEV-10.0M SM7744HEV-12.352M SM7744HEV-14.318M SM7744HEV-14.7456M SM7744HEV-15.625M SM7744HEV-16.384M SM7744HEV-17.28M SM7744HEV-19.440M SM7744HEV-19.6608M SM7744HEV-2.048M SM7744HEV-20.0M SM7744HEV-24.0M SM7744HEV-24.576M SM7744HEV-25.000625M SM7744HEV-25.0M SM7744HEV-27.0M SM7744HEV-3.088M SM7744HEV-30.0M SM7744HEV-32.0M SM7744HEV-32.768M SM7744HEV-33.0M SM7744HEV-33.333M SM7744HEV-34.560M SM7744HEV-35.328M SM7744HEV-36.0M SM7744HEV-37.056M SM7744HEV-39.0M SM7744HEV-40.0M SM7744HEV-44.0M SM7744HEV-49.152M SM7744HEV-50.0M SM7744HEV-50.6250M SM7744HEV-53.125M SM7744HEV-55.0M SM7744HEV-6.144M SM7744HEV-60.0M SM7744HEV-62.208M SM7744HEV-62.50M SM7744HEV-65.0M SM7744HEV-66.0M SM7744HEV-8.0M SM7744HEV-8.192M SM7744HEV-9.8304M SM7745HEV-1.0M SM7745HEV-1.544M SM7745HEV-1.8432M SM7745HEV-10.0M SM7745HEV-11.0592M SM7745HEV-11.286M SM7745HEV-11.2896M SM7745HEV-12.0M SM7745HEV-12.288M SM7745HEV-14.31818M SM7745HEV-14.318M SM7745HEV-14.7456M SM7745HEV-16.0M SM7745HEV-16.384M SM7745HEV-16.666M SM7745HEV-16.667M SM7745HEV-17.024M SM7745HEV-17.734475M SM7745HEV-18.0M SM7745HEV-18.432M SM7745HEV-19.440M SM7745HEV-2.048M SM7745HEV-20.0M SM7745HEV-22.5792M SM7745HEV-23.3422M SM7745HEV-23.83775M SM7745HEV-24.0M SM7745HEV-24.576M SM7745HEV-25.0M SM7745HEV-25.31328M SM7745HEV-25.804M SM7745HEV-26.0M SM7745HEV-26.6649M SM7745HEV-26.66M SM7745HEV-27.0M SM7745HEV-28.224M SM7745HEV-3.088M SM7745HEV-3.6864M SM7745HEV-30.0M SM7745HEV-32.0M SM7745HEV-32.768M SM7745HEV-33.0M SM7745HEV-33.333M SM7745HEV-34.368M SM7745HEV-34.386M SM7745HEV-36.0M SM7745HEV-36.864M SM7745HEV-37.50M SM7745HEV-38.88M SM7745HEV-39.0625M SM7745HEV-4.096M SM7745HEV-4.0M SM7745HEV-4.9152M SM7745HEV-40.0M SM7745HEV-40.0M-SB