


**HLMP-3301, HLMP-3401, HLMP-3507, HLMP-3762,
HLMP-3862, HLMP-3962, HLMP-D401**
T-1³/₄ (5 mm) Diffused LED Lamps



Data Sheet



Description

This family of T-1³/₄ tinted, diffused LED lamps is widely used in general purpose indicator applications. Diffusants, tints, and optical design are balanced to yield superior light output and wide viewing angles. Several intensity choices are available in each color for increased design flexibility.

Device Selection Guide


| Material/Color | Part Number | Luminous Intensity, I _v (mcd) at 10mA | |
|----------------|-----------------|---|------|
| | | Min. | Max. |
| GaP HER | HLMP-3301 | 6.1 | - |
| | HLMP-3301-D00xx | 2.4 | - |
| | HLMP-3301-F00xx | 6.1 | - |
| | HLMP-3301-FG0xx | 6.1 | 15.5 |
| | HLMP-3762 | 9.7 | - |
| | HLMP-3762-G00xx | 9.7 | - |
| GaP Yellow | HLMP-3401 | 6.5 | - |
| | HLMP-3401-E00xx | 6.5 | - |
| | HLMP-3862 | 10.3 | - |
| GaP Orange | HLMP-D401 | 6.1 | - |
| | HLMP-D401-EF0xx | 3.8 | 9.7 |
| GaP Green | HLMP-3507 | 4.7 | - |
| | HLMP-3507-D00xx | 4.7 | - |
| | HLMP-3507-EF0xx | 7.6 | 19.1 |
| | HLMP-3962 | 12.0 | - |
| | HLMP-3962-F00xx | 12.0 | - |

Features


- High intensity
- Choice of 4 bright colors
 - High Efficiency Red
 - Orange
 - Yellow
 - High Performance Green
- Popular T-1³/₄ diameter package
- Selected minimum intensities
- Wide viewing angle
- General purpose leads
- Reliable and rugged
- Available on tape and reel

Part Numbering System

HLMP - x x xx - x x x xx



Package Dimensions



Notes:

1. All dimensions are in mm (inches).
2. An epoxy meniscus may extend about 1 mm (0.040") down the leads.
3. For PCB hole recommendations, see the Precautions section.

Optical/Electrical Characteristics at $T_A = 25^\circ\text{C}$

| Symbol | Parameter | Color | Min. | Typ. | Max. | Units | Test Condition |
|-------------------------|--|---------------------|------|------|------|-----------------------|------------------------------------|
| $2\theta^{1/2}$ | Included Angle Between Half Luminous Intensity Points | High Efficiency Red | | 60 | | Deg. | $I_F = 10\text{ mA}$ See Note 1 |
| | | Orange | | 60 | | | |
| | | Yellow | | 60 | | | |
| | | Green | | 60 | | | |
| λ_{PEAK} | Peak Wavelength | High Efficiency Red | | 635 | | nm | Measurement at Peak |
| | | Orange | | 600 | | | |
| | | Yellow | | 583 | | | |
| | | Green | | 565 | | | |
| $\Delta\lambda_{1/2}$ | Spectral Line Halfwidth | HER/Orange | | 40 | | nm | |
| | | Yellow | | 36 | | | |
| | | Green | | 28 | | | |
| λ_d | Dominant Wavelength | High Efficiency Red | | 626 | | nm | See Note 2 |
| | | Orange | | 602 | | | |
| | | Yellow | | 585 | | | |
| | | Green | | 569 | | | |
| τ_s | Speed of Response | High Efficiency Red | | 90 | | ns | |
| | | Orange | | 280 | | | |
| | | Yellow | | 90 | | | |
| | | Green | | 500 | | | |
| C | Capacitance | High Efficiency Red | | 11 | | pF | $V_F = 0;$ $f = 1\text{ MHz}$ |
| | | Orange | | 4 | | | |
| | | Yellow | | 15 | | | |
| | | Green | | 18 | | | |
| $R\theta_{J-PIN}$ | Thermal Resistance | All | | 260 | | $^\circ\text{C/W}$ | Junction to Cathode Lead |
| V_F | Forward Voltage | HER/Orange | | 1.9 | 2.4 | V | $I_F = 10\text{ mA}$ |
| | | Yellow | | 2.0 | 2.4 | | |
| | | Green | | 2.1 | 2.7 | | |
| V_R | Reverse Breakdown Voltage | All | 5.0 | | | V | $I_R = 100\ \mu\text{A}$ |
| η_V | Luminous Efficacy | High Efficiency Red | – | 145 | | <u>lumens</u> Watt | See Note 3 |
| | | Orange | | 380 | | | |
| | | Yellow | – | 500 | | | |
| | | Green | | 595 | | | |

Notes:

- $\theta^{1/2}$ is the off-axis angle at which the luminous intensity is half the axial luminous intensity.
- The dominant wavelength, λ_d , is derived from the CIE chromaticity diagram and represents the single wavelength which defines the color of the device.
- Radiant intensity, I_e , in Watts/steradian, may be found from the equation $I_e = I_v/\eta_V$, where I_v is the luminous intensity in candelas and η_V is the luminous efficacy in lumens/Watt.

Absolute Maximum Ratings at $T_A = 25^\circ\text{C}$

| Parameter | HER/Orange | Yellow | Green/ Emerald Green | Units |
|--|-------------|-------------|-------------------------|------------------|
| Peak Forward Current | 90 | 60 | 90 | mA |
| Average Forward Current ^[1] | 25 | 20 | 25 | mA |
| DC Current ^[2] | 30 | 20 | 30 | mA |
| Power Dissipation ^[3] | 135 | 85 | 135 | mW |
| Reverse Voltage ($I_R = 100 \mu\text{A}$) | 5 | 5 | 5 | V |
| Transient Forward Current ^[4] (10 μsec Pulse) | 500 | 500 | 500 | mA |
| LED Junction Temperature | 110 | 110 | 110 | $^\circ\text{C}$ |
| Operating Temperature Range | -40 to +100 | -40 to +100 | -20 to +100 | $^\circ\text{C}$ |
| Storage Temperature Range | -40 to +100 | -40 to +100 | -40 to +100 | $^\circ\text{C}$ |

Notes:

- See Figure 5 (Red/Orange), 10 (Yellow), or 15 (Green) to establish pulsed operating conditions.
- For Red, Orange and Green series derate linearly from 50°C at $0.5 \text{ mA}/^\circ\text{C}$. For Yellow series derate linearly from 50°C at $0.2 \text{ mA}/^\circ\text{C}$.
- $1.8 \text{ mW}/^\circ\text{C}$. For Yellow series derate power linearly from 50°C at $1.6 \text{ mW}/^\circ\text{C}$.
- The transient peak current is the maximum non-recurring peak current that can be applied to the device without damaging the LED die and wirebond. It is not recommended that the device be operated at peak currents beyond the peak forward current listed in the Absolute Maximum Ratings.




Figure 1. Relative intensity vs. wavelength

T-1³/₄ High Efficiency Red, Orange Diffused Lamps




Figure 2. Forward current vs. forward voltage characteristics




Figure 3. Relative luminous intensity vs. DC forward current




Figure 4. Relative efficiency (luminous intensity per unit current) vs. peak LED current




Figure 5. Maximum tolerable peak current vs. pulse duration. (I_{DC} MAX as per MAX ratings)




Figure 6. Relative luminous intensity vs. angular displacement

T-1³/₄ Yellow Diffused Lamps




Figure 7. Forward current vs. forward voltage characteristics




Figure 8. Relative luminous intensity vs. forward current




Figure 9. Relative efficiency (luminous intensity per unit current) vs. peak current




Figure 10. Maximum tolerable peak current vs. pulse duration. (I_{DC} MAX as per MAX ratings)




Figure 11. Relative luminous intensity vs. angular displacement

T-1³/₄ Green/Emerald Green Diffused Lamps




Figure 12. Forward current vs. forward voltage characteristics




Figure 13. Relative luminous intensity vs. DC forward current




Figure 14. Relative efficiency (luminous intensity per unit current) vs. peak LED current




Figure 15. Maximum tolerable peak current vs. pulse duration. (I_{DC} MAX as per MAX ratings)




Figure 16. Relative luminous intensity vs. angular displacement

Intensity Bin Limits

| Color | Bin | Intensity Range (mcd) | |
|------------|---------|-----------------------|---------|
| | | Min. | Max. |
| Red/Orange | D | 2.4 | 3.8 |
| | E | 3.8 | 6.1 |
| | F | 6.1 | 9.7 |
| | G | 9.7 | 15.5 |
| | H | 15.5 | 24.8 |
| | I | 24.8 | 39.6 |
| | J | 39.6 | 63.4 |
| | K | 63.4 | 101.5 |
| | L | 101.5 | 162.4 |
| | M | 162.4 | 234.6 |
| | N | 234.6 | 340.0 |
| | O | 340.0 | 540.0 |
| | P | 540.0 | 850.0 |
| | Q | 850.0 | 1200.0 |
| | R | 1200.0 | 1700.0 |
| | S | 1700.0 | 2400.0 |
| | T | 2400.0 | 3400.0 |
| | U | 3400.0 | 4900.0 |
| | V | 4900.0 | 7100.0 |
| | W | 7100.0 | 10200.0 |
| X | 10200.0 | 14800.0 | |
| Y | 14800.0 | 21400.0 | |
| Z | 21400.0 | 30900.0 | |
| Yellow | E | 6.5 | 10.3 |
| | F | 10.3 | 16.6 |
| | G | 16.6 | 26.5 |
| | H | 26.5 | 42.3 |
| | I | 42.3 | 67.7 |
| | J | 67.7 | 108.2 |
| | K | 108.2 | 173.2 |
| | L | 173.2 | 250.0 |
| | M | 250.0 | 360.0 |
| | N | 360.0 | 510.0 |
| | O | 510.0 | 800.0 |
| | P | 800.0 | 1250.0 |
| | Q | 1250.0 | 1800.0 |
| | R | 1800.0 | 2900.0 |
| S | 2900.0 | 4700.0 | |
| T | 4700.0 | 7200.0 | |
| U | 7200.0 | 11700.0 | |
| V | 11700.0 | 18000.0 | |
| W | 18000.0 | 27000.0 | |

Intensity Bin Limits, continued

| Color | Bin | Intensity Range (mcd) | |
|-------|---------|-----------------------|---------|
| | | Min. | Max. |
| Green | D | 4.7 | 7.6 |
| | E | 7.6 | 12.0 |
| | F | 12.0 | 19.1 |
| | G | 19.1 | 30.7 |
| | H | 30.7 | 49.1 |
| | I | 49.1 | 78.5 |
| | J | 78.5 | 125.7 |
| | K | 125.7 | 201.1 |
| | L | 201.1 | 289.0 |
| | M | 289.0 | 417.0 |
| | N | 417.0 | 680.0 |
| | O | 680.0 | 1100.0 |
| | P | 1100.0 | 1800.0 |
| | Q | 1800.0 | 2700.0 |
| | R | 2700.0 | 4300.0 |
| | S | 4300.0 | 6800.0 |
| | T | 6800.0 | 10800.0 |
| U | 10800.0 | 16000.0 | |
| V | 16000.0 | 25000.0 | |
| W | 25000.0 | 40000.0 | |

Maximum tolerance for each bin limit is $\pm 18\%$.

Color Categories

| Color | Category # | Lambda (nm) | |
|--------|------------|-------------|-------|
| | | Min. | Max. |
| Green | 6 | 561.5 | 564.5 |
| | 5 | 564.5 | 567.5 |
| | 4 | 567.5 | 570.5 |
| | 3 | 570.5 | 573.5 |
| | 2 | 573.5 | 576.5 |
| Yellow | 1 | 582.0 | 584.5 |
| | 3 | 584.5 | 587.0 |
| | 2 | 587.0 | 589.5 |
| | 4 | 589.5 | 592.0 |
| | 5 | 592.0 | 593.0 |
| Orange | 1 | 597.0 | 599.5 |
| | 2 | 599.5 | 602.0 |
| | 3 | 602.0 | 604.5 |
| | 4 | 604.5 | 607.5 |
| | 5 | 607.5 | 610.5 |
| | 6 | 610.5 | 613.5 |
| | 7 | 613.5 | 616.5 |
| | 8 | 616.5 | 619.5 |

Tolerance for each bin limit is ± 0.5 nm.

Mechanical Option Matrix

| Mechanical Option Code | Definition |
|------------------------|---|
| 00 | Bulk Packaging, minimum increment 500 pcs/bag |
| 01 | Tape & Reel, crimped leads, minimum increment 1300 pcs/bag |
| 02 | Tape & Reel, straight leads, minimum increment 1300 pcs/bag |
| B1 | Right Angle Housing, uneven leads, minimum increment 500 pcs/bag |
| B2 | Right Angle Housing, even leads, minimum increment 500 pcs/bag |
| DD | Ammo Pack, straight leads with minimum increment 2K/pack |
| R4 | Tape & Reel, straight leads, counter clockwise, anode lead leaving the reel first |

Note:

All categories are established for classification of products. Products may not be available in all categories. Please contact your local Avago representative for further clarification/information.

Precautions

Lead Forming

- The leads of an LED lamp may be preformed or cut to length prior to insertion and soldering into PC board.
- If lead forming is required before soldering, care must be taken to avoid any excessive mechanical stress induced to LED package. Otherwise, cut the leads of LED to length after soldering process at room temperature. The solder joint formed will absorb the mechanical stress of the lead cutting from traveling to the LED chip die attach and wirebond.
- It is recommended that tooling made to precisely form and cut the leads to length rather than rely upon hand operation.

Soldering Conditions

- Care must be taken during PCB assembly and soldering process to prevent damage to LED component.
- The closest LED is allowed to solder on board is 1.59 mm below the body (encapsulant epoxy) for those parts without standoff.
- Recommended soldering conditions:

| | Wave Soldering | Manual Solder Dipping |
|----------------------|----------------|-----------------------|
| Pre-heat Temperature | 105 °C Max. | – |
| Pre-heat Time | 30 sec Max. | – |
| Peak Temperature | 250 °C Max. | 260 °C Max. |
| Dwell Time | 3 sec Max. | 5 sec Max. |

- Wave soldering parameter must be set and maintained according to recommended temperature and dwell time in the solder wave. Customer is advised to periodically check on the soldering profile to ensure the soldering profile used is always conforming to recommended soldering condition.
- If necessary, use fixture to hold the LED component in proper orientation with respect to the PCB during soldering process.
- Proper handling is imperative to avoid excessive thermal stresses to LED components when heated. Therefore, the soldered PCB must be allowed to cool to room temperature, 25°C, before handling.
- Special attention must be given to board fabrication, solder masking, surface plating and lead holes size and component orientation to assure solderability.
- Recommended PC board plated through hole sizes for LED component leads:

| | LED Component Lead Size | Diagonal | Plated Through-Hole Diameter |
|------------------------------|---------------------------------------|------------------------|--|
| Lead size (typ.) | 0.45 × 0.45 mm (0.018 × 0.018 in.) | 0.636 mm (0.025 in) | 0.98 to 1.08 mm (0.039 to 0.043 in) |
| Dambar shear-off area (max.) | 0.65 mm (0.026 in) | 0.919 mm (0.036 in) | |
| Lead size (typ.) | 0.50 × 0.50 mm (0.020 × 0.020 in.) | 0.707 mm (0.028 in) | 1.05 to 1.15 mm (0.041 to 0.045 in) |
| Dambar shear-off area (max.) | 0.70 mm (0.028 in) | 0.99 mm (0.039 in) | |

Note: Refer to application note AN1027 for more information on soldering LED components.




Figure 17. Recommended wave soldering profile

For product information and a complete list of distributors, please go to our website: www.avagotech.com

Avago, Avago Technologies, and the A logo are trademarks of Avago Technologies in the United States and other countries. Data subject to change. Copyright © 2005-2015 Avago Technologies. All rights reserved. Obsoletes 5989-4258EN AV02-1558EN - March 30, 2015

AVAGO
TECHNOLOGIES

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Broadcom Limited:

[HLMP-3301](#) [HLMP-3301-D0000](#) [HLMP-3301-D0001](#) [HLMP-3301-D0002](#) [HLMP-3301-D00B2](#) [HLMP-3301-F0001](#)
[HLMP-3301-F0002](#) [HLMP-3301-F00B2](#) [HLMP-3301-F00DD](#) [HLMP-3301-F00R4](#) [HLMP-3401](#) [HLMP-3401-E0002](#)
[HLMP-3762](#) [HLMP-3762-G00B2](#) [HLMP-3862](#) [HLMP-3962](#) [HLMP-3962-F0002](#) [HLMP-3962-F00B2](#) [HLMP-D401](#)
[HLMP-D401-EF0FH](#)