



Fuse-holder, LV, 32 A, AC 690 V, 10 x 38 mm, 1P, UL, IEC, indicating, DIN rail mount

Catalog No. CHM1DIU

Delivery program

Product range			Fuse accessory
Basic function			Fuse-holder
Field of application			low voltage
Rated current	I	A	32
Rated voltage			AC 690 V
Size			10 x 38 mm
Status indicator			with indicator
Description			DIN rail mounting Modular colour-coded Rated for use with 75°C or 90°C wire, fine stranded wire, spade terminals and with comb-bus bars. Use any higher temperature rated wire with appropriate derating.
Number of poles			1P
usable for size/applications			for cylindrical fuse-links for midget fuses
Standard/Approval			UL IEC
Standards/Regulations			IEC cULus CCC CSA UR

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Holder for cylindrical fuse (EC002705)		
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Holder for cylindrical fuse (ecl@ss10.0.1-27-14-21-21 [ADI305007])		
Nominal voltage	V	690
Mounting method		DIN rail
For fuse size		10x38 mm
Number of poles		1
Concurrently switching N-neutral		No
Lockable		Yes
Optical defect indication		Yes
Width in number of modular spacings		1
Built-in depth	mm	45.1
Degree of protection (IP)		Other

Additional product information (links)

Product datasheet (PDF)	http://www1.cooperbusmann.com/pdf/84e185ef-62d9-48ca-b609-a65353c730ce.pdf
-------------------------	---