## Amphenol® RF



225-101P-52S





225-100J-52S

### Overview

Amphenol RF's line of 2.2/5 connectors are a compact version of the previously released 4.3/10 connector series, with a 53% smaller footprint. This connector series is lightweight and can accommodate thick, low loss cables up to a half inch. The robust design makes these connectors ideal for both indoor and outdoor applications.

The 2.2/5 connector series is designed to meet the needs of applications which require low PIM in order to avoid interference in network quality during high speed data transmission. It offers flexibility in installation with the ability to blind mate.

#### **Features and Benefits**

- · Excellent low PIM performance up to 20 GHz
- · Lightweight, compact design
- · Optimized for 1/4, 3/8 and 1/2 inch corrugated cables
- · Ideal for outdoor applications

## **Applications**

- · Small Cells
- In-Building Architecture
- Mobile Networks
- MIMO Antennas
- Distributed Antenna Systems (DAS)
- Test & Measurement
- Low Power Base Stations

## **Amphenol RF**

Four Old Newtown Road Danbury, CT 06810

## 2.2/5 Product Series

### **Compact, Low PIM Interface**

## **Ordering Information**

#### **Cable Mount Connectors**


Part Number	Description
225-108J-52S	Bulkhead Jack for RG-402
225-109J-52S	Bulkhead Jack for RG-405
225-104J-52S	Jack for RG-402
225-105J-52S	Jack for RG-405
225-100J-52S	4-Hole Flange Jack for RG-402
225-102J-52S	4-Hole Flange Jack for RG-405
225-106P-52A	Right-Angle Plug for RG-402
225-107P-52A	Right-Angle Plug for RG-405
225-101P-52S	Straight Plug for RG-402
225-103P-52S	Straight Plug for RG-405

#### **Adapters**

Part Number	Description
AD-716P225J-1	2.2/5 Jack Adapter to 7/16 Plug
AD-4310J225P-1	2.2/5 Plug to 4.3/10 Jack Adapter
AD-NJ225P-1	2.2/5 Plug to Type-N Jack Adapter
AD-716J225P-1	2.2/5 Plug to 7/16 Jack Adapter

## **Excellent PIM** Performance

<-166 dBc



# **Amphenol® RF**

## **Technical Specifications**

#### **Electrical**

Impedance		50 Ω
Frequency Range		DC - 20 GHz
Dielectric Withstanding Vo	oltage	1500V Min
PIM (Passive Intermodulation)		- 166 dBc @ 2 x 20 W
Insertion Loss (dB)	DC - 4 GHz	33 dB
	4 - 6 GHz	30 dB
Insulation Resistance		3000 MΩ Min
Voltage Proof		1.5 kV @ 50 Hz

#### Mechanical

Mating Cycles	100 Min
Power Handling	150 W (2 GHz) @ 85°C
Recommended Torque (Screw Type)	3 Nm

#### Environmental

Temperature Range	- 65°C to +165°C

#### Materials

Body	Brass, White Bronze Plating
Insulator	PTFE, Natural
Inner Contact	Beryllium Copper, Silver Plating
Outer Contact	Beryllium Copper, White Bronze Plating

## **Size Comparison**

2.2/5 Series 4.3/10 Series 7/16 Series

