


Tactile Switch

B3F

Through-hole-mounting Switches in a Wide Range of Models: 6×6 mm, 12×12 mm, Side-operated Models, Gold-plated Contacts, and Radial Tape

- Extended mechanical/electrical durability: 10 x 10⁶ operations for 12 x 12 mm type and 1 x 10⁶ operations for the 6 x 6 mm type
- Taped radial type, vertical type and high force types are available.
- Gold plated models available for increased contact reliability, resistance to corrosive gas and insulation failure prevention for ion migration in harsh environments
- B32-series Key Tops mount to models with projected plungers.



■ List of Models

6 × 6 mm Models

Туре	Contact	Plunger	ger Height	Operating	Plunger		Bags			
	material			force (OF)	color	Without ground terminal	Minimum packing unit	With ground terminal	Minimum packing unit	
Standard:	Silver	Flat type	4.3 mm	0.98 N {100 gf}	lvory	B3F-1000		B3F-1100		
B3F-1000 Series	plated	r lat type		1.47 N {150 gf}	Yellow	B3F-1002		B3F-1102	-	
Selles				2.55 N {260 gf}	Orange	B3F-1005		B3F-1105		
				4.9 N {500 gf}	Red	B3F-1006				
			5.0 mm	0.98 N {100 gf}	Black	B3F-1020		B3F-1120		
		B		1.47 N {150 gf}	Gray	B3F-1022		B3F-1122		
		5.0 mm (7.5-mm pitch) 7.0 mm		2.55 N {260 gf}	Pink	B3F-1025		B3F-1125		
				4.9 N {500 gf}	Blue	B3F-1026				
			0.98 N {100 gf}	Black		100 pcs	B3F-1110	100 pcs		
			0.98 N {100 gf}	Black	B3F-1060					
				1.47 N {150 gf}	Yellow	B3F-1062				
			9.5 mm	0.98 N {100 gf}	Black	B3F-1070				
				1.47 N {150 gf}	Yellow	B3F-1072	1		1	
				2.55 N {260 gf}	Orange	B3F-1075				
		Projected type	7.3 mm	0.98 N {100 gf}	lvory	B3F-1050		B3F-1150		
				1.47 N {150 gf}	Yellow	B3F-1052		B3F-1152		
				2.55 N {260 gf}	Orange	B3F-1055		B3F-1155		
		8 R. A		4.9 N {500 gf}	Red	B3F-1056				

Туре	Contact material	Plunger	Height	Operating	Plunger		Ва	ıgs	
				force (OF)	color	Without ground terminal	Minimum packing unit	With ground terminal	Minimum packing unit
Side-	Silver plated	Flat type	/pe 3.15 mm	0.98 N {100 gf}	lvory			B3F-3100	-
operated: B3F-3000				1.47 N {150 gf}	Yellow			B3F-3102	
Series		1000		2.55 N {260 gf}	Orange			B3F-3105	
			3.85 mm	0.98 N {100 gf}	Black			B3F-3120	
		8 950		1.47 N {150 gf}	Gray			B3F-3122	
				2.55 N {260 gf}	Pink			B3F-3125	
		Projected type	6.15 mm	0.98 N {100 gf}	Ivory			B3F-3150	
				1.47 N {150 gf}	Yellow			B3F-3152	
		3 100		2.55 N {260 gf}	Orange			B3F-3155	
High-	Gold plated	Flat type	4.3 mm	1.76 N {180 gf}	Yellow	B3F-1002-G	100 pcs	B3F-1102-G	100 pcs
reliability gold-plated:			5.0 mm		Gray	B3F-1022-G		B3F-1122-G	
B3F-1000-G Series			7.0 mm		Yellow	B3F-1062-G (see note)			
		A	9.5 mm		Yellow	B3F-1072-G (see note)			
Side- operated with highly reliable gold-plated: B3F-3000-G Series		Projected type	7.3 mm		Yellow	B3F-1052-G			
		Flat type	3.85 mm		Gray			B3F-3122-G (see note)	

Note: Bulk Packaged, 100 Switches per bag. Order in multiples of the package quantity.

$12 \times 12 \text{ mm Models}$

Туре	Contact	Plunger	Height	Operating force (OF)	Plunger color	Bags				
	material	(or LED color)				Without ground terminal	Minimum packing unit	With ground terminal	Minimum packing unit	
Standard:	Silver	Flat type	4.3 mm	1.27 N {130 gf}	lvory	B3F-4000		B3F-4100		
B3F-4000	plated			2.55 N {260 gf}	Yellow	B3F-4005		B3F-4105	100 pcs	
Series		Projected type	7.3 mm	1.27 N {130 gf}	lvory	B3F-4050		B3F-4150		
				2.55 N {260 gf}	Yellow	B3F-4055	100 pcs	B3F-4155		
Long durability:	Silver	Flat type	4.3 mm	n 1.27 N {130 gf}	Blue	B3F-5000		B3F-5100		
B3F-5000 Se- ries	plated	Projected type	7.3 mm		Blue	B3F-5050		B3F-5150		
High reliability gold-plated:	Gold plated	Flat type	4.3 mm	1.27 N {130 gf}	Blue	B3F-5001		B3F-5101		
B3F-5001 Series		Projected type	7.3 mm		Blue	B3F-5051		B3F-5151		

Note: Bulk Packaged, 100 switches per bag. Order in multiples of the package quantity.

6 × 6 mm Radial Models (Taping Specifications)

Туре	Contact	Plunger	Height	Operating force (OF)	Plunger color	Taped Radial			
	material					Without ground terminal	Minimum packing unit	With ground terminal	Minimum packing unit
Taped Radial: B3F-6000 Series	Silver	Silver plated Flat type	4.3 mm	0.98 N {100 gf}	lvory	B3F-6000	- 1,000 pcs	B3F-6100	1,000 pcs
	plated			1.47 N {150 gf}	Yellow	B3F-6002		B3F-6102	
				0.98 N {100 gf}	Black	B3F-6020		B3F-6120	
				1.47 N {150 gf}	Gray	B3F-6022		B3F-6122	
		Projected type 7.3 mm	0.98 N {100 gf}	lvory	B3F-6050		B3F-6150		
				1.47 N {150 gf}	Yellow	B3F-6052		B3F-6152	

Note: The switches are tape packaged in units of 1,000 per package. Order in multiples of the package size. Switches are not sold individually.

■ Ratings/Characteristics

Rating (resistive load)	1 to 50 mA, 3 to 24 VDC (B3F-G: 100 μA to 50 mA, 3 to 24 VDC)				
Minimum applicable load (reference value)	10 μA at 1 VDC (resistive load)				
Ambient operating temperature	-25°C to +70°C at 60%RH max. (with no icing or condensation)				
Ambient operating humidity	5% to 85% (at +5 to +35°C)				
Contact form	SPST-NO				
Contact resistance (initial value)	100 m $Ω$ max.				
Insulation resistance	100 M Ω min. (at 250 VDC with insulation tester)				
Dielectric strength	500 VAC, 50/60 Hz for 1 min				
Bounce time	5 ms max.				
Vibration resistance	Malfunction: 10 to 55 Hz, 1.5 mm double amplitude				
Shock resistance	Destruction: 1,000 m/s ² {approx. 100G} max. Malfunction: 100 m/s ² {approx. 10G} max.				
Durability	B3F-1000, B3F-3000, B3F-6000: 1,000,000 operations min (OF: 0.98 N {100 gf}) (B3F-1070: 500,000 operations min) 300,000 operations min (OF: 1.47 N {150 gf}) 100,000 operations min (OF: 2.55 N {260 gf}) 50,000 operations min (OF: 4.9 N {500 gf}) B3F-4000: 3,000,000 operations min (OF: 1.27 N {130 gf}) 1,000,000 operations min (OF: 2.55 N {260 gf}) B3F-5000/5001: 10,000,000 operations min. B3F-G: 300,000 operations min.				
Weight	6×6 mm models: approx. 0.25 g 12×12 mm models (standard types): approx. 0.85 g Radial models: approx. 0.25 g				
Degree of protection	IEC IP00				
Washing	Not possible				

■ Operating Characteristics

6×6 mm Models

		B3F-G				
Operating force (OF)	0.98 N	1.47 N	2.55 N	4.9 N	1.76 N	
Item	B3F-1□□0 B3F-3□□0 B3F-6□□0	B3F-1□□2 B3F-3□□2 B3F-6□□2	B3F-1□□5 B3F-3□□5	B3F-10□6	B3F-1□□2-G B3F-3□□2-G	
Operating force (OF)	0.98±0.29 N {100±30 gf}	1.47±0.49 N {150±50 gf}	2.55±0.69 N {260±70 gf}	4.9±1.47 N {500±150 gf}	1.76±0.49 N {180±50 gf}	
Releasing force (RF)	0.2 N {20 gf} min.	0.49 N {50 gf}min.	0.49 N {50 gf}min.	0.7 N {70 gf} min.	0.49 N {50 gf}min.	
Pretravel (PT)	0.25 ^{+0.2} / _{-0.1} mm				0.25 ^{+0.2} / _{-0.1} mm	

$12 \times 12 \text{ mm Models}$

	B3F-4000, B3F-5000, B3F-5001				
Operating force (OF)	1.27 N	2.55 N			
Item	B3F-4□□0 B3F-5□□0 B3F-5□□1	B3F-4□□5			
Operating force (OF)	1.27±0.49 N {130±50 gf}	2.55±0.69 N {260±70 gf}			
Releasing force (RF)	0.29 N {30 gf} min.	0.49 N {50 gf} min.			
Pretravel (PT)	0.3 ^{+0.2} / _{-0.1} mm				

■ **Dimensions** (Unit: mm)


The numbers used for terminals in the following graphics are indicated in the "Bottom View" diagram below. In this diagram, the Switch is rotated so that the terminals are on the right and left-hand sides, and the OMRON logo appears the right way up. (Except Side-operated and Radial Models)



$6 \times 6 \text{ mm Models}$

Standard, Flat Plunger Type (without Ground Terminal)

B3F-1000, B3F-1002, B3F-1005, B3F-1006 B3F-1020 (See note.), B3F-1022 (See note.), B3F-1025 (See note.), B3F-1026 (See note.) B3F-1002-G, B3F-1022-G (See note.)




Note: The height of B3F-1020, B3F-1022, B3F-1025, and B3F-1026 is 5±0.2 mm

Standard, Flat Plunger Type (with Ground Terminal)


Standard, Flat Plunger Type


(without Ground Terminal)

B3F-1100, B3F-1102, B3F-1105 B3F-1120 (See note.), B3F-1122 (See note.) B3F-1125 (See note.) B3F-1102-G, B3F-1122-G (See note.)



Standard, Flat Plunger Type







Note: Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions. No terminal numbers are indicated on the Switches.

Standard, Flat Plunger Type (without Ground Terminal)

B3F-1070, B3F-1072, B3F-1075, B3F-1072-G



Standard, Projected Plunger Type (without Ground Terminal)



Standard, Projected Plunger Type (with Ground Terminal)

B3F-1150, B3F-1152, B3F-1155




Side-operated, Projected Plunger Type

6.15+0.2

B3F-3150, B3F-3152, B3F-3155


8.7



Side-operated, Flat Plunger Type (Height: 3.85 mm) B3F-3120, B3F-3122, B3F-3125, B3F-3122-G

3.85±0.2

8 7



Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions. No terminal numbers are indicated on the Switches.

Two, 1.5 ±0.05 dia

2.5±0.

$12 \times 12 \text{ mm Models}$


Standard, Long-durability, and High-reliability Models Flat Plunger Type (without Ground Terminal)

B3F-4000, B3F-4005, B3F-5000, B3F-5001



PCB Processing Dimensions (Reference Only) (Top View) (PCB thickness, t=1.6)





3.5 3.5 1.6 dia -0.3 12 5+0.5 13.8±0.5

Terminal Arrangement/ Internal Connections (Top View)





Standard, Long-durability, and High-reliability Models Flat Plunger Type (with Ground Terminal)


B3F-4100, B3F-4105, B3F-5100, B3F-5101



PCB Processing Dimensions (Reference Only) (Top View) (PCB thickness, t=1.6)








Standard, Long-durability, and High-reliability Models **Projected Plunger Type** (without Ground Terminal)

B3F-4050, B3F-4055, B3F-5050, B3F-5051



PCB Processing Dimensions (Reference Only) (Top View) (PCB thickness, t=1.6)








B3F-4150, B3F-4155, B3F-5150, B3F-5151

PCB Processing Dimensions (Reference Only) (Top View) (PCB thickness, t=1.6)




Note: Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions.


Note: The numbers used for terminals in the following graphics are indicated in the "Bottom View" diagram below. In this diagram, the Switch is rotated so that the terminals are on the right and left-hand sides, and the OMRON logo appears the right way up.



$6~\text{mm} \times 6~\text{mm}$ Radial Types (Taping Specifications): Sold in Units of 1,000 Switches



Note: Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions. No terminal numbers are indicated on the Switches.



Note: Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions. No terminal numbers are indicated on the Switches.

■ Key Tops

B32-series Key Tops are available for projected plungers. Refer to the Datasheet of B32 for details.

■ Precautions

Be sure to read the safety precautions common to all Tactile Switches for correct use.

Please check each region's Terms & Conditions by region website.

OMRON Corporation

Device & Module Solutions Company

Regional Contact

Americas

https://components.omron.com/us

Asia-Pacific

https://components.omron.com/ap

Korea

https://components.omron.com/kr

Europe

https://components.omron.com/eu

China

https://components.omron.com.cn

Japan

https://components.omron.com/jp

© OMRON Corporation 2007-2022 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice.

Cat. No. A070-E1-09 1122 (0207)