


Metal Oxide Film Resistors

Flame-Proof Type


Normal & Miniature Style [RSF Series]



INTRODUCTION

The RSF Series Metal Oxide Film Flame-Proof Resistors offer excellent performance in applications where stability and uniformity of characteristics are desired. They provide lower cost alternatives to Carbon Composition Resistors and General Purpose Metal Films. Metal Oxides also can replace many low power General Purpose wirewound applications, saving both money and time, with shorter delivery cycles. The normal style & 'RSF-WV' style of RSF series are coated with layers of gray flame-proof lacquer, and the miniature style except 'RSF-WV' style are coated with layers of pink colors flame-proof lacquer.

DIMENSIONS



Note: RSF1WS (for MB Type) $\phi d = 0.8 \pm 0.05 \text{mm}$
RSF3WV, RSF4WV: Marking Printed


FEATURES

Power Rating	1/4W, 1/2W, 1W, 2W, 3W, 5W
Resistance Tolerance	$\pm 2\%$, $\pm 5\%$
T.C.R.	$\pm 300 \text{ppm}/^\circ\text{C}$
Flameproof Multi-layer Coating Meets	UL-94V-0
Flameproof Feature Meets Overload Test	UL-1412

DERATING CURVE

For resistors operated in ambient temperatures above 70°C , power rating must be derated in accordance with the curve below.

Rated Load (%)



Ambient Temperature ($^\circ\text{C}$)

Unit: mm

STYLE		DIMENSION			
Normal	Miniature	L	ϕD	H	ϕd
RSF-25	RSF50S / RSF1WV	6.3 ± 0.5	2.4 ± 0.2	28 ± 2.0	0.55 ± 0.05
RSF-50	RSF1WS	9.0 ± 0.5	3.3 ± 0.3	26 ± 2.0	0.55 ± 0.05
RSF100	RSF2WS / RSF2WV	11.5 ± 1.0	4.5 ± 0.5	35 ± 2.0	0.8 ± 0.05
RSF200	RSF3WS	15.5 ± 1.0	5.0 ± 0.5	33 ± 2.0	0.8 ± 0.05
-	RSF3WV	$16.5 \pm 0/-1.5$	$6.0 \pm 0/-0.5$	33 ± 2.0	0.8 ± 0.05
RSF3WM	RSF5SS	17.5 ± 1.0	6.5 ± 1.0	32 ± 2.0	0.8 ± 0.05
-	RSF4WV	$20 \pm 0/-1$	$9.0 \pm 0/-0.5$	31 ± 2.0	0.8 ± 0.05
RSF300	RSF5WS	24.5 ± 1.0	8.5 ± 1.0	38 ± 2.0	0.8 ± 0.05
RSF500	-	24.5 ± 1.0	8.5 ± 1.0	38 ± 2.0	0.8 ± 0.05

ELECTRICAL CHARACTERISTICS

NORMAL STYLE

STYLE	RSF-25	RSF-50	RSF100	RSF200	RSF3WM	RSF300	RSF500
Power Rating at 70°C	1/4W	1/2W	1W	2W	3W		5W
Maximum Working Voltage	200V	250V	350V		450V	500V	750V
Maximum Overload Voltage	300V	400V	600V		700V	800V	1,000V
Voltage Proof on Insulation	250V	350V	500V				
Resistance Range	1Ω - 1MΩ & 0Ω for E24 series value						
Operating Temp. Range	-55°C to +235°C						
Temperature Coefficient	±300ppm/°C						

MINIATURE STYLE

STYLE	RSF50S	RSFI1WV	RSFI1WS	RSF2WS	RSF2WV	RSF3WS	RSF3WV	RSF5SS	RSF4WV	RSF5WS
Power Rating at 70°C	1/2W	1W		2W		3W		5W	4W	5W
Maximum Working Voltage	250V	500V	300V	350V	500V	350V	750V	500V	750V	700V
Maximum Overload Voltage	400V	500V		600V			750V	800V		900V
Voltage Proof on Insulation	350V	500V	400V	500V						
Resistance Range	1Ω - 1MΩ & 0Ω for E24 series value									
Operating Temp. Range	-55°C to +235°C									
Temperature Coefficient	±300ppm/°C									

Note: Special value is available on request

ENVIRONMENTAL CHARACTERISTICS

PERFORMANCE TEST	TEST METHOD		APPRAISE
Short Time Overload	IEC 60115-1 4.13	2.5 times RCWV for 5 Sec.	±1.0%+0.05Ω for normal style ±2.0%+0.05Ω for miniature style
Voltage Proof on Insulation	IEC 60115-1 4.7	in V-block for 60 Sec., test voltage by type	By type
Temperature Coefficient	IEC 60115-1 4.8	-55°C to +155°C	By type
Insulation Resistance	IEC 60115-1 4.6	in V-block for 60 Sec.	>1,000MΩ
Solderability	IEC 60115-1 4.17	235±5°C for 3±0.5 Sec.	95% Min. coverage
Solvent Resistance of Marking	IEC 60115-1 4.30	IPA for 5±0.5 Min. with ultrasonic	No deterioration of coatings and markings
Robustness of Terminations	IEC 60115-1 4.16	Direct load for 10 Sec. in the direction of the terminal leads	≥2.5kg (24.5N)
Periodic-pulse Overload	IEC 60115-1 4.39	4 times RCWV 10,000 cycles (1 Sec. on, 25 Sec. off)	±2.0%+0.05Ω
Damp Heat Steady State	IEC 60115-1 4.24	40±2°C, 90-95% RH for 56 days, loaded with 0.1 times RCWV	±5.0%+0.05Ω
Endurance at 70°C	IEC 60115-1 4.25	70±2°C at RCWV for 1,000 Hr. (1.5 Hr. on, 0.5 Hr. off)	±5.0%+0.05Ω
Temperature Cycling	IEC 60115-1 4.19	-55°C ⇌ Room Temp. ⇌ +155°C ⇌ Room Temp. (5 cycles)	±1.0%+0.05Ω
Resistance to Soldering Heat	IEC 60115-1 4.18	260±3°C for 10±1 Sec., immersed to a point 3±0.5mm from the body	±1.0%+0.05Ω
Accidental Overload Test	IEC 60115-1 4.26	4 times RCWV for 1 Min.	No evidence of flaming or arcing

Note: Rated Continuous Working Voltage (RCWV) = $\sqrt{\text{Power Rating} \times \text{Resistance Value}}$ or Max. working voltage listed above, whichever less.



EXPLANATIONS OF ORDERING CODE

MFR	-12	F	T	F	52-	100R
Code 1 - 3 Series Name See Index	Code 4 - 6 Power Rating -05 = \varnothing d0.5mm -06 = \varnothing d0.6mm -07 = \varnothing d0.7mm -08 = \varnothing d0.8mm -10 = \varnothing d1.0mm -14 = \varnothing d1.4mm -12 = 1/6W -25 = 1/4W 25S = 1/4WS -50 = 1/2W 50S = 1/2WS 100 = 1W 1WS = 1WS 200 = 2W 2WS = 2WS 204 = 0.4W 207 = 0.6W 300 = 3W 3WS = 3WS 3WM = 3WM 400 = 4W 500 = 5W 5WS = 5WS 5SS = 5WSS 700 = 7W 7WS = 7WS 10A = 10W 20A = 20W 30A = 30W 40A = 40W 50A = 50W 10S = 10WS 15A = 15W 25A = 25W 10B = 100W 25B = 250W	Code 7 Tolerance P = ± 0.02 % A = ± 0.05 % B = ± 0.1 % C = ± 0.25 % D = ± 0.5 % F = ± 1 % G = ± 2 % J = ± 5 % K = ± 10 % - = Base on Spec.	Code 8 Packing Style T = Tape/Box R = Tape/Reel B = Bulk	Code 9 Temperature Coefficient of Resistance - = Base on Spec. A = ± 5 ppm/ $^{\circ}$ C B = ± 10 ppm/ $^{\circ}$ C C = ± 15 ppm/ $^{\circ}$ C S = ± 20 ppm/ $^{\circ}$ C D = ± 25 ppm/ $^{\circ}$ C E = ± 50 ppm/ $^{\circ}$ C F = ± 100 ppm/ $^{\circ}$ C G = ± 200 ppm/ $^{\circ}$ C H = ± 250 ppm/ $^{\circ}$ C I = ± 300 ppm/ $^{\circ}$ C J = ± 350 ppm/ $^{\circ}$ C	Code 10 - 12 Forming Type 26- = 26mm 52- = 52.4mm 73- = 73mm 81- = 81mm 91- = 91mm F = F Type FK = FK Type FKK = FKK Type FFK = F-form Kink M = M-Type Forming MB = M-form W/flat MT = MT Type Forming MR = MR Type AV = AVIsert PN = PANAsert	Code 13 - 17 Resistance Value 0R1 = 0.1 100R = 100 10K = 10,000 10M = 10,000,000

EXCEPTION:

• Cement series:

<Code 8>: Special packing style code

B: Bulk with wirewound or metal oxide sub-assembly for resistance value

W: Bulk with ceramic based wirewound sub-assembly for resistance value

M: Bulk with metal oxide sub-assembly for resistance value

F: Bulk with Fiberglass based wirewound sub-assembly for resistance value

<Code 10-12>: Without forming code

Example: **SQP500JB-10R**

• JPW series:

<Code 13-17>: without resistance value code

Example: **JPW-06-T-52-**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Yageo:

[RSF100JB-73-24R](#) [RSF200JB-73-10R](#) [RSF100JR-52-220K](#) [RSF2WSJR-52-82K](#) [RSF1WSJR-52-270R](#)
[RSF2WSJR-52-22K](#) [RSF2WSJR-52-33R](#) [RSF1WSJR-52-560R](#) [RSF1WSJR-52-680R](#) [RSF1WSJR-52-82R](#)
[RSF2WSJR-52-560R](#) [RSF3WSJR-73-15R](#) [RSF3WSJR-73-27K](#) [RSF3WSJR-73-47K](#) [RSF1WSJR-52-36R](#)
[RSF3WSJR-73-22K](#) [RSF3WSJR-73-56K](#) [RSF3WSJR-73-100K](#) [RSF3WSJR-73-100R](#) [RSF3WSJR-73-18K](#)
[RSF3WSJR-73-5K1](#) [RSF1WSJR-52-68R](#) [RSF2WSJR-52-3K6](#) [RSF2WSJR-52-51K](#) [RSF1WSJR-52-330R](#)
[RSF2WSJR-52-820R](#) [RSF3WSJR-73-12K](#) [RSF1WSJR-52-200R](#) [RSF1WSJR-52-820R](#) [RSF2WSJR-52-18K](#)
[RSF2WSJR-52-51R](#) [RSF1WSJR-52-4K7](#) [RSF2WSJR-52-120R](#) [RSF2WSJR-52-27R](#) [RSF2WSJR-52-39K](#)
[RSF3WSJR-73-10K](#) [RSF2WSJR-52-150R](#) [RSF2WSJR-52-220R](#) [RSF2WSJR-52-510R](#) [RSF2WSJR-52-4K7](#)
[RSF2WSJR-52-68K](#) [RSF1WSJR-52-100R](#) [RSF2WSJR-52-470R](#) [RSF2WSJR-52-1K2](#) [RSF2WSJR-52-20K](#)
[RSF3WSJR-73-6K2](#) [RSF2WSJR-52-5K6](#) [RSF2WSJR-52-82R](#) [RSF3WSJR-73-8K2](#) [RSF2WSJR-52-100R](#)
[RSF2WSJR-52-10K](#) [RSF3WSJR-73-1K](#) [RSF2WSJR-52-6K2](#) [RSF1WSJR-52-47R](#) [RSF2WSJR-52-10R](#) [RSF3WSJR-](#)
[73-47R](#) [RSF3WSJR-73-680R](#) [RSF3WSJR-73-110R](#) [RSF1WSJR-52-120R](#) [RSF1WSJR-52-22R](#) [RSF1WSJR-52-39R](#)
[RSF2WSJR-52-12K](#) [RSF3WSJR-73-150R](#) [RSF3WSJR-73-4K7](#) [RSF2WSJR-52-27K](#) [RSF2WSJR-52-30R](#)
[RSF2WSJR-52-5K1](#) [RSF3WSJR-73-1K5](#) [RSF3WSJR-73-24R](#) [RSF2WSJR-52-1K5](#) [RSF2WSJR-52-270R](#)
[RSF1WSJR-52-1K5](#) [RSF1WSJR-52-33R](#) [RSF3WSJR-73-10R](#) [RSF3WSJR-73-20R](#) [RSF3WSJR-73-20K](#) [RSF3WSJR-](#)
[73-56R](#) [RSF1WSJR-52-220R](#) [RSF1WSJR-52-3K3](#) [RSF2WSJR-52-100K](#) [RSF2WSJR-52-47R](#) [RSF2WSJR-52-24K](#)
[RSF2WSJR-52-2K](#) [RSF2WSJR-52-15K](#) [RSF3WSJR-73-5K6](#) [RSF3WSJR-73-7K5](#) [RSF3WSJR-73-15K](#) [RSF2WSJR-](#)
[52-15R](#) [RSF2WSJR-52-3K3](#) [RSF2WSJR-52-68R](#) [RSF2WSJR-52-180R](#) [RSF2WSJR-52-33K](#) [RSF2WSJR-52-680R](#)
[RSF1WSJR-52-51K](#) [RSF1WSJR-52-56K](#) [RSF1WSJR-52-3K9](#) [RSF1WSJR-52-5K1](#) [RSF1WSJR-52-75R](#) [RSF1WSJR-](#)
[52-300R](#) [RSF2WSJR-52-91R](#)