

Precision Devices, Inc.

8840 N. Greenview Dr.
Middleton, WI 53562
Phone: 608-831-4445
1-800-274-XTAL
Fax: 608-831-3343



Visit our web site at www.pdixtal.com

Sales Information sales@pdixtal.com

Electrical Specifications

- Center Frequency: 66.000000 MHz
- Output: CMOS
- Frequency Stability at +25°C: See Line 5
- Operating Temperature Range: -40°C to +85°C
- Frequency Stability: ±50ppm (Inclusive of tolerance @25°C, operating temperature, supply voltage, 10 year aging, shock and vibration not under operation)
- Storage Temperature Range: -40°C to +100°C
- Duty Cycle: 45/55% maximum @ 50% Vcc
- T-Rise, T-Fall: 4.0nS maximum @ 20% to 80% Vcc
- Supply Current : output enabled: 10mA maximum
output disabled: 10uA maximum
- Supply Voltage: +3.3Vdc ±5%
- Load: 15pF maximum
- Output Voltage: Vol: 0.1Vcc maximum (Iol = 4mA)
Voh: 0.9Vcc minimum (Ioh = -4mA)
- Start-up Time: 10mS maximum
- Jitter (RMS): 1pS Maximum (Bandwidth: 12kHz to 20MHz)



- Note: 1) 6 days aging Minimum @ 105°C**
2) 24 hour settle time before 100% testing @ 25°C
3) Sample Perturbation Test Every 1°C: ±5ppm Maximum

Truth Table for Enable/Disable Function




Terminal 1 (Enable/Disable control)	Function	Terminal 3 (Output)
Ground or ≤ 0.2Vcc	Disabled	High Impedance
Vcc ≥ VIH ≥ 0.7Vcc or Open (1)	Enabled	Active

(1) Terminal 1 is normally high by an internal pull-up resistor.

REV.	DATE	PAGE	DESCRIPTION	Auth.	ECN
FOR PRELIMINARY USE ONLY Specifications subject to change without notice.					
			TITLE	FKA	65792R
Ceramic Crystal Oscillator Tape/Reel					
			PART NUMBER	OC2E6600XCDDR	
	DATE	SCALE	ECN.	REV.	
	5/4/12	N.T.S.	N/A	N/A	
	SIZE	CAGE	Page 1 of 2		
	A	0S4G1			



Recommended Land Pattern



PIN	CONNECTION
1	Enable/Disable
2	Ground
3	Output
4	Vcc



Precision Devices Inc.



8840 N. Greenview Dr.
Middleton WI 53562
608-831-4445
1-800-274-XTAL



Manufacturer of Quartz Crystal Products

DECIMAL	DWG FILE	PART NUMBER	
XX=±.020 XXX=±.008	65792R	OC2E66000XCDDR	
METRIC	SCALE	FREQUENCY	DRAWN BY
XX=±.50 XXX=±.20	N.T.S.	66.000000 MHz	J.Lawinger
ANGULAR	DRAWING TYPE		DATE
XX=±2°	Ceramic Crystal Oscillator Tape/Reel		5/4/12
	REV. LEVEL	ECN NO.	CAGE CODE
	N/A	N/A	0S4G1