


NOTES:


1. ROHS COMPLIANT
2. MATERIAL: CONNECTOR SOCKET - POLYPROPYLENE; UI, RATING 94-HB
 PANEL CONNECTOR - POLYESTER, UI RATING 94-V0
 TERMINALS - PHOSPHOR BRONZE, TIN PLATE
3. WIRE: 24 AWG 1007/11569
4. MOUNTING: HOLE SIZE - .932" (7.14mm)
 PANEL THICKNESS: .030" (.762mm) MIN. - .220" (5.588mm) MAX
 USING CMC 285:
 FOR PANEL THICKNESS .030" (.762mm) - .045" (1.143mm) USE 2 SPC 060 SPACERS
 FOR PANEL THICKNESS .050" (1.27mm) - .100" (2.54mm) USE 1 SPC 060 SPACER
 FOR PANEL THICKNESS .105" (2.67mm) - .125" (3.175mm) NO SPACER REQUIRED
 USING CML 325 OR CML 327:
 FOR PANEL THICKNESS .060" (1.524mm) - .100" (2.54mm) USE 2 SPC 060 SPACERS
 FOR PANEL THICKNESS .105" (2.667mm) - .125" (3.175mm) USE 1 SPC 060 SPACER
 FOR PANEL THICKNESS .150" (3.81mm) - .220" (5.588mm) NO SPACER REQUIRED
5. LED LEAD LENGTH: FOR CMC 285 - .350" ± .01" (8.89mm ± 0.254mm)
 FOR CML 325 OR CML 327 - .275" ± 0.01" (6.985mm ± 0.254)
6. U.S. & FOREIGN PATENT ISSUED AND PENDING

CABLE ORDERING CODE EXAMPLE:
CNX D F 4 6 12




TERMINATION *		WIRE SIZE *	WIRE COLOR*	WIRE LENGTH *
X =	STRIPPED END	24	6 WHITE - BLACK - RED	04 4 INCHES (101.6mm)
F =	SINGLE ROW LOCKING HEADER	24 AWG		06 6 INCHES (152.4mm)
				08 8 INCHES (203.2mm)
				12 12 INCHES (304.8mm)
				18 18 INCHES (457.2mm)
				24 24 INCHES (609.6mm)

* CALL FACTORY FOR ADDITIONAL OPTIONS



ANODE (+) WHITE LEAD
 CATHODE (-) BLACK LEAD
 ANODE (+) RED LEAD



DIMENSION STYLE INCHES / MM GIVE UNLESS OTHERWISE SPECIFIED	MATERIAL	SEE NOTES	V99 OPTOELECTRONICS 199 POSTISCK BLVD SUITE 101 SAN MARCOS, CA 92061 U.S.A. PHONE: (760) 560-1300 FAX: (760) 560-1301 EMAIL: vccsales@vccalle.com	
	FINISH	SEE NOTES	TITLE: CNX D CABLE ASSEMBLY	REV: 001
INCHES ±.500 MM ±.127	THIRD ANGLE PROJECTION	APPROVAL	SIZE	DWG. NO.
		DRAWN K Howard	B	CNX D ASSY
DO NOT SCALE DRAWING	DATE 11/28/10	CHECKED DPZ	SCALE: 1.75:1	SHEET 1 OF 1
		11/28/10		