



Part Number : [15311033](#)


Product Description : [4.80mm Pitch Wire-to-Wire Plug Housing, 3 Circuits](#)

Series Number : [5025](#)

Status : Active

Product Category : [Connector Housings](#)

Engineering Number : [5025-03P1](#)



NO IMAGE AVAILABLE

Documents & Resources

Drawings

[Drawing 015311033_sd.pdf](#)

[Packaging Design Drawing SPK-5025-001-001.pdf](#)

3D Models and Design Files

[3D Model 015311033_stp.zip](#)

[3D Model PDF 015311033.pdf](#)

Specifications

[Product Specification PS-5025-002-001.pdf](#)

[Product Specification PS-5025-003-001.pdf](#)

[Product Specification PS-5025-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	5025
Description	4.80mm Pitch Wire-to-Wire Plug Housing, 3 Circuits
Application	Power, Wire-to-Wire
Product Name	N/A
UPC	800753684287

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	3
Flammability	94V-2
Gender	Plug
Glow-Wire Capable	No
Net Weight	1270.700/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.80mm

Pitch - Termination Interface	4.80mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
4.80mm Pitch Wire-to-Wire Receptacle Housing, 3 Circuits	<u>0015311032</u>

Use with Part(s)

Description	Part Number
4.80mm Pitch Male Crimp Terminal	<u>5006</u>

This document was generated on Sep 04, 2023