

## Features

- Maximum reliability
- Halogen-free and phosphorus
- UL94-V0 flammability class
- UL standard F1 resistance to ultraviolet radiation
- IP68 protection grade, reference to DIN EN 60529
- Meets various electrical environment requirements
- Chemical, corrosion, temperature, acid and high impact resistant
- Advanced precision, lightweight design
- RoHS and REACH compliant



## Applications


- Electrical power distribution
- Network communication
- LED solar lighting and machinery
- Inlet - outlet connections & more

## Specification

Protection Rating	IP 68
Temperature Range	-40...+100 °C
Thread Type	PG, According to DIN40340

## Material Specification

Sealing Element	Nitrile Rubber
Clamp Jaw	Polyamide, UL 94-V2
Body Material	Nickel Plated Brass



## Product Range

Art. Nr.	Thread	Clamping Range	Colour	GL	H	AG	Spanner Size	Panel Mounting Hole
RND 465-00849	PG11	5 ... 10 mm	Grey	6 mm	29 mm	18.6 mm	20 mm	18 ... 18.3 mm
RND 465-00850	PG13.5	6 ... 12 mm	Grey	6.5 mm	31 mm	20.4 mm	22 mm	20.4 ... 20.7 mm
RND 465-00851	PG16	10 ... 14 mm	Grey	6.5 mm	31 mm	22.5 mm	24 mm	22.5 ... 22.8 mm
RND 465-00852	PG21	13 ... 18 mm	Grey	7 mm	37 mm	28.3 mm	30 mm	28.3 ... 28.6 mm