


Surface Mount Schottky Barrier Diode



FEATURES:

Low forward voltage

Fast switching


SPECIFICATION:
Absolute Maximum Ratings ($T_a = 25^\circ\text{C}$)

Parameter	Symbol	Value	Unit
Repetitive Peak Reverse Voltage	V_{RRM}	40	V
DC Blocking Voltage	V_R	40	V
Forward Continuous Current	I_F	200	mA
Peak Forward Surge Current (at $t_p < 1 \text{ s}$)	I_{FSM}	600	mA
Junction Temperature	T_J	150	$^\circ\text{C}$
Storage Temperature Range	T_{Stg}	- 55 to + 150	$^\circ\text{C}$

Characteristics at $T_a = 25^\circ\text{C}$

Parameter	Symbol	Min.	Max.	Unit
Forward Voltage at $I_F = 1 \text{ mA}$ at $I_F = 40 \text{ mA}$	V_F V_F	- -	380 1000	mV mV
Reverse Current at $V_R = 30 \text{ V}$	I_R	-	200	nA
Reverse Breakdown Voltage at $I_R = 10 \mu\text{A}$	$V_{(BR)R}$	40	-	V
Reverse Recovery Time from $I_F = 10 \text{ mA}$ through $I_R = 10 \text{ mA}$ to $I_R = 1 \text{ mA}$	t_{rr}	-	5	ns
Total Capacitance at $V_R = 0 \text{ V}$, $f = 1 \text{ MHz}$	C_T	-	5	pF

Art. Nr.
RND BAS40-06