


Spring-loaded test probe  
**GKS-080 301 035 A 0805**  
Item GKS-080-0001



**ingun**<sup>®</sup>  
Partner for Future Technology

**INGUN SELECTION**



1:1

# Spring-loaded test probe

## GKS-080 301 035 A 0805

Item GKS-080-0001



GO TO PRODUCT


# ingun®

Partner for Future Technology

### General data

Product group	ICT / FCT (in-circuit test and function test)
Sub-product group	Fine-pitch
Series	GKS-080 with spring pin
Grid	1 mm [40 mil]
Contacting from	Pad
Magnetic	Yes
Installation type	Plug-in
Quick-exchange system	No
Type of test probe connection	Solder connection
Adjustable installation height	No
Non-rotating	No
Min. temperature	- 40 °C [- 104 °F]
Max. temperature	+ 80 °C [+ 176 °F]
RoHS-compliant	Yes

### INGUN SELECTION




### Electrical data

Current load capacity / rated current	3 A
Typical resistance (Ri)	<20 mOhm

### Mechanical data

Total length	22.3 mm [.877 in]
Barrel diameter	0.7 mm [.027 in]
Maximum stroke	3.8 mm [.149 in]
Spring pre-load	0.2 N [.719 ozf]
Collar height	05
Spring force at working stroke	0.8 N [2.87 ozf]
Recommended working stroke	3 mm [.118 in]



### Tip style data

Tip style	01 30° needle tip, self-cleaning
Tip diameter	0.35 mm [.013 in]
Tip style surface	A gold
Tip style material	3 CuBe

### INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162  
78467, Constance, Germany  
Phone +49 7531 8105-0  
Customer hotline +49 7531 8105-888  
Fax +49 7531 8105-65  
info@ingun.com



Prices and delivery times on request.  
Technical changes reserved. 11/22 EN

Weitere Informationen zum Thema  
ICT/FCT Test probes

