

MLFB-Ordering data

6SL3210-1KE12-3UF2



Figure similar

Client order no.: Order no. : Offer no. : Remarks:

Item no.: Consignment no. : Project:

Rated da	ta
nput	
Number of phases	3 AC
Line voltage	380 480 V +10 % -20 %
Line frequency	47 63 Hz
Rated current (LO)	2.90 A
Rated current (HO)	2.50 A
Output	
Number of phases	3 AC
Rated voltage	400 V
Rated power IEC 400V (LO)	0.75 kW
Rated power NEC 480V (LO)	1.00 hp
Rated power IEC 400V (HO)	0.55 kW
Rated power NEC 480V (HO)	0.75 hp
Rated current (IN)	2.30 A
Rated current (LO)	2.20 A
Rated current (HO)	1.70 A
Max. output current	3.40 A
Pulse frequency	4.000 kHz
Output frequency for vector control	0 240 Hz
Output frequency for V/f control	0 550 Hz

Overload ca	pability
-------------	----------

Low Overload (LO)

150 % base load current IL for 3 s, followed by 110 % base load current IL for 57 s in a 300 s cycle time

High Overload (HO)

200 % base load current IH for 3 s, followed by 150 % base load current IH for 57 s in a 300 s cycle time

General tech. specifications		
Power factor λ	0.70 0.85	
Offset factor cos φ	0.95	
Efficiency η	0.97	
Sound pressure level (1m)	49 dB	
Power loss	0.04 kW	
Filter class (integrated)	Unfiltered	

Ambient conditions		
Cooling	Air cooling using an integrated fan	
Cooling air requirement	0.005 m³/s (0.177 ft³/s)	
Installation altitude	1000 m (3280.84 ft)	
Ambient temperature		
Operation	-10 40 °C (14 104 °F)	
Transport	-40 70 °C (-40 158 °F)	
Storage	-40 70 °C (-40 158 °F)	
Relative humidity		

95 % At 40 °C (104 °F), condensation Max. operation and icing not permissible

Closed-loop control techniques		
V/f linear / square-law / parameterizable	Yes	
V/f with flux current control (FCC)	Yes	
V/f ECO linear / square-law	Yes	
Sensorless vector control	Yes	
Vector control, with sensor	No	
Encoderless torque control	No	
Torque control, with encoder	No	



MLFB-Ordering data

6SL3210-1KE12-3UF2



			Figure s
Mechanical data		Com	munication
Degree of protection	IP20 / UL open type	Communication	PROFINET / EtherNet/IP
Size	FSAA	Connections	
Net weight	1.40 kg (3.09 lb)	Signal cable	
Width	73 mm (2.87 in)	Conductor cross-section	0.15 1.50 mm² (AWG 24 AWG 1
Height	173 mm (6.81 in)	Line side	
Depth	178 mm (7.01 in)	Version	Plug-in screw terminals
Inputs / ou	tputs	Conductor cross-section	1.00 2.50 mm² (AWG 18 AWG 14
tandard digital inputs		Motor end	
Number	6	Version	Plug-in screw terminals
Switching level: 0→1	11 V	Conductor cross-section	1.00 2.50 mm² (AWG 18 AWG 14
Switching level: 1→0	5 V	DC link (for braking resistor)	
Max. inrush current	15 mA	Version	Plug-in screw terminals
ail-safe digital inputs		Conductor cross-section	1.00 2.50 mm² (AWG 18 AWG 14
Number	1	Line length, max.	15 m (49.21 ft)
oigital outputs		PE connection	On housing with M4 screw
Number as relay changeover contact	1	Max. motor cable length	on nearing man in second
Output (resistive load)	DC 30 V, 0.5 A	Shielded	50 m (164.04 ft)
Number as transistor	1	Unshielded	100 m (328.08 ft)
Output (resistive load)	DC 30 V, 0.5 A	S	tandards
analog / digital inputs		Compliance with standards	UL, cUL, CE, C-Tick (RCM)
Number	1 (Differential input)		
Resolution	10 bit	CE marking	EMC Directive 2004/108/EC, Low-Volt Directive 2006/95/EC
witching threshold as digital in	put		
0→1	4 V		
1→0	1.6 V		
Analog outputs			
Number	1 (Non-isolated output)		
	. (Horr isolated output)		

PTC/ KTY interface

1 motor temperature sensor input, sensors that can be connected: PTC, KTY and Thermo-Click, accuracy $\pm 5~^{\circ}\text{C}$



MLFB-Ordering data


6SL3210-1KE12-3UF2



Figure similar

Converter losses to EN 50598-2*

Efficiency class	IE2
Comparison with the reference converter (90% /	-80.87 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard EN 50598) of the relative torque generating current (I) over the relative motor stator frequency(f). The values are valid for the basic version of the converter without options/components.

*converted values