



GBP Plastic-Encapsulate Bridge Rectifier

GBP4005 THRU GBP410 General Purpose Bridge Rectifier

Features


- I_o 4A
- VRRM 50V-1000V
- High surge current capability
- Glass passivated chip

Applications

- General purpose 1 phase Bridge rectifier applications

Marking

- GBP4XX
- XX : From 005 To 10



Limiting Values (Absolute Maximum Rating)

Item	Symbol	Unit	Conditions	GBP4						
				005	01	02	04	06	08	10
Repetitive Peak Reverse Voltage	V _{RRM}	V		50	100	200	400	600	800	1000
Average Rectified Output Current	I _o	A	60Hz sine wave, R-load T _c =50°C	4.0						
Surge(Non-repetitive)Forward Current	I _{FSM}	A	60Hz sine wave, 1 cycle, T _j =25°C	125						
Current Squared Time	I ² t	A ² S	1ms ≤ t < 8.3ms T _j =25°C, Rating of per diode	64.8						
Storage Temperature	T _{stg}	°C		-55 ~+150						
Junction Temperature	T _j	°C		-55 ~+150						

Electrical Characteristics (T_a=25°C Unless otherwise specified)

Item	Symbol	Unit	Test Condition	Max
Peak Forward Voltage	V _{FM}	V	I _{FM} =4.0A, Pulse measurement, Rating of per diode	1.1
Peak Reverse Current	I _{RRM}	μ A	V _{RM} =V _{RRM} , Pulse measurement, Rating of per diode	10
Thermal Resistance	R _{θ J-A}	°C/W	Between junction and ambient	47
	R _{θ J-C}		Between junction and lead	10

Typical Characteristics

FIG.1-MAXIMUM NON-REPETITIVE SURGE CURRENT




FIG.2-FORWARD DERATING CURRENT




FIG.3-TYPICAL FORWARD CHARACTERISTICS







FIG.4-TYPICAL REVERSE CHARACTERISTICS



GBP Package Outline Dimensions



Dimensions in inches and (millimeters)

NOTICE

JSCJ reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. JSCJ does not assume any liability arising out of the application or use of any product described herein.