

# Han C axial module female 2,5-8mm<sup>2</sup>



Part number	09 14 003 2701
Specification	Han C axial module female 2,5-8mm <sup>2</sup>
HARTING eCatalogue	https://b2b.harting.com/09140032701

Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Modules
Series	Han-Modular <sup>®</sup>
Type of module	Han <sup>®</sup> C module
Size of the module	Single module

#### Version

Termination method	Axial screw termination
Gender	Female
Number of contacts	3

## **Technical characteristics**

Conductor cross-section	2.5 8 mm²
Rated current	40 A
Rated voltage	690 V
Rated impulse voltage	8 kV
Pollution degree	3
Rated current acc. to UL	40 A
Rated voltage acc. to UL	600 V
Insulation resistance	>10 <sup>10</sup> Ω
Contact resistance	≤0.3 mΩ
Stripping length	5 mm @ 2.5 mm² 5 mm @ 4 mm² 8 mm @ 6 mm²

Page 1 / 3 | Creation date 2023-08-25 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Stiftung & Co. KG | Marienwerderstr. 3 | 32339 Espelkamp | Germany



## **Technical characteristics**

Tightening torque	1.5 Nm @ 2.5 mm² 1.5 Nm @ 4 mm² 2 Nm @ 6 mm²
Limiting temperature	-40 +125 °C
Mating cycles	≥500
Material properties	
Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076 UL 2237 PVVA2.E318390 CSA-C22.2 No. 182.3 PVVA8.E318390
Approvals	DNV GL

Page 2 / 3 | Creation date 2023-08-25 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Stiftung & Co. KG | Marienwerderstr. 3 | 32339 Espelkamp | Germany

Product data sheet 09 14 003 2701 Han C axial module female 2,5-8mm<sup>2</sup>



#### Commercial data

Packaging size	2
Net weight	31.63 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140020016
ETIM	EC000438
eCl@ss	27440217 Module for industrial connectors (power/signals)

Page 3 / 3 | Creation date 2023-08-25 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Stiftung & Co. KG | Marienwerderstr. 3 | 32339 Espelkamp | Germany