


SFH618A-2X, SFH618A-3X, SFH618A-4X,  
SFH618-2, SFH618-3, SFH618-4



## LOW INPUT CURRENT PHOTOTRANSISTOR OPTICALLY COUPLED ISOLATORS



### APPROVALS

- UL recognised, File No. E91231  
Package Code " EE "

### 'X' SPECIFICATION APPROVALS

- VDE 0884 in 3 available lead form :-
  - STD
  - G form
  - SMD approved to CECC 00802
- Certified to EN60950 by :-  
Nemko - Certificate No. P01102465

### DESCRIPTION



The SFH618 series of optically coupled isolators consist of infrared light emitting diodes and NPN silicon photo transistors in space efficient dual in line plastic packages.

### FEATURES

- Options :-
  - 10mm lead spread - add G after part no.
  - Surface mount - add SM after part no.
  - Tape&reel - add SMT&R after part no.
- Low input current 0.5mA  $I_F$
- High Current Transfer Ratios (63-320% at 1mA, 32% min at 0.5mA)
- High Isolation Voltage (5.3kV<sub>RMS</sub>, 7.5kV<sub>PK</sub>)
- High BV<sub>CEO</sub> (55V min)
- All electrical parameters 100% tested
- Custom electrical selections available

### APPLICATIONS

- Computer terminals
- Industrial systems controllers
- Measuring instruments
- Signal transmission between systems of different potentials and impedances



ISOCOM COMPONENTS LTD  
Unit 25B, Park View Road West,  
Park View Industrial Estate, Brenda Road  
Hartlepool, Cleveland, TS25 1YD  
Tel: (01429) 863609 Fax :(01429) 863581

**ABSOLUTEMAXIMUMRATINGS**  
**(25°C unless otherwise specified)**

Storage Temperature	_____	-55°C to +125°C
Operating Temperature	_____	-30°C to +100°C
Lead Soldering Temperature (1/16 inch (1.6mm) from case for 10 secs)		260°C

**INPUTDIODE**

Forward Current	_____	50mA
Reverse Voltage	_____	6V
Power Dissipation	_____	70mW

**OUTPUTTRANSISTOR**

Collector-emitter Voltage BV <sub>CEO</sub>	_____	55V
Emitter-collector Voltage BV <sub>ECO</sub>	_____	6V
Collector Current	_____	50mA
Power Dissipation	_____	150mW

**POWERDISSIPATION**

Total Power Dissipation	_____	200mW
(derate linearly 2.67mW/°C above 25°C)		

**ELECTRICAL CHARACTERISTICS ( T<sub>A</sub> = 25°C Unless otherwise noted )**

PARAMETER		MIN	TYP	MAX	UNITS	TEST CONDITION
Input	Forward Voltage (V <sub>F</sub> )			1.5	V	I <sub>F</sub> =5mA
	Reverse Current (I <sub>R</sub> )			10	μA	V <sub>R</sub> =6V
Output	Collector-emitter Breakdown (BV <sub>CEO</sub> ) ( Note 2 )	55			V	I <sub>C</sub> =1mA
	Emitter-collector Breakdown (BV <sub>ECO</sub> ) Collector-emitter Dark Current (I <sub>CEO</sub> )	6		200	V nA	I <sub>E</sub> =100μA V <sub>CE</sub> =10V
Coupled	Current Transfer Ratio (CTR) (Note 2)  SFH618-2 SFH618-2 SFH618-3 SFH618-3 SFH618-4 SFH618-4	63		125	%	1mA I <sub>F</sub> , 0.5VV <sub>CE</sub>
		32			%	0.5mA I <sub>F</sub> , 1.5VV <sub>CE</sub>
		100		200	%	1mA I <sub>F</sub> , 0.5VV <sub>CE</sub>
		50			%	0.5mA I <sub>F</sub> , 1.5V V <sub>CE</sub>
		160		320	%	1mA I <sub>F</sub> , 0.5V V <sub>CE</sub>
		80			%	0.5mA I <sub>F</sub> , 1.5VV <sub>CE</sub>
	Collector-emitter Saturation Voltage V <sub>CESAT</sub>  SFH618-2 SFH618-3 SFH618-4			0.4	V	1mA I <sub>F</sub> , 0.32mA I <sub>C</sub>
				0.4	V	1mA I <sub>F</sub> , 0.5mA I <sub>C</sub>
				0.4	V	1mA I <sub>F</sub> , 0.8mA I <sub>C</sub>
	Input to Output Isolation Voltage V <sub>ISO</sub>	5300			V <sub>RMS</sub>	See note 1
		7500			V <sub>PK</sub>	See note 1
	Input-output Isolation Resistance R <sub>ISO</sub>	5x10 <sup>10</sup>			Ω	V <sub>IO</sub> =500V (note 1)
	Output Rise Time, tr		4	18	μS	V <sub>CE</sub> =2V, I <sub>C</sub> =2mA
	Output Fall Time, tf		3	18	μS	R <sub>L</sub> =100Ω

Note 1 Measured with input leads shorted together and output leads shorted together.

Note 2 Special Selections are available on request. Please consult the factory.

