

3DP-PLA1.75GE-01-B

Filament, PLA Blue, 1.75 mm, 200 g, GEMMA printer spool

VERSATILE & EASY TO USE

- PLA (polylactide) is a biodegradable thermoplastic polyester, which is easy to print for variety 3D printers.
- It has no odor, a lower melting point and good flowability, no need to post-treatment.



Features

- High precision roundness enables higher printing quality
- No bubbles, vivid colors
- Can be applied to a variety of 3D printers

Packaging

Q'ty in crtn, pcs	60
Crtn volume, CUM	0.088
Crtn weight, kgs	25.28
Individual package size LxWxH:	164x164x45 mm
Carton size LxWxH:	720x350x350 mm
Country of origin	CN
Barcode	8716309118958
Customs code	3916909000

Specifications

Material: PLA, 1.75 mm diameter
Weight: 0.2 kg/spool
Density at 21.5 °C: 1.25 g/cm³
Melt Flow Index at 10min, 2.16kg: 5
Melt Point: 190 220 °C
Heat-Deflection-Temperature at 0.455 MPa: 50 °C
Yield Strength at 5mm/min: 45 MPa
Impact Strength: 5 KJ/m²
Elongation at Break: 20 %
Diameter: 1.75 ± 0.05 mm

System requirements

A 3D printer with 1.75 mm extruder of temperature around 200 °, suitable for PLA filament

Certificates

