

www.vishay.com

Vishay Draloric

# Pulse Proof, High Power Thick Film Chip Resistors



#### **LINKS TO ADDITIONAL RESOURCES**



The pulse proof, high power thick film chip resistors series is the perfect choice for most fields of power measurement electronics where reliability, stability, high power rating and excellent pulse load performance are of major concern. Typical applications include battery management systems in automotive appliances.

#### **FEATURES**

- Excellent pulse load capability
- Enhanced power rating
- · Double side printed resistor element
- AEC-Q200 qualified



# RoHS

COMPLIANT HALOGEN

#### **APPLICATIONS**

- Automotive
- Industrial
- Commercial
- High power

TECHNICAL SPEC	FICATION	IS						
DESCRIPTION	CRCW0402- HP e3	CRCW0603- HP e3	CRCW0805- HP e3	CRCW1206- HP e3	CRCW1210- HP e3	CRCW1218- HP e3	CRCW2010- HP e3	CRCW2512- HP e3
Imperial size	0402	0603	0805	1206	1210	1218	2010	2512
Metric size code	RR1005M	RR1608M	RR2012M	RR3216M	RR3225M	RR3246M	RR5025M	RR6332M
Resistance range				1 Ω to 1 MΩ:	; jumper (0 Ω)			
Resistance tolerance				± 5 %; ± 1	%; ± 0.5 %			
Temperature coefficient				± 200 ppm/K;	; ± 100 ppm/K			
Rated dissipation, P <sub>70</sub> (1)	0.2 W <sup>(2)</sup>	0.33 W	0.5 W	0.75 W <sup>(3)</sup>	0.75 W	1.5 W	1.0 W	1.5 W
Operating voltage, <i>U</i> <sub>max.</sub> AC <sub>RMS</sub> /DC	50 V	75 V	150 V	200 V	200 V	200 V	400 V	500 V
Permissible film temperature, $\vartheta_{\text{F max.}}^{(1)}$	155 °C							
Operating temperature range				-55 °C to	+155 °C			
Max. resistance change at $P_{70}$ for resistance range, $ \Delta R/R $ after:								
1000 h		≤ 2.0 %						
8000 h		≤ 4.0 %						
Permissible voltage against ambient (insulation):								
1 min, U <sub>ins</sub>	75 V	100 V	200 V	300 V	300 V	300 V	300 V	300 V
Failure rate: FIT observed	≤ 0.1 x 10 <sup>-9</sup> /h							

#### Notes

- (1) Please refer to APPLICATION INFORMATION below
- (2) CRCW0402-HP resistors feature a single side printed resistive layer only, except jumpers
- (3) Specified power rating requires a thermal resistance of  $R_{th} \le 110 \text{ K/W}$

### **APPLICATION INFORMATION**

When the resistor dissipates power, a temperature rise above the ambient temperature occurs, dependent on the thermal resistance of the assembled resistor together with the printed circuit board. The rated dissipation applies only if the permitted film temperature is not exceeded.

These resistors do not feature a limited lifetime when operated within the permissible limits. However, resistance value drift increasing over operating time may result in exceeding a limit acceptable to the specific application, thereby establishing a functional lifetime.



TYPE / SIZE	TCR	TOLERANCE	RESISTANCE	E-SERIES	
	± 200 ppm/K	± 5 %	1 Ω to 1 MΩ	E24	
CRCW0402-HP e3	± 100 ppm/K	± 1 %	1 Ω to 1 MΩ	E24; E96	
0110110402-111 60	• •	± 0.5 %	1 32 10 1 10132		
	Jumper, I <sub>max.</sub> = 3 A	≤ 10 mΩ	0 Ω	-	
	± 200 ppm/K	± 5 %	1 $\Omega$ to 1 M $\Omega$	E24	
CRCW0603-HP e3	± 100 ppm/K	± 1 % ± 0.5 %	1 Ω to 1 MΩ	E24; E96	
-	Jumper, I <sub>max.</sub> = 5 A	± 0.5 % ≤ 8 mΩ	0 Ω		
	± 200 ppm/K	± 5 %	1 Ω to 1 MΩ	E24	
		± 1 %			
CRCW0805-HP e3	± 100 ppm/K	± 0.5 %	1 Ω to 1 MΩ	E24; E96	
-	Jumper, I <sub>max.</sub> = 6 A	≤ 5 mΩ	0 Ω	-	
	± 200 ppm/K	± 5 %	1 Ω to 1 MΩ	E24	
CRCW1206-HP e3	± 100 ppm/K	± 1 %	1 Ω to 1 MΩ	E24; E96	
ChCW1200-nF es	± 100 pp11/K	± 0.5 %	1 52 10 1 10152	□24, □90	
	Jumper, I <sub>max.</sub> = 10 A	≤ 5 mΩ	0 Ω	-	
	± 200 ppm/K	± 5 %	1 $\Omega$ to 1 M $\Omega$	E24	
CRCW1210-HP e3	± 100 ppm/K	± 1 %	1 Ω to 1 MΩ	E24; E96	
01101112101111 00	• •	± 0.5 %		LL+, L00	
	Jumper, I <sub>max.</sub> = 12 A	≤ 4 mΩ	0 Ω	-	
	± 200 ppm/K	± 5 %	1 Ω to 1 MΩ	E24	
CRCW1218-HP e3	± 100 ppm/K	± 1 %	1 Ω to 1 MΩ	E24; E96	
		± 0.5 %			
	Jumper, I <sub>max.</sub> = 20 A	≤ 4 mΩ	0 Ω	-	
	± 200 ppm/K	± 5 %	1 Ω to 1 MΩ	E24	
CRCW2010-HP e3	± 100 ppm/K	± 1 %	1 Ω to 1 MΩ	E24; E96	
		± 0.5 %			
	Jumper, I <sub>max.</sub> = 12 A	≤ 5 mΩ	0 Ω	-	
	± 200 ppm/K	± 5 %	1 Ω to 1 MΩ	E24	
CRCW2512-HP e3	± 100 ppm/K	± 1 %	1 Ω to 1 MΩ	E24; E96	
	• •	± 0.5 %		,	
	Jumper, $I_{\text{max.}} = 16 \text{ A}$	≤ 5 mΩ	0 Ω		


Note • The temperature coefficient of resistance (TCR) is not specified for 0  $\Omega$  jumpers

PACKAGING						
TYPE / SIZE	CODE	QUANTITY	PACKAGING STYLE	WIDTH	PITCH	PACKAGING DIMENSIONS
CRCW0402-HP e3	ED = ET7	10 000			2 mm	Ø 180 mm / 7"
0110110402-111 60	EE = EF4	50 000			2 111111	Ø 330 mm / 13"
	EI = ET2	5000				Ø 180 mm / 7"
	ED = ET3	10 000		8 mm	2 mm	Ø 180 mm / 7"
	EL = ET4	20 000				Ø 285 mm / 11.25"
CRCW0603-HP e3	EE = ET8	20 000				Ø 330 mm / 13"
	EA = ET1	5000			4 mm	Ø 180 mm / 7"
	EB = ET5	10 000				Ø 285 mm / 11.25"
	EC = ET6	20 000	Paper tape acc. to			Ø 330 mm / 13"
	EA = ET1	5000	IEC 60286-3, type 1a		4 mm	Ø 180 mm / 7"
CRCW0805-HP e3	EB = ET5	10 000				Ø 285 mm / 11.25"
	EC = ET6	20 000				Ø 330 mm / 13"
	EA = ET1	5000			4 mm	Ø 180 mm / 7"
CRCW1206-HP e3	EB = ET5	10 000				Ø 285 mm / 11.25"
	EC = ET6	20 000				Ø 330 mm / 13"
	EA = ET1	5000				Ø 180 mm / 7"
CRCW1210-HP e3	EB = ET5	10 000			4 mm	Ø 285 mm / 11.25"
	EC = ET6	20 000				Ø 330 mm / 13"
CRCW1218-HP e3	EK = ET9	4000			4 mm	Ø 180 mm / 7"
CRCW2010-HP e3	EF = E02	4000	District and the		4 mm	Ø 180 mm / 7"
Chowzulu-ne es	EJ = E08	16 000	Blister tape acc. to IEC 60286-3, type 2a	12 mm	4 mm	Ø 330 mm / 13"
CRCW2512-HP e3	EG = E67	2000	120 00200-3, type 2a		8 mm	Ø 180 mm / 7"
CHCW2512-HP e3	EH = E82	4000	]		4 mm	יי וווווו / / "



www.vishay.com

Vishay Draloric





### Vishay Draloric

#### **DESCRIPTION**

Production is strictly controlled and follows an extensive set of instructions established for reproducibility. A cermet film layer and a glass-over are deposited on both sides of a high grade ( $Al_2O_3$ ) ceramic substrate with its prepared inner contacts on both sides. A special laser is used to achieve the target value by smoothly fine trimming the resistive layer without damaging the ceramics. The resistor elements are covered by a protective coating designed for electrical, mechanical and climatic protection. The terminations receive a final pure tin on nickel plating.

The result of the determined production is verified by an extensive testing procedure on 100 % of the individual chip resistors. Only accepted products are laid directly into the tape in accordance with **IEC 60286-3 Type 1a and Type 2a** <sup>(1)</sup>.

#### **ASSEMBLY**

The resistors are suitable for processing on automatic SMD assembly systems. They are suitable for automatic soldering wave, reflow or vapor phase as shown in **IEC 61760-1** <sup>(1)</sup>. The encapsulation is resistant to all cleaning solvents commonly used in the electronics industry, including alcohols, esters and aqueous solutions. The suitability of conformal coatings, potting compounds and their processes, if applied, shall be qualified by appropriate means to ensure the long-term stability of the whole system.

The resistors are RoHS-compliant, the pure tin plating provides compatibility with lead (Pb)-free and lead-containing soldering processes. Solderability is specified for 2 years after production or requalification. The permitted storage time is 20 years. The immunity of the plating against tin whisker growth has been proven under extensive testing.

#### **MATERIALS**

Vishay acknowledges the following systems for the regulation of hazardous substances:

- IEC 62474, Material Declaration for Products of and for the Electrotechnical Industry, with the list of declarable substances given therein (2)
- The Global Automotive Declarable Substance List (GADSL) (3)
- The REACH regulation (1907/2006/EC) and the related list of substances with very high concern (SVHC) (4) for its supply chain

The products do not contain any of the banned substances as per IEC 62474, GADSL, or the SVHC list, see <a href="https://www.vishay.com/how/leadfree">www.vishay.com/how/leadfree</a>.

Hence the products fully comply with the following directives:

- 2000/53/EC End-of-Life Vehicle Directive (ELV) and Annex II (ELV II)
- 2011/65/EU Restriction of the Use of Hazardous Substances Directive (RoHS) with amendment 2015/863/EU
- 2012/19/EU Waste Electrical and Electronic Equipment Directive (WEEE)

Vishay pursues the elimination of conflict minerals from its supply chain, see the Conflict Minerals Policy at www.vishay.com/doc?49037.

#### **APPROVALS**

The resistors are qualified according to AEC-Q200. Where applicable, the resistors are tested in accordance with **EN 140401-802** which refers to **EN 60115-1**, **EN 60115-8** and the variety of environmental test procedures of the **IEC 60068** <sup>(1)</sup> series.

#### **RELATED PRODUCTS**

For more information about products with superior surge and pulse performance please refer to datasheet: D/CRCW-IF e3, Pulse Proof Thick Film Chip Resistors www.vishay.com/doc?20024.

For thick film resistors with standard requirements for power rating, please refer to datasheet: D/CRCW e3, Standard Thick Film Chip

www.vishay.com/doc?20035.

For anti-surge products and high power rating, please refer to datasheet:

RCS e3, Anti-Surge High Power Thick Film Chip Resistors www.vishay.com/doc?20065.

#### Notes


- (1) The quoted IEC standards are also released as EN standards with the same number and identical contents
- (2) The IEC 62474 list of declarable substances is maintained in a dedicated database, which is available at http://std.iec.ch/iec62474
- (3) The Global Automotive Declarable Substance List (GADSL) is maintained by the American Chemistry Council and available at <a href="https://www.gadsl.org">www.gadsl.org</a>
  (4) The Old British of the Substance List (GADSL) is maintained by the American Chemistry Council and available at <a href="https://www.gadsl.org">www.gadsl.org</a>

(4) The SVHC list is maintained by the European Chemical Agency (ECHA) and available at http://echa.europa.eu/candidate-list-table




#### **FUNCTIONAL PERFORMANCE**

#### Single Pulse




Maximum pulse load, single pulse; applicable if  $\bar{P} \to 0$  and n < 1000 and  $\hat{U} \le \hat{U}_{max}$ ; for permissible resistance change equivalent to 8000 h operation

#### **Continuous Pulse**




Maximum pulse load, continuous pulses; applicable if  $\bar{P} \leq P \ (\vartheta_{amb})$  and  $\hat{U} \leq \hat{U}_{max}$ ; for permissible resistance change equivalent to 8000 h operation

### **Pulse Voltage**



Maximum pulse voltage, single and continuous pulses; applicable if  $\hat{P} \leq \hat{P}_{max}$ .; for permissible resistance change equivalent to 8000 h operation

### **Derating**





Vishay Draloric

#### **TESTS AND REQUIREMENTS**

All executed tests are carried out in accordance with the following specifications:

EN 60115-1, generic specification

EN 60115-8 (successor of EN 140400), sectional specification

EN 140401-802, detail specification

IEC 60068-2-xx, test methods

The parameters stated in the Test Procedures and Requirements table are based on the required tests and permitted limits of EN 140401-802. The table presents only the most important tests, for the full test schedule refer to the documents listed above. However, some additional tests and a number of improvements against those minimum requirements have been included.

The testing also covers most of the requirements specified by EIA/IS-703 and JIS-C-5201-1.

The tests are carried out under standard atmospheric conditions in accordance with IEC 60068-1, 4.3, whereupon the following values are applied:

Temperature: 15 °C to 35 °C

Relative humidity: 25 % to 75 %

Air pressure: 86 kPa to 106 kPa (860 mbar to 1060 mbar).

A climatic category LCT / UCT / 56 is applied, defined by the lower category temperature (LCT), the upper category temperature (UCT), and the duration of exposure in the damp heat, steady state test (56 days).

The components are mounted for testing on boards in accordance with EN 60115-8, 2.4.2 unless otherwise specified.

EN 60115-1 CLAUSE			PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (△F	
			Stability for product types:	STABILITY CLASS 2 OR BETTER	
			CRCW-HP e3	1 Ω to 1 MΩ	
4.5	-	Resistance	-	± 0.5 %; ± 1 %; ± 5 %	
4.8	-	Temperature coefficient	(20 / -55 / 20) °C and (20 / 155 / 20) °C	± 100 ppm/K; ± 200 ppm/K	
4.25.1	_	Endurance at 70 °C	$U = \sqrt{P_{70} \times R}$ or $U = U_{\text{max.}}$ ; whichever is the less severe; 1.5 h on; 0.5 h off		
4.23.1	_	Lindulance at 70 C	70 °C; 1000 h	$\pm$ (2 % $R$ + 0.1 $\Omega$ )	
			70 °C; 8000 h	$\pm$ (4 % R + 0.1 $\Omega$ )	
4.25.3	-	Endurance at upper category temperature	155 °C, 1000 h	± (2 % R + 0.1 Ω)	
4.24	78 (Cab)	Damp heat, steady state	(40 ± 2) °C; 56 days; (93 ± 3) % RH;	± (1 % R + 0.05 Ω)	
4.37	67 (Cy)	Damp heat, steady state, accelerated	$(85 \pm 2) \text{ °C; } (85 \pm 5) \text{ % RH;}$ $U = \sqrt{0.1 \times P_{85} \times R} \le 100 \text{ V;}$ $1000 \text{ h}$	± (2 % R + 0.1 Ω)	
4.23	-	Climatic sequence:	-		
4.23.2	2 (Bb)	dry heat	125 °C; 16 h		
4.23.3	30 (Db)	damp heat, cyclic	55 °C; 24 h; ≥ 90 % RH; 1 cycle		
4.23.4	1 (Ab)	cold	-55 °C; 2 h	$\pm (2 \% R + 0.1 \Omega)$	
4.23.5	13 (M)	low air pressure	8.5 kPa; 2 h; (25 ± 10) °C	_ (_ /0// . 0 22)	
4.23.6	30 (Db)	damp heat, cyclic	55 °C; 24 h; ≥ 90 % RH; 5 cycles		
4.23.7	-	DC load	$U = \sqrt{P_{70} \times R} \le U_{\text{max.}}; 1 \text{ min}$		
-	1 (Aa)	Cold	-55 °C; 2 h	± (0.5 % R + 0.05 Ω)	

www.vishay.com Vishay Draloric


IEST PR	UCEDUR	ES AND REQUIR	EMENTS	
EN 60115-1 CLAUSE	IEC 60068-2 <sup>(1)</sup> TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (△R)
·			Stability for product types:	STABILITY CLASS 2 OR BETTER
			CRCW-HP e3	1 Ω to 1 MΩ
4.19	14 (Na)	Rapid change of temperature	30 min at -55 °C and 30 min at 125 °C; 1000 cycles	± (1 % R + 0.05 Ω) no visible damage
4.13	-	Short time overload	$U = 2.5 \text{ x } \sqrt{P_{70} \text{ x } R} \le 2 \text{ x } U_{\text{max.}};$ whichever is the less severe; 5  s	± (2 % R + 0.05 Ω)
4.27	-	Single pulse high voltage overload	Severity no. 4: $U = 10 \text{ x } \sqrt{P_{70} \text{ x } R}$ or $U = 2 \text{ x } U_{\text{max.;}}$ whichever is the less severe; 10 pulses 10 µs/700 µs	± (1 % R + 0.05 Ω) no visible damage
4.39	-	Periodic electric overload	$U = \sqrt{15 \times P_{70} \times R} \text{ or } $ $U = 2 \times U_{\text{max.}};$ whichever is the less severe; $0.1 \text{ s on; } 2.5 \text{ s off;}$ $1000 \text{ cycles}$	± (1 % R + 0.05 Ω) no visible damage
4.38	-	Electrostatic discharge (human body model)	IEC 61340-3-1 <sup>(1)</sup> ; 3 pos. + 3 neg. discharges; ESD voltage acc. to the size	± (1 % R + 0.05 Ω)
4.22	6 (Fc)	Vibration	Endurance by sweeping; 10 Hz to 2000 Hz; no resonance; amplitude ≤ 1.5 mm or ≤ 200 m/s²; 7.5 h	± (0.5 % R + 0.05 Ω) no visible damage
4.17	58 (Td)	Solderability	Solder bath method; Sn60Pb40 non-activated flux; $(235 \pm 5)$ °C; $(2 \pm 0.2)$ s Solder bath method; Sn96.5Ag3Cu0.5 non-activated flux; $(245 \pm 5)$ °C;	Good tinning (≥ 95 % covered) no visible damage
4.18	58 (Td)	Resistance to soldering heat	(3 ± 0.3) s  Solder bath method (260 ± 5) °C; (10 ± 1) s	± (0.5 % R + 0.05 Ω)
4.29	45 (XA)	Component solvent resistance	Isopropyl alcohol; +50 °C; method 2	No visible damage
4.32	21 (Uu <sub>3</sub> )	Shear (adhesion)	CRCW0402-HP and CRCW0603-HP: 9 N CRCW0805-HP to CRCW2512-HP: 45 N	No visible damage
4.33	21 (Uu <sub>1</sub> )	Substrate bending	Depth 2 mm; 3 times	$\pm$ (0.25 % $R$ + 0.05 $\Omega$ ) no visible damage, no open circuit in bent position
4.7	-	Voltage proof	$U = 1.4 \times U_{ins}$ ; 60 s	No flashover or breakdown
4.35	-	Flammability, needle flame test	IEC 60695-11-5 <sup>(1)</sup> ; 10 s	No burning after 30 s

#### Note

<sup>(1)</sup> The quoted IEC standards are also released as EN standards with the same number and identical contents








DIMENSIONS AND MASS								
TYPE / SIZE	L (mm)	W (mm)	H (mm)	T1 (mm)	T2 (mm)	MASS (mg)		
CRCW0402-HP e3	1.0 ± 0.05	0.5 ± 0.05	0.3 ± 0.10	0.25 ± 0.10	0.2 ± 0.10	0.65		
CRCW0603-HP e3	1.6 ± 0.10	0.85 ± 0.10	0.45 ± 0.10	0.3 ± 0.20	0.3 ± 0.20	2		
CRCW0805-HP e3	2.0 ± 0.15	1.25 ± 0.15	0.5 ± 0.10	0.4 ± 0.20	0.35 ± 0.20	5.5		
CRCW1206-HP e3	3.1 ± 0.20	1.6 ± 0.15	0.5 ± 0.15	0.5 ± 0.20	0.45 ± 0.20	10		
CRCW1210-HP e3	3.2 ± 0.20	2.5 ± 0.20	0.6 ± 0.10	0.45 ± 0.20	0.4 ± 0.20	18		
CRCW1218-HP e3	3.1 ± 0.20	4.6 ± 0.20	0.6 ± 0.10	0.45 ± 0.20	0.4 ± 0.20	31		
CRCW2010-HP e3	5.0 ± 0.15	2.5 ± 0.15	0.6 ± 0.10	0.6 ± 0.20	0.6 ± 0.20	25.5		
CRCW2512-HP e3	6.3 ± 0.20	3.15 ± 0.15	0.6 ± 0.10	0.6 ± 0.20	0.6 ± 0.20	42		

#### **SOLDER PAD DIMENSIONS**



RECOMMENDED SOLDER PAD DIMENSIONS								
	WAVE SOLDERING				REFLOW SOLDERING			
TYPE / SIZE	G (mm)	Y (mm)	X (mm)	Z (mm)	G (mm)	Y (mm)	X (mm)	Z (mm)
CRCW0402-HP e3	-	-	-	=	0.45	0.6	0.6	1.65
CRCW0603-HP e3	0.65	1.10	1.25	2.85	0.75	0.75	1.00	2.25
CRCW0805-HP e3	0.90	1.30	1.60	3.50	1.00	0.95	1.45	2.90
CRCW1206-HP e3	1.40	1.40	1.95	4.20	1.50	1.05	1.8	3.60
CRCW1210-HP e3	1.80	1.45	2.95	4.70	1.70	1.10	2.80	3.90
CRCW1218-HP e3	1.60	1.50	5.10	4.60	1.70	1.10	4.90	3.90
CRCW2010-HP e3	3.60	1.65	2.85	6.90	3.70	1.20	2.70	6.10
CRCW2512-HP e3	4.90	1.60	3.50	8.10	5.00	1.25	3.35	7.50

#### **Notes**

<sup>•</sup> The given solder pad dimensions reflect the considerations for board design and assembly as outlined e.g in standards IEC 61188-5-x (1) or in publication IPC-7351.

Still, the given solder pad dimensions will be found adequate for most general applications

<sup>(1)</sup> The quoted IEC standards are also released as EN standards with the same number and identical contents



## **Legal Disclaimer Notice**

Vishay

### **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

# Vishay:

CRCW12062K00FKEAHF	CRCW120610K0FKEAH	CRCW201010R0FKEFHF	CRCW1206100KFKEAHP
CRCW120615K0FKEAHP	CRCW12061R00JNEAHP	CRCW120610R0FKEAHP	CRCW12061K00FKEAHP
CRCW04020000Z0EDHP	CRCW06030000Z0EAHP	CRCW12060000Z0EAHP	CRCW08050000Z0EAHP
CRCW0603100KFKEAHP	CRCW121012R0JNEAHP	CRCW12103K30FKEAHP	CRCW1210750RFKEAHP
CRCW1210150RFKEAHP	CRCW04021K00FKEDHP	CRCW040210K0FKEDHP	CRCW060310K0FKEAHP
CRCW06031K00FKEAHP	CRCW08051K00FKEAHP	CRCW080510K0FKEAHP	CRCW251210R0FKEGHP
CRCW2512100RFKEGHP	CRCW201010K0FKEFHP	CRCW2010100RFKEFHP	CRCW20101K00FKEFHP
CRCW25121K00FKEGHP	CRCW080520K0FKEAHP	CRCW20102K21FKEFHP	CRCW08051R00FKEAHP
CRCW080515R0FKEAHP	CRCW12061R00FKEAHP	CRCW0402100KFKEDHP	CRCW0402100RFKEDHP
CRCW040210R0FKEDHP	CRCW040210R0JNEDHP	CRCW040215K0FKEDHP	CRCW04021K50FKEDHP
CRCW04021M00FKEDHP	CRCW04021R00FKEDHP	CRCW04021R00JNEDHP	CRCW040220K0FKEDHP
CRCW040222R0FKEDHP	CRCW040222R0JNEDHP	CRCW040222R1FKEDHP	CRCW04022K00FKEDHP
CRCW04022R20JNEDHP	CRCW040233R0FKEDHP	CRCW040233R2FKEDHP	CRCW040247K0FKEDHP
CRCW040247R0JNEDHP	CRCW0402499RFKEDHP	CRCW040249K9FKEDHP	CRCW040249R9FKEDHP
CRCW04024K70FKEDHP	CRCW04024K75FKEDHP	CRCW04024K99FKEDHP	CRCW04024R70JNEDHP
CRCW040275R0FKEDHP	CRCW0603100RFKEAHP	CRCW060310R0FKEAHP	CRCW060310R0JNEAHP
CRCW060315K0FKEAHP	CRCW06031K50FKEAHP	CRCW06031M00FKEAHP	CRCW06031R00FKEAHP
CRCW06031R00JNEAHP	CRCW060320K0FKEAHP	CRCW060322R0JNEAHP	CRCW06032K00FKEAHP
CRCW06032R20JNEAHP	CRCW060330K9FKEAHP	CRCW060333R0FKEAHP	CRCW060333R2FKEAHP
CRCW060347K0FKEAHP	CRCW060347R0JNEAHP	CRCW0603499RFKEAHP	CRCW060349R9FKEAHP
CRCW06034K22FKEAHP	CRCW06034K70FKEAHP	CRCW06034K75FKEAHP	CRCW06034K99FKEAHP
CRCW06034R70JNEAHP	CRCW060375R0FKEAHP	CRCW0805100KFKEAHP	CRCW0805100RFKEAHP
CRCW080510R0FKEAHP	CRCW080510R0JNEAHP	CRCW0805150RFKEAHP	CRCW080515K0FKEAHP
CRCW08051K50FKEAHP	CRCW08051M00FKEAHP	CRCW08051R00JNEAHP	CRCW080522R0JNEAHP
CRCW080527K0FKEAHP	CRCW08052K00FKEAHP	CRCW08052K20FKEAHP	CRCW08052R20JNEAHP