
Vishay Dale

CSC

Thick Film Resistor Networks, Single-In-Line, Conformal Coated SIP



www.vishay.com

FEATURES

- Isolated, bussed, and dual terminator schematics available
- Body height: "A" profile = 0.195" (4.95 mm) and "B" profile = 0.295" (7.50 mm) standard; custom "C" profile = 0.350" (8.89 mm) also available



- "A" profile standard in 4 thru 12 pins
- Thick film resistive elements
- · Reduces total assembly costs
- Resistor elements protected by tough epoxy conformal coating
- Wide resistance range (10 Ω to 2.2 MΩ)
- Available in bulk pack as standard; optional tube pack is also available
- Meets EIA/ECA-CB23 rev. G whisker test requirements for class 1A products
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

Note

This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

STANDARD ELECTRICAL SPECIFICATIONS								
GLOBAL MODEL / SCHEMATIC	PACKAGE HEIGHT	POWER RATING ELEMENT ⁽¹⁾ P _{70 °C} W	RESISTANCE RANGE Ω	TEMPERATURE COEFFICIENT (-55 °C to +125 °C) ± ppm/°C	TOLERANCE (2) ± %	TCR TRACKING ⁽¹⁾ (-55 °C to +125 °C) ± ppm/°C	MAX. WORKING VOLTAGE ⁽³⁾ V _{DC}	
	А	0.20	10 to 50	250		50	100	
CSCxxx01	A	0.20	50.1 to 2.2M	100	105			
0300001	В	0.25	10 to 50	250	1, 2, 5			
			50.1 to 2.2M	100				
	А	0.30	10 to 50	250		50	100	
CSCxxx03			50.1 to 2.2M	100	105			
CSCXXXU3	В	0.40	10 to 50	250	1, 2, 5			
			50.1 to 2.2M	100				
	А	A 0.20	10 to 50	250			100	
000,000			50.1 to 2.2M	100	105	150		
CSCxxx05	В	0.25	10 to 50	250	1, 2, 5	150		
			50.1 to 2.2M	100				

Notes

- See derating curves for package power rating
- ⁽¹⁾ For resistor power ratings at +25 °C see derating curves
- $^{(2)}$ \pm 2 % standard, \pm 1 % and \pm 5 % available
- ⁽³⁾ Continuous working voltage shall be $\sqrt{P \times R}$ or maximum working voltage, whichever is less



www.vishay.com


CSC Vishay Dale

GLOBAL PA	GLOBAL PART NUMBER INFORMATION										
New Global Pa	New Global Part Numbering: CSC08A03100RGEK (preferred part number format)										
C S	C S C 0 8 A 0 3 1 0 0 R G E K										
			ATIC	RESISTA	-	TOLERAN	-	P		GING	SPECIAL
ava 04 = 08 = 12 =	HEIC 12 pin ilable 4 pin 5 pin 12 pin HEIC A = "A" B = "B" B = "B"	profile profile 03 = iso 00 = sp	lated ecial	VALUI R = Ω K = kΩ M = M: 10R0 = 1 680K = 68 1M00 = 1.1 0000 = 0 Jumpe	2 Ω Ο Ω 60 kΩ 0 MΩ 0 Ω 2 Ω	$CODE$ $F = \pm 1$ $G = \pm 2$ $J = \pm 5$ $S = spec$ $Z = 0 G$ Jumpe	% % cial 2 er			-free, bulk ad, bulk	Blank = standard (dash number) (up to 3 digits) From 1 to 999 as applicable
Historical Part	Number example	e: CSC08A03101	GEK (w	ill continu	e to be	e accepted	I)				,
CSC	08	A		0	3		101			G	EK
HISTORICAL MODEL	PIN COUN	T PACKA HEIGH		SCHEN	MATIC		ISTAN /ALUE			RANCE ODE	PACKAGING
New Global Pa	rt Numbering: C	SC08A05131AG	EK (pre	ferred par	t num	per format))				
C S	C 0	8 A 0	5	1	3	1	Α	G	Е	К	
GLOBAL MODEL PIN (IATIC	RESISTAI VALUI		TOLERAN		P	ACKAG	aing	SPECIAL
CSC04 to 12 pin available $04 = 4 pin$ $08 = 8 pin$ $A = "A" profileB = "B" profile05 = dualterminator3 digitimpedancecode, followedby alphaF = \pm 1 \%G = \pm 2 \%J = \pm 5 \%EK = lead (Pb)-free, bulkBank = standationBlank = standation(dash number(up to 3 digitsFrom 1 to 999$					Blank = standard (dash number) (up to 3 digits) From 1 to 999 as applicable						
Historical Part	Historical Part Number example: CSC08A05131AGEK (will continue to be accepted)										
CSC	08	Α		05		221		331		G	EK
HISTORICAL MODEL	PIN COUNT	PACKAGE HEIGHT	SCH	EMATIC		ISTANCE ALUE 1		SISTANC ALUE 2	ET	OLERANC CODE	E PACKAGING

Note

• For additional information on packaging, refer to the Through-Hole Network Packaging document (www.vishay.com/doc?31542)

TECHNICAL SPECIFICATIONS				
PARAMETER	UNIT	CSC SERIES		
Voltage coefficient of resistance	V _{eff}	< 50 ppm typical		
Dielectric strength	V _{AC}	200		
Isolation resistance (03 schematic)	Ω	> 100M		
Operating temperature range	°C	-55 to +125		



Revision: 16-Jun-2020

For technical questions, contact: ff2aresistors@vishay.com

Document Number: 31509

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

www.vishay.com

CSC Vishay Dale

01 SCHEMATIC	GLOBAL MODEL	NUMBER OF RESISTORS	A (MAX.)	В	C (MAX.)	
	CSC04	3	0.390 (9.91)	0.300 (7.62)		
	CSC05	4	0.490 (12.45)	0.400 (10.16)		
	CSC06	5	0.590 (14.99)	0.500 (12.70)		
	CSC07	6	0.690 (17.53)	0.600 (15.24)	"A" profile = 0.195 (4.95) "B" profile = 0.295 (7.50)	
	CSC08	7	0.790 (20.07)	0.700 (17.78)		
	CSC09	8	0.890 (22.61)	0.800 (20.32)	Б ргоше = 0.200 (7.00)	
1 2 3 n-1 n	CSC10	9	0.990 (25.15)	0.900 (22.86)		
	CSC11	10	1.09 (27.69)	1.00 (25.40)		
	CSC12	11	1.19 (30.23)	1.100 (27.94)		
	GLOBAL MODEL	NUMBER OF RESISTORS	A (MAX.)	В	С (МАХ.)	
	CSC04	2	0.390 (9.91)	0.300 (7.62)		
	CSC06	3	0.590 (14.99)	0.500 (12.70)		
	CSC08	4	0.790 (20.07)	0.700 (17.78)	"A" profile = 0.195 (4.95) "B" profile = 0.295 (7.50)	
	CSC10	5	0.990 (25.15)	0.900 (22.86)	D prome = 0.200 (7.00)	
1 2 3 4 n-1 n	CSC12	6	1.19 (30.23)	1.100 (27.94)		
05 SCHEMATIC	GLOBAL MODEL	NUMBER OF RESISTORS	A (MAX.)	В	С (МАХ.)	
	CSC04	4	0.390 (9.91)	0.300 (7.62)		
≩ ≩ `R₂≩	CSC05	6	0.490 (12.45)	0.400 (10.16)		
	CSC06	8	0.590 (14.99)	0.500 (12.70)		
$\left \begin{array}{c} \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\$	CSC07	10	0.690 (17.53)	0.600 (15.24)		
	CSC08	12	0.790 (20.07)	0.700 (17.78)	"A" profile = 0.195 (4.95) "B" profile = 0.295 (7.50)	
	CSC09	14	0.890 (22.61)	0.800 (20.32)	2 p. cilic = ci2cc (1.00)	
 1 2 3 n-1 n	CSC10	16	0.990 (25.15)	0.900 (22.86)		
	CSC11	18	1.09 (27.69)	1.00 (25.40)		
	CSC12	20	1.19 (30.23)	1.100 (27.94)		

MECHANICAL SPECIFICATIONS				
Marking resistance to solvents	Permanency testing per MIL-STD-202, method 215			
Solderability	Per MIL-STD-202, method 208E, RMA flux			
Body	High alumina, epoxy coated			
Terminals ⁽¹⁾	Solder plated leads			

Note

⁽¹⁾ Coating meniscus meets class 2 requirements of IPC-A-610

STOCKED RESISTANCE VALUES IN Ω ("G" TOLERANCE)

Standard E-24 resistance values stocked; consult factory. Many dual terminator resistance values stocked; consult factory.

IMPEDANCE CODES						
CODE	R ₁ (Ω)	R ₂ (Ω)	CODE	R ₁ (Ω)	R ₂ (Ω)	
500B	82	130	141A	270	270	
750B	120	200	181A	330	390	
800C	130	210	191A	330	470	
990A	160	260	221B	330	680	
101C	180	240	281B	560	560	
111C	180	270	381B	560	1.2K	
121B	180	390	501C	620	2.7K	
121C	220	270	102A	1.5K	3.3K	
131A	220	330	202B	ЗК	6.2K	

Note

• For additional impedance codes, refer to the Dual Terminator Impedance Code Table document (www.vishay.com/doc?31530)


Revision: 16-Jun-2020

For technical questions, contact: <u>ff2aresistors@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>

CSC Vishay Dale




"A" Profile



"A" PROFILE +70 °C PACKAGE RATINGS CSC12A 1.5 W 1.37 W CSC11A CSC10A 1.25 W CSC09A 1.12 W CSC08A 1.00 W CSC07A 0.87 W CSC06A 0.75 W CSC05A 0.62 W CSC04A 0.40 W

"B" PROFILE +70 °C PACKAGE RATINGS					
CSC12B	1.90 W				
CSC11B	1.75 W				
CSC10B	1.60 W				
CSC09B	1.45 W				
CSC08B	1.30 W				
CSC07B	1.15 W				
CSC06B	1.00 W				
CSC05B	0.80 W				
CSC04B	0.60 W				


"B" Profile



Vishay Dale

www.vishay.com





PERFORMANCE						
TEST	CONDITIONS	MAX. ΔR (TYPICAL TEST LOTS)				
Thermal shock	5 cycles between -65 °C and +125 °C	± 0.50 % ΔR				
Short time overload	2.5 x rated working voltage, 5 s	± 0.25 % ΔR				
Low temperature operation	45 min at full rated working voltage at -65 °C	± 0.25 % ΔR				
Moisture resistance	240 h with humidity ranging from 80 % RH to 98 % RH	± 1.00 % ΔR				
Resistance to soldering heat	Leads immersed in +350 $^\circ\text{C}$ solder to within 1/16" of body for 3 s	± 0.25 % ΔR				
Shock	Total of 18 shocks at 100 g's	± 0.25 % ΔR				
Vibration	12 h at maximum of 20 g 's between 10 Hz and 2000 Hz	± 0.25 % ΔR				
Load life	1000 h at +70 °C, rated power applied 1.5 h "ON", 0.5 h "OFF" for full 1000 h period; derated according to the curve	± 1.00 % ∆R				
Terminal strength	4.5 pound pull for 30 s	± 0.25 % ΔR				
Insulation resistance	10 000 MΩ (minimum)	-				
Dielectric withstanding voltage	No evidence of arcing or damage (200 V_{RMS} for 1 min)	-				



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

CSC10A0382K0GPA CSC10A03150RGPA CSC08A0333R0GPA CSC09B0110K0GPA CSC10B014K70FPA CSC10C0147K0GPA CSC07A01102G CSC10A01220RGDA CSC08A03820RGPA CSC10C011K00GPA CSC10A01100KFEJ CSC10A0110K0GPA109 CSC08A05750AFEK CSC06A0122K0GEK CSC06A012K20GEK CSC06A014K70GEK CSC08A01100KGEK CSC08A03100KGEK CSC08A03100RGEK CSC08A032K00GEK CSC08A0347R0GEK CSC08A0356R0GEK CSC09A01470RGEK CSC10A0122K0GEK CSC10A01470RGEK CSC10A0147K0GEK CSC10A031K00GEK CSC10A05121BGEK CSC04A03560RGEK CSC10B01100RGEK CSC05A0110K0GEJ CSC08A0322K0FEK CSC08A03331RFEK CSC08B012K00GEJ CSC09A01330RJEK