

PRODUCT-DETAILS

PSR37-600-70 PSR37-600-70 Softstarter



General Information	
Global Commercial Alias	PSR37-600-70
Extended Product Type	PSR37-600-70
Product ID	1SFA896110R7000
ABB Type Designation	PSR37-600-70
EAN	7320500338322
Catalog Description	PSR37-600-70 Softstarter
Long Description	The softstarter PSR37-600-70 has a rated maximum operational current of 37 A with an operating voltage span from 208600 V AC. The rated control voltage is between 100240 V AC at 50/60 Hz. PSR features a two-phase control soft start and stop through a voltage ramp. It has a built-in bypass for easy installation and energy saving. A RUN and a TOR signal is available from a relay output in NO (normally open state). The start/stop ramp and time is easy to set by three potentiometers on the front. PSR is often used in combination with a manual motor starter (MMS) from ABB, so mechanical connection kits are available. Another popular option is Fieldbus communication, which can be enabled by an external adaptor and a Fieldbus plug. The PSR range is our most compact softstarters with basic functionality and values. They are suitable for small three-phase motors with nominal currents from 3105 A and can manage up to 100 starts per hour. Common applications are, for example, pumps, fans, compressors, and conveyors.

Ordering	
Minimum Order Quantity	1 piece
Customs Tariff Number	85044090

Popular Downloads	
Data Sheet, Technical Information	1SFC132012C0201
Instructions and Manuals	1SFC132032M0001

Dimensions	
Product Net Width	153 mm
Product Net Height	187 mm
Product Net Depth / Length	54 mm
Product Net Weight	1 kg

Technical	
Rated Operational Voltage	208 600 V AC
Rated Control Supply Voltage (U _s)	100 240 V AC
Rated Control Circuit Voltage (U _C)	50 Hz / 60 Hz 100 240 V AC DC Operation 24 V
Rated Frequency (f)	50/60 Hz Main Circuit 50 / 60 Hz
Rated Operational Power - In-Line Connection (Pe)	(230 V) 7.5 kW (400 V) 18.5 kW (500 V) 22 kW
Rated Operational Current - In-Line Connection (Ie)	37 A
Service Factor Percentage	100 %
Overload Protection	Recommended MS450 28 40
Integrated Electronic Overload	No
Adjustable Rated Motor Current le	No
Starting Capacity at Maximum Rated Current Ie	4xle for 6s
Ramp Time	0 20 second [unit of time] 1 10 second [unit of time]
Initial Voltage During Start	40 70 %
Step Down Voltage Special Ramp	100 60 %
Current Limit Function	Να
Switch for Inside Delta Connection	No
Run Signal Relay	Yes
By-pass Signal Relay	Yes
Fault Signal Relay	Nc
Overload Signal Relay	Nc
Signal indication completed start ramp (LED)	Greer
Signal indication ready to start/standby ON (LED)	Green
Signal indication running R (LED)	Greer

Package Level 1 EAN Package Level 1 Units

Signal indication ramping up/down (LED)	Green
Number of Starts Per	10
Hour at 3.5*le for 7 sec.	
50% ON Time 50% OFF Time	
Communication	FiledBusPlug(Optional
Degree of Protection	IP10
Terminal Type	Screw Terminals
Connecting Capacity	Rigid 1x 6 35 mm ²
Main Circuit	Rigid 2 x 6 16 mm ⁴
Connecting Capacity	1 x 0.75 2.5
Control Circuit	2 x 0.75 2.5 mm ⁱ Rigid 1 x 0.75 2.5 mm ⁱ
	Rigid 2 x 0.75 2.5 mm
Connecting Capacity	Rigid 1 x 0.75 2.5 mm ²
Supply Circuit	
Tightening Torque	Control Circuit 0.6 N·m
	Main Circuit 4 N·m
Droduct Main Tuno	Supply Circuit 0.6 N·m PSR37
Product Main Type	-2421 -2421
Technical UL/CSA	
Maximum Operating	Main Circuit 600 V
Voltage UL/CSA	
Ampere Rating UL/CSA	34 A
Tightening Torque UL/CSA	Control Circuit 5.3 in Ib Main Circuit 35.4
	Supply Circuit 5.3 in Ib
Environmental Ambient Air Temperature	Operation -25 +60 °C Storage -40 +70 °C
RoHS Status	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Certificates and Declarations	(Document Number)
CQC Certificate	CQC2006010304208083
Declaration of	2020980304001085
Conformity - CCC	
Declaration of	1SFA1-91
Conformity - CE	
Environmental Information	1SFC132038D0201
Instructions and Manuals	1SFC132032M0001
RoHS Information	1SFC132031D0202
Container Information	
Container Information	163 mm
Package Level 1 Width	
Package Level 1 Width Package Level 1 Depth /	
Package Level 1 Width Package Level 1 Depth / Length	56 mr
Container Information Package Level 1 Width Package Level 1 Depth / Length Package Level 1 Height Package Level 1 Gross	56 mm 217 mm
Package Level 1 Width Package Level 1 Depth / Length Package Level 1 Height	163 mm 56 mm 217 mm 1.1 kg

7320500338322

box 1 piece

Classifications	
Object Classification Code	Q
ETIM 4	EC002572 - Electronic motor control and protection device
ETIM 5	EC002572 - Electronic motor control and protection device
ETIM 6	EC002572 - Motor management device
UNSPSC	39121521

Categories

 $\mathsf{Drives} \to \mathsf{Softstarters} \to \mathsf{Softstarters} \to \mathsf{PSR}\,\mathsf{Softstarters} \to \mathsf{PSR37}$

Low Voltage Products and Systems \rightarrow Control Products \rightarrow Softstarters \rightarrow Softstarters \rightarrow PSR Softstarters \rightarrow PSR37





