


MOUNTING HOLE LAYOUT



CABLE STRIP DIMENSIONS

NOTES: UNLESS OTHERWISE SPECIFIED.

1. MATERIAL & FINISH:

- 1.1 BODY : (142-9003-201) GOLD PLATED COPPER ALLOY
(142-9003-204) SILVER PLATED COPPER ALLOY
- 1.3 CRIMP SLEEVE: GOLD PLATED COPPER
(142-9003-204) SILVER PLATED COPPER

2. ELECTRICAL SPECIFICATIONS:

- 2.1 CABLE ACCEPTABILITY: RG 188, RG 316, RG 161,
RG 174, RG 179, RG 187
- 2.2 CABLE HEX CRIMP SIZE: .128
- 2.3 CABLE RETENTION: 20 LBS MIN OR CABLE BREAKING STRENGTH.

3. CONNECTOR MARKED "NM" FOR NON-MAGNETIC.

<p>This PROPRIETARY Document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not to be traced or copied without permission and is returnable upon demand.</p> <p>INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2009.</p>	<p>3RD ANGLE PROJECTION</p>	<p>JOHNSON</p>		
	<p>RoHS2 <input checked="" type="checkbox"/> 2011/65/EU</p>	<p>Title: CABLE TERMINATION STR PC MOUNT RG 316 NON-MAGNETIC</p>		<p>Model No.</p>
<p>UNLESS OTHERWISE SPECIFIED UNITS: INCH</p>		<p>.XX ±.02</p> <p>.XXX ±.005</p> <p>ANGLES ±2°</p>	<p>142-9003-201/210</p>	<p>Sheet 1 OF 1</p>
<p>Size B</p>		<p>DO NOT SCALE DRAWING</p>	<p>Date 8/09/2016</p>	<p>1 OF 1</p>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[142-9003-201](#)