

100V PNP MEDIUM POWER TRANSISTOR IN SOT223

Features

- BV_{CEO} > -100V
- $BV_{ECO} > -7V$
- I_C = -2A High Continuous Current
- Low Saturation Voltage V_{CE(sat)} < -130mV @ -1A
- $R_{CE(sat)} = 100 m\Omega$
- Complementary NPN Type: ZXTN19100CG
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability

Mechanical Data

- Case: SOT223
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads. Solderable per MIL-STD-202, Method 208 @3
- Weight: 0.112 grams (Approximate)


Applications

- Motor Drive
- High Side Driver






Top View



Device Symbol



Top View Pin-Out


Ordering Information (Note 4)

	Product	Compliance	Marking	Reel size (inches)	Tape width (mm)	Quantity per reel
ZXTF	P19100CGTA	AEC-Q101	ZXTP19100C	7	12	1,000

Notes:

- 1. EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant. All applicable RoHS exemptions applied.
- 2. See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + CI) and -1000ppm antimony compounds.
 4. For packaging details, go to our website at http://www.diodes.com/products/packages.html.

Marking Information



ZXTP19100C = Product Type Marking Code YWW = Date Code Marking Y or \overline{Y} = Last Digit of Year (ex: 5= 2015) WW or $\overline{W}W = \text{Week Code } (01~53)$



Absolute Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Collector-Base Voltage	V _{CBO}	-110	V
Collector-Emitter Voltage (forward blocking)	V _{CEX}	-110	V
Collector-Emitter Voltage	V _{CEO}	-100	V
Emitter-Collector Voltage (reverse blocking)	V _{ECO}	-7	V
Emitter-Base Voltage	V _{EBO}	-7	V
Continuous Collector Current	Ic	-2	А
Base Current	I _B	-1	Α
Peak Pulse Current	Ісм	-3	Α

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit		
	(Note 5)		1.2 9.6		
Power Dissipation	(Note 6)		1.6 12.8	W mW/°C	
Linear Derating Factor	(Note 7)	P _D	3 24		
	(Note 8)		5.3 42		
	(Note 5)		104		
Thermal Decistores Junction to Ambient	(Note 6)		78		
Thermal Resistance, Junction to Ambient	(Note 7)	R _{θJA}	42	°C/W	
	(Note 8)		23.5		
Thermal Resistance, Junction to Lead (Note 9)		$R_{ heta JL}$	16		
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +150	°C		

ESD Ratings (Note 10)


Characteristic	Symbol	Value	Unit	JEDEC Class
Electrostatic Discharge - Human Body Model	ESD HBM	4,000	V	3A
Electrostatic Discharge - Machine Model	ESD MM	400	V	С


Notes:


- 5. For a device mounted with the collector lead on 15mm x 15mm 1oz copper that is on a single-sided 1.6mm FR4 PCB; device is measured under still air conditions whilst operating in steady-state.
- 6. Same as Note 6, except the device is mounted on 25mm x 25mm 1oz copper.
- 7. Same as Note 6, except the device is mounted on 50mm x 50mm 2oz copper.
- 8. Same as Note 8 measured at t<5 seconds.
- 9. Thermal resistance from junction to solder-point (at the end of the collector lead).
- 10. Refer to JEDEC specification JESD22-A114 and JESD22-A115.




Thermal Characteristics and Derating Information (@TA = +25°C, unless otherwise specified.)










Transient Thermal Impedance

Pulse Power Dissipation



Derating Curve




Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
Collector-Base Breakdown Voltage	BV _{CBO}	-110	-135	-	V	$I_{C} = -100 \mu A$
Collector-Emitter Breakdown Voltage (Note 11)	BV _{CEO}	-100	-135	-	V	I _C = -10mA
Collector-Base Breakdown Voltage (forward blocking)	BV_CEX	-110	-130			I _C = -100μA
Emitter-Collector Breakdown Voltage (reverse blocking)	BV _{ECX}	-7	-8.3	_	V	$I_C = -100\mu A$, $R_{BC} < 1k\Omega$ or $0.25V < V_{BC} > -0.25V$
Emitter-Collector Breakdown Voltage (reverse blocking)	BV _{ECO}	-7	-8.7	-	٧	I _E = -100μA
Emitter-Base Breakdown Voltage	BV_EBO	-7	-8.3	-	٧	$I_E = -100 \mu A$
Collector Cut-Off Current	1	_	< 1	-50	nA	V _{CB} = -110V
Collector Cut-Oil Current	I _{CBO}	_	-	-0.5	μΑ	$V_{CB} = -110V, T_A = +100$ °C
Emitter Cut-Off Current	I _{EBO}	_	< 1	-50	nA	$V_{EB} = -5.6V$
	V _{CE(sat)}	_	-100	-130	mV	$I_C = -500 \text{mA}, I_B = -20 \text{mA}$
Collector-Emitter Saturation Voltage (Note 11)		_	-100	-125	mV	$I_C = -1A$, $I_B = -100mA$
Collector-Entitler Saturation voltage (Note 11)		_	-180	-230	mV	$I_C = -1A$, $I_B = -50mA$
		_	-220	-295	mV	$I_C = -2A$, $I_B = -200mA$
Base-Emitter Saturation Voltage (Note 11)	V _{BE(sat)}	_	-890	-1,000	mV	$I_C = -2A$, $I_B = -200mA$
Base-Emitter Turn-On Voltage (Note 11)	$V_{BE(on)}$	_	-840	-950	mV	$I_C = -2A$, $V_{CE} = -2V$
	h _{FE}	200	300	500		$I_C = -100 \text{mA}, V_{CE} = -2 \text{V}$
DC Current Gain (Note 11)		70	130	-	Ī	$I_C = -1A$, $V_{CE} = -2V$
		20	28	-	I	$I_C = -2A$, $V_{CE} = -2V$
Current Gain-Bandwidth Product (Note 11)	f⊤	-	142	_	MHz	$V_{CE} = -10V, I_{C} = -100mA,$ f = 50MHz
Input Capacitance (Note 11)	C _{ibo}	_	291	400	pF	$V_{EB} = -0.5V$, $f = 1MHz$
Output Capacitance (Note 11)	C _{obo}	_	23.5	40	pF	V _{CB} = -10V, f = 1MHz
Delay Time	t _d	_	24.7		ns	1 500 - 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1
Rise Time	t _r	_	22.4	_	ns	$I_{C} = -500 \text{mA}, V_{CC} = -10 \text{V},$
Storage Time	t _s	_	660		ns	$I_{B1} = -I_{B2} = -50 \text{mA}$ $R_b = 100 \text{W}, R_c = 20 \text{W}$
Fall Time	t _f	_	107	-	ns	ND - 1000V, NC = 20VV

Note: 11. Measured under pulsed conditions. Pulse width \leq 300 μ s. Duty cycle \leq 2%.




Typical Electrical Characteristics (@TA = +25°C, unless otherwise specified.)





Package Outline Dimensions


Please see AP02002 at http://www.diodes.com/datasheets/ap02002.pdf for the latest version.



SOT223					
Dim	Min	Max	Тур		
Α	1.55	1.65	1.60		
A1	0.010	0.15	0.05		
b	0.60	0.80	0.70		
b1	2.90	3.10	3.00		
С	0.20	0.30	0.25		
D	6.45	6.55	6.50		
Е	3.45	3.55	3.50		
E1	6.90	7.10	7.00		
е	-	-	4.60		
e1	-	-	2.30		
L	0.85	1.05	0.95		
Q	0.84	0.94	0.89		
All Dimensions in mm					

Suggested Pad Layout

Please see AP02001 at http://www.diodes.com/datasheets/ap02001.pdf for the latest version.



Dimensions	Value (in mm)		
С	2.30		
C1	6.40		
X	1.20		
X1	3.30		
Y	1.60		
Y1	1.60		
Y2	8 00		



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2015, Diodes Incorporated

www.diodes.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated: ZXTP19100CGTA