













MICRO SWITCH Safety Switch Comparison



Design	Cable Pull			Mechanical Actuation				Key Actuation				
Series	1CPS	2CPS	CLSX	GSX	GSA	GSS Hinge	924/24CE	GKR/L	GK	GKE	GKM	GKN
												
Typical applications	Conveyor systems, perimeter guarding, packaging equipment, assembly lines			Position detection, mechanical travel limits, drift detection, machine tools, material handling, doors, apertures				Doors, apertures, safety interlock, cabinet power isolation, and guard detection				
Certifications	UL, CSA, CE, SIL3	UL, CSA, CE, SIL3	UL, CSA	cULus, CE, IEC Ex, INMETRO, KOSHA, SIL3	UL, CSA, CE, SIL 3	UL, CSA, CE, SIL 3	CE, cULus, SIL3	UL, CSA, CE, SIL 3	UL, CSA, CE, SIL 3	cULus, CE, SIL3	UL, CSA, CE, SIL3	cULus, CE, CCC, SIL3
Mounting centers (mm)	152 x 72	139 x 104	120 x 30	120 x 30	30 x 60	20	25	100 x 100	30 x 60	20	22	40
Housing	Zinc	Zinc	Aluminium	Aluminium	Zinc	Polyester/Zinc	Zinc	Zinc	Zinc	Polyester	Polyester	Polyester
Body dimensions (l x w [depth] x h (mm))	178 x 99 x 65	152 x 165 x 84	154 x 76 x 72	154 x 76 x 72	121 x 42 x 42	83 x 30 x 30	49 x 40 x 16	110 x 110 x 43	121 x 42 x 42	95 x 30 x 33	69 x 34 x 16	90 x 64 x 30
Environmental sealing	NEMA 1, 4, 13; IP67	NEMA 1, 4, 12, 13; IP67	NEMA 1, 3, 4, 13; IP67	NEMA 1, 3, 4, 12, 13; IP67	NEMA 1, 4, 12, 13; IP66 & IP67	NEMA 1, 4 (zinc housing only), 12, 13; IP66	IP66	NEMA 1, 4, 6P, 12, 13; IP68	NEMA 1, 4, 12, 13; IP67	NEMA 1, 4X (indoor only), 12, 13; IP66/67	IP67	NEMA 1, 4X (indoor only), 12, 13; IP67
Operating temperature	-40 °C to 80 °C	-40 °C to 80 °C	1 °C to 70 °C	-40 °C to 70 °C	-25 °C to 85 °C	-25 °C to 85 °C	0 °C to 70 °C (-40 °C optional)	-25 °C to 40 °C	-25 °C to 85 °C	-25 °C to 85 °C	-25 °C to 85 °C	-25 °C to 70 °C
Circuits	1NC/1NO 2NC/2NO 3NC/1NO 4NC	1NC/1NO 2NC/2NO 3NC/1NO 4NC	1NC 1NC/1NO 2NC 1NO/3NC 2NO/2NC	1NC/1NO 1NC/1NO BBM 1NC/1NO MBB 2NC 2NC/2NO 4NC slow 2NC/1NO BBM 2NC/2NO BBM 3NC/1NO BBM	1NC/1NO 1NC/1NO BBM 1NC/1NO MBB 2NC 2NC/2NO 4NC slow 2NC/1NO BBM 2NC/2NO BBM 3NC/1NO BBM	1NO/1NC snap 2NC slow 4NC slow 2NC/2NO BBM 3NC/1NO BBM	1NC/1NO BBM 1NC/1NO MBB 1NC	2NC/2NO snap 1NC/1NO BBM 2NC/1NO BBM 2NC/2NO BBM 3NC/1NO BBM 2NC 4NC	1NC/1NO snap 2NC/2NO snap 1NC/1NO BBM 1NC/1NO MBB 2NC/1NO BBM 2NC/2NO BBM 2NC/2NO BBM 3NC/1NO BBM 2NC 4NC	1NC/1NO snap 1NC/1NO BBM 2NC slow	1NC/1NO BBM 2NC	2NC/1NO slow 3NC Slow
Electrical	10A th AC15, A300 DC13, Q300	10A th AC15, A300 DC13, Q300	10A th 24 Vdc, 250 Vdc 120 Vac, 240 Vac, 600 Vac	10A th AC15, A300/A600; DC13, Q300	10A th AC15, A300/A600; DC13, Q300	10A th AC15, A300/A600; DC13, Q300	10A th AC15, B300; DC13, R300	10A th AC15, A300; DC13, Q300	10A th AC15, A300/A600; DC13, Q300	10A th AC15, A300/A600; DC13, Q300	5A/2A th AC15, A300: DC13, Q300	10A th AC15, A600: DC13, Q300
Positive opening NC contacts	yes	yes	yes	yes	yes	yes	yes	yes	yes	yes	yes	yes
Connection	Conduit	Conduit	Conduit	Conduit	Conduit	Conduit	Pre-Cabled/Connector	Conduit /Connector	Conduit /Connector	Conduit	Pre-Cabled	Conduit
Contacts	Silver, Gold	Silver, Gold	Silver, Gold	Silver, Gold	Silver, Gold	Silver, Gold	Silver	Silver, Gold	Silver, Gold	Silver	Silver, Gold	Silver
Hazardous approvals	-	-	NEMA 7, Class I Div 1 & 2 Groups B, C, D NEMA 9, Class II Div 1 & 2 Groups E, F, G	Class I (Flammable Gas) Div 1 & 2, Groups B, C, D Class II (Combustible Dust) Div 1 & 2, Groups E, F, G Class III (Combustible Fibers and Filings) Div 1 & 2 ATEX, IEC Ex, INMETRO II 2GD Exd IIC T6 Gb Ex t IIIC IP6X T85°C Db (Tamb -40°C to 70°C)	-	-	-	-	-	-	-	-

Honeywell Sensing and Internet of Things
 9680 Old Bailes Road
 Fort Mill, SC 29707
 800-582-4263
 www.honeywell.com

00XXXX-1-EN IL50 GLO
 July 2017
 © 2017 Honeywell International Inc. All rights reserved.

Find out more

Honeywell serves its customers through a worldwide network of sales offices, representatives and distributors. For application assistance, current specifications, pricing or name of the nearest Authorized Distributor, contact your local sales office. To learn more about Honeywell's sensing and switching products, call +1-815-235-6847 or 1-800-537-6945, visit sensing.honeywell.com, or e-mail inquiries to info.sc@honeywell.com