

HUBER+SUHNER® DATA SHEET

Within Series Adapter: 37_N-50-0-1/133_N

Rev.: C 

Description

Panel adaptor jack/jack, flange mount
N jack (female) / N jack (female)

Interface standards
IEC 61169-16_MIL-STD-348A/304_CECC 22210

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz
VSWR	DC - 12.4 GHz ≤ 1.19 + 0.06 f

Mechanical Data

Number of matings	500
Weight	0.0511 kg

Environmental Data

Operating Temperature 2002/95/EC (RoHS)	-65 °C to 165 °C compliant
--	-------------------------------

Material Data

Piece Parts (N)

Centre contact	Copper Beryllium Alloy
Outer contact	Brass
Body	Brass
Insulator	PFA / PTFE

Piece Parts (N)

Centre contact	Copper Beryllium Alloy
Outer contact	Brass
Body	Brass
Insulator	PFA / PTFE

Surface Plating

Gold Plating (Nickel underplated)
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating

Surface Plating

Gold Plating (Nickel underplated)
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating

Related Documents

Mounting hole	DOU-00008795
---------------	--------------

Ordering Information

Single package	37_N-50-0-1/133_NE
----------------	--------------------



HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!
It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.

HUBER+SUHNER – Excellence in Connectivity Solutions



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com