Air reservoirs

FESTO



Air reservoirs CRVZS FESTO

Technical data

Function CRVZS-0.1/0.4/0.75/2





CRVZS-5/10/20 with condensate drain














Technical data								
Туре		CRVZS-0.1	CRVZS-0.4	CRVZS-0.75	CRVZS-2	CRVZS-5	CRVZS-10	CRVZS-20
Pneumatic connection		G1/8	G1/4		G1/2	G1		
Condensate drain connection		-				G3/8		
Type of mounting		Retaining clip	S		Via through-holes			
Installation position		Any	Any			Condensate drain downwards		
Volume	[l]	0.1 ±20%	0.4 ±20%	0.75 ±20%	2 ±10%	5 ±10%	10 ±10%	20 ±10%
Weight	[g]	226	543	736	1,681	3,581	6,459	10,208

Note: This product conforms to ISO 1179-1 and to ISO 228-1

Operating and environmental co	onditions									
Туре		CRVZS-0.1	CRVZS-0.4	CRVZS-0.75	CRVZS-2	CRVZS-5	CRVZS-10	CRVZS-20		
Operating pressure [b	bar]	-0.95 +16								
Operating medium		Compressed a	ir in accordanc	e with ISO 857	3-1:2010 [-:-:	-]				
		Nitrogen	Nitrogen							
Ambient temperature [°	temperature [°C] -10 +100 (observe operating range of tubing and pipe)									
Temperature of medium [c	°C]	-10 +100 (observe operat	ing range of tul	oing and pipe)					
Corrosion resistance class CRC ¹⁾)	3								
Conforms to standard ²⁾		AD 2000								
CE symbol		-				In accordance with EU Pressure Equipment Directive				
(see declaration of conformity) ²⁾										
Approval ²⁾		German Technical Control Board (TÜV)								
		- CRN								
RISK criterion		-				Pressure equipment	CRN			
Certificate issuing department – CRNOH15669.5C TSSAOH15669.5 CRNOH					CRN0H15669.5C					

¹⁾ CRC3: Corrosion resistance class to Festo standard 940 070 Components with heavy corrosion exposure. Externally visible components in direct contact with normal industrial atmosphere or media such as solvents and cleaning agents, where the surface requirement is predominantly functional.


Additional information www.festo.com/sp → User documentation.

Materials							
Туре	CRVZS-0.1	CRVZS-0.4	CRVZS-0.75	CRVZS-2	CRVZS-5	CRVZS-10	CRVZS-20
Air reservoir	High-alloy sta	High-alloy stainless steel					
Retaining clips	High-alloy sta	High-alloy stainless steel –					
Note on materials	Free of copper and PTFE						
	Conforms to F	Conforms to RoHS					

Air reservoirs CRVZS


FESTO

Technical data




Туре	L	L1		L2	L3	=©	Max. tightening torque
	±1	min.	max.				for connecting thread [Nm]
CRVZS-0.1	132	13	50	10	6	19	15
CRVZS-0.4	240	13	150	14	9	27	23
CRVZS-0.75	248	13	140	14	9	27	23

 $^{\|\}cdot\|$ Note: This product conforms to ISO 1179-1 and to ISO 228-1




· ♦ Note: This product conforms to ISO 1179-1 and to ISO 228-1

Technical data



Note: This product conforms to ISO 1179-1 and to ISO 228-1



Туре	D1	H1	L1	Max. tightening torque	
	±2	±1.5	±3	Connecting thread [Nm]	Condensate drain [Nm]
CRVZS-10	160	115	558	130	27
CRVZS-20	194	136	740	130	27

 $[\]parallel\cdot\parallel$ Note: This product conforms to ISO 1179-1 and to ISO 228-1


Ordering data						
Volume [l]	Part No.	Туре	Volume [l]		Part No.	Туре
0.1 ±20%	160233	CRVZS-0.1	5 ±10%		192159	CRVZS-5
0.4 ±20%	160234	CRVZS-0.4	10 ±10%		160237	CRVZS-10
0.75 ±20%	160235	CRVZS-0.75	20 ±10%		534845	CRVZS-20
2 ±10%	160236	CRVZS-2		·		

Air reservoirs VZS FESTO


Technical data

Function with condensate drain














Technical data		
Туре		VZS-20-B
Pneumatic connection		G1
Condensate drain connection		G3/8
Type of mounting		Via through-holes
Installation position		Condensate drain downwards
Volume	[1]	20 ±10%
Weight	[g]	8,600

 $[\]parallel$ Note: This product conforms to ISO 1179-1 and to ISO 228-1


Operating and environment	perating and environmental conditions					
Туре		VZS-20-B				
Operating pressure	[bar]	-0.95 +16				
Operating medium		Compressed air in accordance with ISO 8573-1:2010 [-:-:-]				
		Nitrogen				
Ambient temperature	[°C]	−10 +100 (observe operating range of tubing and pipe)				
Temperature of medium	[°C]	−10 +100 (observe operating range of tubing and pipe)				
Corrosion resistance class	CRC ¹⁾	4				
Conforms to		EN 286-1				
CE symbol		In accordance with EU Simple Pressure Vessel Directive				
(see declaration of conformit	ty)					

¹⁾ CRC4: Corrosion resistance class to Festo standard 940 070 Components with very heavy corrosion exposure. Components in contact with aggressive media, e.g. in food or chemical industries. These applications must, if necessary, be verified by special tests with the media concerned

Materials	
Air reservoir	Painted steel
Note on materials	Free of copper and PTFE

Air reservoirs VZS FESTO

Technical data



 $[\]parallel\cdot\parallel$ Note: This product conforms to ISO 1179-1 and to ISO 228-1

Ordering data	
Volume [l]	Part No. Type
20 ±10%	192161 VZS-20-B