



Product: [9463F](#)

Blue Hose®, 1 Pr #20 Str TC, PE Ins Blu,Clr, Foil+TC Brd, PVC Jkt, High Flex CM, AWM 2464

[Request Sample](#)

Product Description

Blue Hose® for Data Highway Plus, 1 Pair 20AWG (42x36) Tinned Copper, PE Insulation Blue & Clear, Overall Beldfoil®+Tinned Copper Braid(85%) Shield, Blue PVC Outer Jacket, High Flex, CM, AWM 2464

Technical Specifications

Suitable Applications: robotic, harsh environment, Allen Bradley Data Highway communication interface between PLC processors, I/O devices, operator interfaces, computers and other intelligent devices, PLC processor interlocking, peer-to-peer messaging, remote programming, troubleshooting, I/O updates, etc.

Conductor

Element	Number of Element	AWG	Stranding	Material
Pair(s)	1	20	42x36	TC - Tinned Copper

Insulation

Element	Material	Thickness [in.]	Color Code	Notes
Pair(s)	PE - Polyethylene	0.0185	Clear & Blue	Twinax with rod fillers

Outer Shield Material

Shield Type	Material	Coverage
Tape + Braid	Bi-Laminate (Alum+Poly) + Tinned Copper (TC)	100% + 85%

Outer Jacket Material

Material	Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.033 in	0.243 in

Cable Diameter (Nominal): 0.243 in

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Shield	Characteristic Impedance	Nom. Velocity of Prop.
Pair(s)	9.5 Ohm/1000ft	19.7 pF/ft	37 pF/ft	78 Ohm	66%

High Frequency (Nominal/Typical)

Element	Frequency [MHz]	Nom. Insertion Loss
Pair(s)	1 MHz	0.6 dB/100ft
	10 MHz	2.1 dB/100ft
	50 MHz	5.0 dB/100ft
	100 MHz	7.5 dB/100ft
	200 MHz	11.0 dB/100ft
	400 MHz	16.0 dB/100ft

Voltage

UL Voltage Rating
300 V (CM, CI2)

Temperature

UL Rating	Operating
80°C	-40°C to 80°C

Bend Radius

Stationary Min.	Installation Min.
2.5 in	2.5 in

Max. Pull Tension:	40 lbs
Bulk Cable Weight:	34 lbs/1000ft
Environmental Suitability:	Indoor
Flammability / Fire Resistance:	UL1685 UL Loading, IEC 60332-1-2
NEC / UL Compliance:	Article 725, Article 800, CM, CL2
AWM Compliance:	2464
CEC / C(UL) Compliance:	CM
CPR Euroclass:	Eca
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	P-7K-SC-182141-MSHA
Update and Revision:	Revision Number: 0.265 Revision Date: 09-30-2020

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9463F J221000](#)