



NOTES:

1. MATERIALS AND FINISHES:
 SMPM STR PLUG - BeCu, GOLD PLATING
 CABLE - 0.047 SEMI-RIGID CONFORMABLE
2. ELECTRICAL:
 A. IMPEDANCE: 50 OHM
3. PACKAGING:
 A. QUANTITY: SINGLE PACK
 B. MARKING: BAG TO BE MARKED
 "AMPHENOL RF, 95-725-112-XXX AND DATE CODE"

THIRD ANGLE PROJ.

REVISIONS

REV	DESCRIPTION	DATE	ECN	APPR
A	RELEASE TO MFG.	20-Mar-17	3344	BMG
B	SHEET 1 CHANGE	06-Apr-17	3506	BMG
C	FREQUENCY AND VSWR REQUIREMENTS UPDATED	19-Mar-18	7383	BMG
D	UPDATED CONNECTOR DESIGN AND VSWR REQUIREMENTS	13-Jun-19	11841	EH



LENGTH TABLE		
PART NUMBER (IMPERIAL)	PART NUMBER (METRIC)	LENGTH AND TOLERANCE 'L' IN INCHES [METERS]
95-725-112-030	-	3.00 [0.076]
-	95-725-112M010	3.94 [0.100]
95-725-112-040	-	4.00 [0.102]
95-725-112-050	-	5.00 [0.127]
95-725-112-060	-	6.00 [0.152]
95-725-112-070	-	7.00 [0.178]
95-725-112-080	-	8.00 [0.203]
95-725-112-090	-	9.00 [0.229]
-	95-725-112M025	9.84 [0.250]
95-725-112-100	-	10.00 [0.254]
95-725-112-110	-	11.00 [0.279]
95-725-112-120	-	12.00 [0.305]
95-725-112-180	-	18.00 [0.457]
-	95-725-112M050	19.69 [0.500]
95-725-112-240	-	24.00 [0.610]
-	95-725-112M075	29.53 [0.750]
95-725-112-360	-	36.00 [0.914]
-	95-725-112M100	39.37 [1.000]
95-725-112-480	-	48.00 [1.219]
-	95-725-112M200	78.74 [2.000]

TOLERANCE TABLE	
LENGTH IN INCHES/FT [METERS]	TOLERANCE
0" - 23.90" [0 - 0.607]	±0.25" [0.006]
24.00" - 59.00" [0.610 - 1.499]	±0.50" [0.013]
5.0' - 24.9' [1.524 - 7.617]	±2.5%
25.0' & UP [7.620 & UP]	±5.0%

DESIGN REQUIREMENTS:

- | | |
|---|---|
| <input checked="" type="checkbox"/> FREQUENCY : DC TO 18 GHz | <input checked="" type="checkbox"/> CONTINUITY |
| <input checked="" type="checkbox"/> VSWR : 1.30 MAX @ DC-18 GHz | <input checked="" type="checkbox"/> HI-POT : 500 VRMS |
| <input type="checkbox"/> INS. LOSS: ---- dB MAX | <input type="checkbox"/> OTHER |

CUSTOMER OUTLINE DRAWING
 ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:
 <0.5mm ±0.05mm 0.5 - 6mm ±0.1mm 6 - 30mm ±0.2mm 30 - 120mm ±0.3mm ANGLES ±1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL	DRAWN	DATE	TITLE	Amphenol RF www.amphenolrf.com
-	VIJI K	06-Apr-17	SMPM STR PLUG TO SMPM STR PLUG USING 0.047 SEMI-RIGID CONFORMABLE CABLE, VARIOUS LENGTH	
REFERENCE	ENGINEER	DATE	SCALE: 4.0:1.0 SHEET 2 OF 2	DRAWING NO. 95-725-112-XXX
EAR# 7428	VIJI K	06-Apr-17	DWG SIZE B	ITEM NO. 95-725-112-XXX
REF: --	APPROVED	DATE	REV D	PART NO. 95-725-112-XXX
CONFIGURATION LEVEL: In Work	K. CAPOZZI	13-Jun-19		
FINISH	CAD FILE			