3.0x2.0mm, Blue LED Surface Mount PLCC-2 LED Indicator

Technical Data Sheet

Luckylight

Features:

- PLCC-2 package.
- High reliability LED package.
- Colorless clear window.
- Inter reflector.
- Suitable for automatic placement equipment.
- Suitable for vapor-phase reflow, Infrared reflow and wave solder processes.
- Available on tape and reel (8mm Tape).
- The product itself will remain within RoHS compliant Version.

Descriptions:

 The R3020 series is available in soft red, orange, yellow, green, blue and white. Due to the package design, the LED has wide viewing angle and optimized light coupling by inter reflector. This feature makes the SMT TOP LED ideal for light pipe application. The low current requirement makes this device ideal for portable equipment or any other application where power is at a premium.

Applications:

- Indicator and backlight in office and family equipment.
- Flat backlight for LCD's, switches and symbols.
- Light pipe application.
- General use.


3.0x2.0mm, Blue LED Surface Mount PLCC-2 LED Indicator


Technical Data Sheet



Part No.	Emitting Color	Lens Color		
R3020BC-B4-1B	Blue	Water Clear		

Package Dimension:





Unit: mm Tolerance: ± 0.10 mm

Notes:

- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is \pm 0.25 mm (.010") unless otherwise noted.

Spec No.: R3020 Issue No.: G-Rev-4 Luckylight Electronics Co., Ltd Copyright © 2017 Luckylight All Rights Reserved

Date:	12-Sep-2017
E-mail:	sales@luckylight.cn
http://	www.luckylight.cn
Page:	2 / 10

3.0x2.0mm, Blue LED Surface Mount PLCC-2 LED Indicator

Luckylight

Technical Data Sheet

Absolute Maximum Ratings at Ta=25℃

Parameters	Symbol	Max	Unit
Power Dissipation	Pd	90	mW
Peak Forward Current ^(a)	IFP	100	mA
DC Forward Current ^(b)	IF	25	mA
Reverse Voltage	VR	5	V
Electrostatic Discharge (HBM)	ESD	1000	V
Operating Temperature Range	Topr	-40°C to +80°C	
Storage Temperature Range	Tstg	-40℃ to +85℃	
Soldering Temperature	Tsld	260 $^\circ\!\!\!\mathrm{C}$ for 5 Seconds	

Notes:

a. Derate linearly as shown in derating curve.

b. Duty Factor = 10%, Frequency = 1 kHz

Electrical Optical Characteristics at Ta=25°C

Parameters	Symbol	Min.	Тур.	Max.	Unit	Test Condition
Luminous Intensity ^(a)	IV	200	400		mcd	IF=20mA
Viewing Angle ^(b)	201/2		130		Deg	IF=20mA
Peak Emission Wavelength	λр		468		nm	IF=20mA
Dominant Wavelength ^(C)	λd		470		nm	IF=20mA
Spectral Line Half-Width	Δλ		25		nm	IF=20mA
Forward Voltage	VF	2.80	3.20	3.60	V	IF=20mA
Reverse Current	IR			10	μA	VR=5V

Notes:

a. ALuminous intensity is measured with a light sensor and filter combination that approximates the CIE eye-response curve.

b. 201/2 is the o -axis angle where the luminous intensity is 1/2 the peak intensity


c. The dominant wavelength (λ d) is derived from the CIE chromaticity diagram and represents the single wavelength which defines the color of the device.

Spec No.: R3020 Issue No.: G-Rev-4 Luckylight Electronics Co., Ltd Copyright © 2017 Luckylight All Rights Reserved Date: 12-Sep-2017 E-mail: sales@luckylight.cn http:// www.luckylight.cn Page: 3 / 10

3.0x2.0mm, Blue LED Surface Mount PLCC-2 LED Indicator

Technical Data Sheet

Typical Electrical / Optical Characteristics Curves (25℃ Ambient Temperature Unless Otherwise Noted)



Ta=25℃ 50 40 30 20 10 0 3.4 3.6 3.0 3.2 3.8 2.8 2.6 Forward Voltage VF (V) Luminous Intensity & Forward Current Ta=25℃ Relative Luminous Intensity (%) 1000 f=1KHz Duty=1/10 100 10 1 10° 10^{2} 10^{1} 10^{3} Forward Current IF (mA) **Radiation Diagram** Ta=25℃ 0° 10° 20° 30° 40° 1.0 50° 0.9 60° 0.8 70° 80[°] 0.7 90` 0.5 0.3 0.10 0.2 0.4 0.6

Spec No.: R3020 Issue No.: G-Rev-4 Luckylight Electronics Co., Ltd Copyright © 2017 Luckylight All Rights Reserved

Date: 12-Sep-2017 E-mail: sales@luckylight.cn http:// www.luckylight.cn 4 / 10 Page:




3.0x2.0mm, Blue LED Surface Mount PLCC-2 LED Indicator

Technical Data Sheet

Luckylight


Reel Dimensions:



Unit: mm Tolerance: ± 0.25 mm

Carrier Tape Dimensions:

Loaded quantity 3000 pcs per reel.



Spec No.: R3020 Issue No.: G-Rev-4 Luckylight Electronics Co., Ltd Copyright © 2017 Luckylight All Rights Reserved Date:12-Sep-2017E-mail:sales@luckylight.cnhttp://www.luckylight.cnPage:5 / 10


3.0x2.0mm, Blue LED Surface Mount PLCC-2 LED Indicator

Technical Data Sheet

Luckylight

Packing & Label Specifications:

Moisture Resistant Packaging:



Label Outside Box Side 285 (410) Part No .: XXXXXXXXXXX PO No .: XXXXXX FQC XXXXXX XXXX PCS Lot No .: PASS ~٢ RoHS Quantity: 300 305 Label Outside Bin Code: XXXX Label 475 (465) Date

S	Spec No.: R3020	Date:	12-Sep-2017
ls	ssue No.: G-Rev-4	E-mail:	sales@luckylight.cn
L	uckylight Electronics Co., Ltd	http://	www.luckylight.cn
Copyright © 2017 Luckylight All Rights Reserved		Page:	6 / 10

3.0x2.0mm, Blue LED Surface Mount PLCC-2 LED Indicator


Luckylight

Technical Data Sheet

CAUTIONS

1. Handling Precautions:

- 1.1. Handle the component along the side surfaces by using forceps or appropriate tools.
- 1.2. Do not directly touch or handle the silicone lens surface. It may damage the internal circuitry.
- 1.3. Do not stack together assembled PCBs containing exposed LEDs. Impact may scratch the silicone lens or damage the internal circuitry.



Compare to epoxy encapsulant that is hard and brittle, silicone is softer and flexible. Although its characteristic significantly reduces thermal stress, it is more susceptible to damage by external mechanical force. As a result, special handling precautions need to be observed during assembly using silicone encapsulated LED products. Failure to comply might lead to damage and premature failure of the LED.

2. Storage

- 2.1. Do not open moisture proof bag before the products are ready to use.
- 2.2. Before opening the package, the LEDs should be kept at 30°C or less and 60%RH or less.
- 2.3. The LEDs should be used within a year.
- 2.4. After opening the package, the LEDs should be kept at 30°C or less and 60%RH or less.
- 2.5. The LEDs should be used within 24 hours after opening the package.
- 2.6. If the moisture adsorbent material has fabled away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions. Baking treatment: 65±5°C for 24 hours.

Spec No.: R3020 Issue No.: G-Rev-4 Luckylight Electronics Co., Ltd Copyright © 2017 Luckylight All Rights Reserved Date:12-Sep-2017E-mail:sales@luckylight.cnhttp://www.luckylight.cnPage:7 / 10


3.0x2.0mm, Blue LED Surface Mount PLCC-2 LED Indicator

Luckylight

Technical Data Sheet

3. Soldering Condition:

3.1 Pb-free solder temperature profile.



- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.
- 3.5 Recommended soldering conditions:

Reflow soldering		Soldering iron		
Pre-heat	150~200°C	Temperature	300°C Max.	
Pre-heat time	120 sec. Max.	Soldering time	3 sec. Max.	
Peak temperature	260°C Max.		(one time only)	
Soldering time	10 sec. Max. (Max. two times)			

3.6 Because different board designs use different number and types of devices, solder pastes, reflow ovens, and circuit boards, no single temperature profile works for all possible combinations.

However, you can successfully mount your packages to the PCB by following the proper guidelines and PCB-specific characterization.


3.0x2.0mm, Blue LED Surface Mount PLCC-2 LED Indicator

Technical Data Sheet

Luckylight

4. Drive Method:

4.1 An LED is a current-operated device. In order to ensure intensity uniformity on multiple LEDs connected in parallel in an application, it is recommended that a current limiting resistor be incorporated in the drive circuit, in series with each LED as shown in Circuit A below.



(A) Recommended circuit.

(B) The brightness of each LED might appear different due to the differences in the I-V characteristics of those LEDs.

5. ESD (Electrostatic Discharge):

Static Electricity or power surge will damage the LED. Suggestions to prevent ESD damage:

- Use of a conductive wrist band or anti-electrostatic glove when handling these LEDs.
- All devices, equipment, and machinery must be properly grounded.
- Work tables, storage racks, etc. should be properly grounded.
- Use ion blower to neutralize the static charge which might have built up on surface of the LED's plastic lens as a result of friction between LEDs during storage and handling.

ESD-damaged LEDs will exhibit abnormal characteristics such as high reverse leakage current, low forward voltage, or "no lightup" at low currents. To verify for ESD damage, check for "lightup" and Vf of the suspect LEDs at low currents. The Vf of "good" LEDs should be >2.0V@0.1mA for InGaN product and >1.4V@0.1mA for AlInGaP product.

3.0x2.0mm, Blue LED Surface Mount PLCC-2 LED Indicator

Luckylight

Technical Data Sheet

Terms and conditions for the usage of this document:

1. The information included in this document reflects representative usage scenarios and is intended for technical reference only.

2. The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.

3. When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Luckylight will not be responsible for any subsequent issues.

4. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with Luckylight representative for further assistance.

5. The contents and information of this document may not be reproduced or re-transmitted without permission by Luckylight.

Spec No.: R3020 Issue No.: G-Rev-4 Luckylight Electronics Co., Ltd Copyright © 2017 Luckylight All Rights Reserved Date:12-Sep-2017E-mail:sales@luckylight.cnhttp://www.luckylight.cnPage:10 / 10