Resistors

Electronics

Precision Metal Film Resistors

RC series

- Available to EN140101 & IECQ-CECC40101 release
- Resistance tolerance down to 0.05%
- Wide resistance range
- Low noise and negligible voltage coefficient
- · Screened parts available for critical applications
- Temperature Coefficient of Resistance down to 5 ppm/°C
- Options for RoHS compliant and Lead bearing wire finishes



All Pb-free parts comply with EU Directive 2011/65/EU amended by (EU) 2015/863 (RoHS3)

Electrical Data

Commercial		RC55	RC65	RC70	Notes
Power rating at 70°C	watts	0.25	0.5	1.0	
Resistance range	ohm	1R to 4M	1R to 4M	1R to 10M	
Limiting element voltage	volts	350	350	500	
Isolation voltage	volts	500	750	700	
TCR (20 to +70°C)	ppm/°C		See resistance		
Resistance tolerance	%		restrictions		

EN140101-806 Requirements		В	С		
Power rating at 70°C	watts	0.25	0.5		
Resistance range	ohms	56R – 820K	56R – 1M0		
Limiting element voltage	volts	350	350		
Isolation voltage	volts	500	750		
TCR	ppm/°C		See resistance		
Resistance tolerance	%		restrictions		

IECQ-CECC 40101-004 Requirements		Н	J	K	К	L	
Power rating at 70°C	watts	0.063	0.125	0.25	0.25	0.5	
Resistance range	ohms	1R to 1M	1R to 1M	1R to 1M	10R to 1M	10R to 1M	
Limiting element voltage	volts	200	200	250	250	350	
Isolation voltage	volts	280	280	350	350	500	
TCR	ppm/° C		15, 25, 50, 100				
Resistance tolerance	%		0.05, 0.1, 0.25., 0.5 & 1				

IECQ-CECC 40101-804 Requirements		Α	В	В	С			
Power rating at 70°C	watts	0.125	0.25	0.25	0.5			
Resistance range	ohms	1R to 1M	1R to 1M	10R to 1M	10R to 1M			
Limiting element voltage	volts	200	250	250	350			
Isolation voltage	volts	280	350	350	500			
TCR	ppm/°C		15, 25, 50, 100					
Resistance tolerance	%		0.05, 0.1, 0.25, 0.5 & 1					

These tables indicate the EN140101 & CECC40101 specification requirements, and these are met or exceeded by the corresponding RC series products.

Standard values			E24, E96 preferred		Any value
Thermal impedance	°C/watt	110	to order		
Ambient temperature range	°C				

General Note


Precision Metal Film Resistors



RC series

Physical Data

Dimen	Dimensions (mm) & Weight (g)													
					PCB	Min.								
					mounting	Bend								
Type	L max	D max	f min '	d nom	centres	Radius	Wt. nom							
RC55	7.2	2.5	30	0.6	10.2	0.6	0.24							
RC65	10.0	3.7	30	0.6	12.7	0.6	0.40							
RC70	15.5	5.5	30	0.8	18.4	1.2	1.15							



Note 1 - dimension relates only to bulk packed product.

Construction

A metal film is deposited onto a high quality ceramic former. Nickel-plated steel caps are force fitted to the former and termination wires are welded to the caps.

The resistor is adjusted to value by a helical cut in the film and the body is protected with a specially formulated epoxy coating.

Terminations

Material Solder coated copper wire

Strength The terminations meet the requirements of

IEC 68.2.21.

Solderability The terminations meet the requirements of

IEC 115-1, Clause 4.17.3.2.

Marking

Type reference, TCR code, resistance value and tolerance code.

The resistance values conform to IEC 62.

Solvent Resistance

The body protection and marking are resistant to all normal industrial cleaning solvents suitable for printed circuits.

Performance Data

		EN140101-806	IECQ-CECC 40101-004	IECQ-CECC 40101-804	*Actual Pe	rformance
		Requirements	Requirements	Requirements	Maximum	Typical
Load at commercial rating: 1000 hours at 70°C	∆R%				0.3	0.1
Load at EN140101 & CECC40101 ratings 1000 hours at 70°C	Δ R%	0.25	0.5	0.5	**0.3	0.05
Dry heat: 1000 hours at 155°C	ΔR%	0.25	0.5	0.5	**1.0	0.15
Shelf life: 12 months at room temperature	∆R%	Not Specified	Not specified	Not specified	0.1	0.03
Derating from rated power at 70°C		Zero at 155°C	Zero at 155°C	50% at 125°C	50% at 125℃ 8	Zero at 155°C
Short term overload	∆R%	1	0.1	0.1	0.1	0.02
Climatic	∆R%	0.25	0.5	0.5	**0.3	0.1
Climatic category		55/155/56	55/155/56	55/125/56	55/155/56	
Long term damp heat	∆R%	0.25	0.5	0.5	**0.5	0.1
Temperature rapid change	∆R%	1	0.1	0.1	**0.2	0.05
Resistance to solder heat	∆R%	0.05	0.1	0.1	**0.06	0.03
Vibration and bump	∆R%	0.05	0.1	0.1	**0.06	0.02
Noise (in a decade of frequency)	μV/V	Not Specified	Not specified	Not specified	1.0	0.1
Voltage coefficient of resistance	ppm/V	Not Specified	Not specified	Not specified		<1

Note: *An 0.01 ohm addition to be added to the performance claims of all resistors <10R.

General Note

^{**} All products within the specified approved range meet EN140101 and CECC40101 requirements.

Precision Metal Film Resistors



RC series

Table of Resistance Restrictions

	Tolerance													
TCR		RC55			RC65			RC70						
ppm/°C	0.05%	0.1 - 0.25%	0.5%3 - 1%3	0.05%	0.1 - 0.25%	0.5%³ - 1%³	0.05%	0.1 - 0.25%	0.5%³ - 1%³					
5 ¹	10R to 500K	10R to 500K	1R to 500K	10R to 500K	10R to 500K	1R to 500K	10R to 750K	10R to 750K	10R to 750K					
10	10R to 1M	10R to 1M	1R to 1M	10R to 1M	10R to 1M	1R to 1M	10R to 1M	10R to 1M	1R to 1M					
15	10R to 1M	2R49 to 1M	1R to 1M	10R to 1M	5R to 1M	1R to 1M	10R to 1M	10R to 2M	1R to 2M					
25	10R to 1M	2R49 to 2M	1R to 2M	10R to 1M	5R to 2M	1R to 2M	10R to 1M	10R to 5M	1R to 5M					
50 ²	10R to 1M	2R49 to 2M	1R to 4M	10R to 1M	5R to 2M	1R to 4M	10R to 1M	5R to 10M	1R to 10M					
100²	10R to 1M	1R to 2M	1R to 4M	10R to 1M	1R to 2M	1R to 4M	10R to 1M	1R to 10M	1R to 10M					

Note1:

- 1. Based on sampling. 100% screened product is available.
- 2. For maximum availability, where the ohmic value permits, 25ppm/°C is preferred to 50 or 100ppm/°C.
- 3. For maximum availability, where the ohmic value permits, 0.25% is preferred to 0.5% or 1%

Application Notes


Matched Sets

TT Electronics has many years' experience in the supply of matched sets of precision resistors.

Resistors can be supplied matched for tolerance and TCR down to $\pm 0.02\%$ and $\pm 2ppm^{\circ}C$.

Packaging

RC55 and RC65 standard packing is in tape, as shown below, whilst RC70 is bulk packed. Taped resistors on reel or loose packed components can also be supplied by special request.



Body location $f_1 - f_2 \le 1.4 \text{ mm}$

Precision Metal Film Resistors




RC series

Ordering Procedure

This product has two valid part numbers:

European (Welwyn) Part Number: RC55V-31K6BI (RC55 with TCR ±5ppm/°C at 31.6 kilohms ±0.1%, Pb-free)



1	2	3	4	5			5	
Туре	TCR (ppm/°C)	Value	Tolerance	Finish, Screening & Packing				
RC55	V = ±5	E24 = 3/4 characters	$W = \pm 0.05\%$	- 1		Pb-fr	ee (RoHS)	
RC65	T = ±10	E96 = 4/5 characters	$B = \pm 0.1\%$	SC	Pb-f	ree with screened TCR (5ppm only		
RC70	Y = ±15	R = ohms	$C = \pm 0.25\%$	Sn(95)Pb(5) finish)Pb(5) finish	
	D = ±25	K = kilohms	$D = \pm 0.5\%$	HL		Sn(60)Pb(4	0) high lead finish	
	C = ±50	M = megohms	F = ±1%		Al	l above in St	andard Packing	
	$Z = \pm 100$			RC	555	A mama a	Up to 5000/box	
				RC	65	Ammo	Up to 2500/box	
				RC	70	Bulk	250/box	

For product released to EN140101 or CECC40101, state on order the relevant number and style.

Examples: RC55Y-31K6BI EN140101-806 B RC55Y-31K6BI CECC40101-004 JY

For CECC 40101-804 the TCR codes T and E relate to 15 and 25ppm/°C and are coded in the MPN as Y and D respectively. Also an additional suffix-804 is added after the Finish, Screening & Packing code, and, in the case of Pb-free, this code (I) is omitted. Example: RC65Y-31K6B-804 CECC 40101-804BT

USA (IRC) Part Number: RC55LFV3162BA (RC55 with TCR ±5ppm/°C at 31.6 kilohms ±0.1%, Pb-free)



1	2	3	4	5			6	
Туре	Termination	TCR (ppm/°C)	Value	Tolerance		Packing		
RC55	Omit for	V = ±5	3 digits + multiplier	$A = \pm 0.05\%$	۸	RC55	Ammo, up to 5000/box	
RC65	Sn(95)Pb(5)	T = ±10	R = ohms for	$B = \pm 0.1\%$	Α	RC65	Ammo, up to 2500/box	
RC70	LF = Pb-free	Y = ±15	values <100 ohms	$C = \pm 0.25\%$	В	RC70	Bulk, 250/box	
		D = ±25		$D = \pm 0.5\%$				
		C = ±50		F = ±1%				
		$Z = \pm 100$]					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TT Electronics:

```
RC55Y-8K25BI
RC55Y-243KBI
RC55Y-20KBI
RC55Y-5K62BI
RC55Y-10K2BI
RC55Y-1K3BI
RC55Y-1K5BI

RC55Y-681KBI
RC55Y-1K0BI
RC55Y-9K76BI
RC55Y-10K7BI
RC55Y-1K1BI
RC55Y-1K24BI
RC55Y-200KBI

RC55Y-49K9BI
RC55Y-27K4BI
RC55Y-1K21BI
RC55Y-9K09BI
RC55Y-33K2BI
RC55Y-200RBI
RC55Y-499RBI

RC55Y-20K5BI
RC55Y-3K16BI
RC55Y-4K02BI
RC55Y-511RBI
RC55Y-2K21BI
RC55Y-3K65BI
RC55Y-5K11BI

RC55Y-12K1BI
RC55Y-4K99BI
RC55Y-4K02BI
RC55Y-1K02BI
RC55Y-7K5BI
RC55Y-909KBI

RC55Y-30K1BI
RC55Y-22K1BI
RC55Y-182RBI
RC55Y-39K2BI
RC55Y-2K67BI
RC55Y-232RBI
RC55Y-255KBI

RC55Y-30K1BI
RC55Y-24K9BI
RC55Y-562KBI
RC55Y-61K9BI
RC55Y-475KBI
RC55Y-25Y-20KBI
RC55Y-248K7BI

RC55Y-100KBI
RC55Y-82K5BI
RC55Y-100RBI
RC55Y-33ZKBI
RC55Y-15KBI
RC55Y-301KBI
RC55Y-237KBI
RC55Y-16K9BI

RC55Y-26K04BI
RC55Y-33ZRBI
RC55Y-15KBI
RC55Y-47K5BI
RC55Y-249KBI
RC55Y-124KBI
```