
+

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PLUG POSITION ONE -

MODULAR PLUG

NOTES:

- **!. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
 - 2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
 - 3. TERMINATED WITH (8 POSITION) MODULAR PLUGS AT BOTH ENDS PER T568A.
 - 4. CONSTRUCTED WITH 24AWG STRANDED CATSE UTP CM PATCH CABLE
 - 5. MATERIALS:
- PLUG: POLYCARBONATE

DRAWING FILENAME

∠J 6. NOMINAL CABLE DIAMETER IS 0.215 IN (5.46MM).

T T568A WIRING SCHEME

PLUG POSITION CABLE WIRE
WHITE GREEN
GREEN
3 WHITE ORANGE
4 BLUE
5 WHITE BLUE
6 ORANGE
7 WHITE BROWN
8 BROWN

7	CABLE COLORS	** = COLOR
	OFF WHITE	
	BLACK	BL
	BLUE	BU
	RED	RD
	YELLOW	YL
	GREEN	GR
	ORANGE	OR
	VIOLET	VL
7	GRAY	GY

SEE SHEET 2 FOR PATCH CORD LENGTHS AND PART NUMBERS

MO2479KU_DC282/OOD / TX5e UTP COPPER PATCH CORDS (CM) CUSTOMER DRAWING

SIZE

-					1					∤ / G \		
												I.I. NUMBER
3	5-13-10	BJN		M. ADDED IDENTIFICATION LABEL L. ADDED TANGLE-FREE LATCH J. ADDED NEW NOTE 6 K. ADDED () TO P/N	02479-282						CORP. INLEY PARK, IL 60477	PRODUCT SPEC
2	7-25-07	BJN	EJH	I. T568A WAS T568B H. ADDED GY-GRAY	02479-282		REGA				ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:	WORK INSTRUCTION
				G. TX5e UTP WAS CATEGORY 5E W/PANDUIT PLUGS F. ADDED T568B WIRING SCHEME E. MODULAR PLUG WAS PANDUIT PLUG						THIRD ANGLE PROJECTION	(.X) ± .06(1.5) (.XXX) ± .010(.3) (.XX)± ANGLES ±	INOINE
1	4-18-07	BJN	EJH	C. ADDED COLOR TABLE D. ADDED CABLE LG A. ADDED SH2 B. ADDED NOTES 3-5	02479-282		REGA			DRAWN BY NER	REVIEW DRAWING NUMBERS	UTPCHXX**(Y)
R	3-21-06	NER	WJC	RELEASED TO PRODUCTION	02479-282		RMD			3-16-06		DRAWING NO.
REV	DATE	BY	СНК	DESCRIPTION	ECN -	R	CUST	SUP	отн	M AC		02479-282 SHEET 1 OR 2

-

UTPCH25**Y

UTPCH30**Y

UTPCH35**Y

UTPCH40**Y

25 FT.

30 FT.

35 FT.


40 FT.


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TX5e UTP PATCH CORDS

PANDUIT PART NUMBER	MIN. CABLE LENGTH	PANDUIT PART NUMBER	MIN. CABLE LENGTH
UTPCHI**Y	l FT.	UTPCHO.5M**Y	0.5 m
UTPCH2**Y	2 FT.	UTPCH1M**Y	l m
UTPCH3**Y	3 FT.	UTPCH1.5M**Y	1.5 m
UTPCH4**Y	4 FT.	UTPCH2M**Y	2 m
UTPCH5**Y	5 FT.	UTPCH2.5M**Y	2.5 m
UTPCH6**Y	6 FT.	UTPCH3M**Y	3 m
UTPCH7**Y	7 FT.	UTPCH4M**Y	4 m
UTPCH8**Y	8 FT.	UTPCH5M**Y	5 m
UTPCH9**Y	9 FT.	UTPCH6M**Y	6 m
UTPCH10**Y	10 FT.	UTPCH7M**Y	7 m
UTPCH11**Y	11 FT.	UTPCH8M**Y	8 m
UTPCH12**Y	12 FT.	UTPCH9M**Y	9 m
UTPCH13**Y	13 FT.	UTPCH10M**Y	10 m
UTPCH14**Y	l4 FT.	UTPCH15M**Y	15 m
UTPCH15**Y	15 FT.	UTPCH20M**Y	20 m
UTPCH16**Y	16 FT.	UTPCH25M**Y	25 m
UTPCH17**Y	17 FT.	UTPCH30M**Y	30 m
UTPCH18**Y	18 FT.	UTPCH35M**Y	35 m
UTPCH19**Y	19 FT.	UTPCH40M**Y	40 m
UTPCH20**Y	20 FT.		







Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

UTPCH10Y UTPCH14Y UTPCH16BUY UTPCH1Y UTPCH20Y UTPCH25BUY UTPCH25GRY UTPCH25RDY
UTPCH25Y UTPCH2Y UTPCH3ORY UTPCH4Y UTPCH5BUY UTPCH5Y UTPCH6Y UTPCH7BUY UTPCH7GRY
UTPCH7ORY UTPCH7YLY UTPCH8Y UTPCH2GRY UTPCH7Y UTPCH20BUY UTPCH18UY UTPCH10BUY
UTPCH30RDY UTPCH30RY UTPCH1MRDY UTPCH1VLY UTPCH20MRDY UTPCH30V UTPCH30BUY
UTPCH6BLY UTPCH30GRY UTPCH1.5MY UTPCH4BLY UTPCH3VLY UTPCH3VLY UTPCH16RDY
UTPCH5MGRY UTPCH7GYY UTPCH3GRY UTPCH10RDY UTPCH14BUY UTPCH5YLY UTPCH10YLY
UTPCH3YLY UTPCH2BUY UTPCH10ORY UTPCH7VLY UTPCH18LY UTPCH4BUY UTPCH6BUY UTPCH10GRY
UTPCH1GRY UTPCH8GRY UTPCH12GRY UTPCH4MVLY UTPCH16BLY UTPCH4RDY UTPCH2RDY
UTPCH5RDY UTPCH8ORY UTPCH18BUY UTPCH3BLY UTPCH4FDY UTPCH6RDY UTPCH8VLY
UTPCH12ORY UTPCH18Y UTPCH18VLY UTPCH6VLY UTPCH4RDY UTPCH14GRY UTPCH5VLY
UTPCH2ORY UTPCH18BLY UTPCH16VLY UTPCH4RDY UTPCH14GRY UTPCH4GRY
UTPCH5ORY UTPCH5BLY UTPCH1RDY UTPCH16YLY UTPCH18YLY UTPCH12VLY UTPCH4GRY
UTPCH5ORY UTPCH5BLY UTPCH1RDY UTPCH16YLY UTPCH6YLY UTPCH11VLY UTPCH4GRY
UTPCH25GYY UTPCH6GRY UTPCH6ORY UTPCH20RDY UTPCH4VLY UTPCH12BLY UTPCH5GRY
UTPCH25GYY UTPCH6RDY UTPCH5ORY UTPCH20RDY UTPCH4VLY UTPCH12BLY UTPCH5GRY
UTPCH12RDY UTPCH7RDY UTPCH2VLY UTPCH110RY