

Slide Switch

Q-2519




TYPE: **MS-1380**

SPECIFICATIONS


Contact Type	SP3T
Pin Width	2mm
Rating	DC 6V, 0.3A
Contacts Resistance	70mΩ
Insulation Resistance	100MΩ
Minimum Load	DC 500V
Dielectric Strengths	AC 500V / 1 minute
Life Test	10 000 cycles/ minute
Temperature Range	- 10°C ~ + 60°C
Material	Plastic & Metal



Outline Drawing



Mounting



Circuitry

