

SMD LED LAMP, BI-COLOR

BL-LS1311xx-3

■ Features:

- 3.5mmx2.8mm SMD, 1.9mm THICKNESS PLCC4 package
- Mono-color type, Ultra brightness, with 3 chips
- Compatible with automatic placement equipment
- WIDE VIEWING ANGLE.
- IDEAL FOR BACKLIGHT AND INDICATOR.
- PACKAGE: 2KPCS/REEL
- RoHs Compliance



■ Electrical-optical characteristics: (Ta=25°C) (Test Condition: IF=20mA)

Part Number	Chip			Lens Type	Forward Voltage(VF) Unit:V		Luminous Intensity (Iv) Unit:mcd		Viewing Angle 2θ1/2 (deg)
	Emitted Color	Material	λp (nm)						
					Typ	Max	Min.	Typ.	
BL-LS1311UEC-3	Ultra Orange	AlGaAs	630	Water Clear	2.10	2.50	400	800	120
BL-LS1311UYO-3	Ultra Amber	AlGaInP	610		2.10	2.60	300	600	
BL-LS1311UYC-3	Ultra Yellow	AlGaInP	593		2.10	2.60	600	800	
BL-LS1311UGC-3	Ultra Green	AlGaInP	575		2.20	2.70	28	50	
BL-LS1311PGC-3	Ultra Pure Green	InGaN	525		3.50	4.20	700	1000	
BL-LS1311UBC-3	Ultra Blue	InGaN	470		3.50	4.20	400	700	
BL-LS1311UWC-3	Ultra White	InGaN	/		3.50	4.20	1000	1500	

■ Absolute maximum ratings (Ta=25°C)

Parameter	UE	UYO	UY	UG	PG	UB	UW	Unit
Forward Current I_F	30	30	30	30	30	30	30	mA
Power Dissipation P_d	78	78	78	78	78	78	78	mW
Reverse Voltage V_R	5	5	5	5	5	5	5	V
Peak Forward Current I_{PF} (Duty 1/10 @1KHZ)	100	100	100	100	100	100	100	mA
Operation Temperature T_{OPR}	-30 to +80							°C
Storage Temperature T_{STG}	-40 to +85							°C
Lead Soldering Temperature T_{SOL}	Max.260±5°C for 3 sec Max. (1.6mm from the base of the epoxy bulb)							°C

The drawing shows three views of the 1N4148 diode package:

- Top View:** A square package with a central circular die area. Dimensions include overall width $3.5(.138) \pm 0.2$, mounting hole spacing $3.2(.126) \pm 0.2$, and lead spacing $2.8(0.11) \pm 0.2$. A polarity mark is indicated on the right side.
- Side View:** Shows the package profile with dimensions for lead height $0.15(.0059)$, mounting hole diameter $0.8(.031) \pm 0.3$, and package thickness $1.9(.075) \pm 0.2$.
- Pin Connection View:** A schematic showing the internal diode structure with pins 1, 2, 3, and 4.


1. All dimensions are in millimeters (inches)
2. Tolerance is $\pm 0.25(0.01")$ unless otherwise noted.
3. Specifications are subject to change without notice.

Technical drawing of a stepped profile. The profile consists of two rectangular steps. The first step has a width of 1.5 and a height of 2.2. The second step has a width of 1.5 and a height of 1.6. The total width of the profile is 3.0, and the total height is 3.8.







SMD LED LAMP, BI-COLOR

BL-LS1311xx-3

Typical electrical-optical characteristics curves:



- | | |
|---|--------------------------------------|
| (1) - GaAsP/GaAs 655nm/Red | (9) - GaAlAs 880nm |
| (2) - GaP 570nm/Yellow Green | (10) - GaAs/GaAs & GaAlAs/GaAs 940nm |
| (3) - GaAsP/GaP 585nm/Yellow | (A) - GaN/SiC 430nm/Blue |
| (4) - GaAsP/GaP 635nm/Orange & Hi-Eff Red | (B) - InGaN/SiC 470nm/Blue |
| (5) - GaP 700nm/Bright Red | (C) - InGaN/SiC 505nm/Ultra Green |
| (6) - GaAlAs/GaAs 660nm/Super Red | (D) - InGaN/SiC 525nm/Ultra Green |
| (8) - GaAsP/GaP 610nm/Super Red | |



NOTE: 25°C free air temperature unless otherwise specified