

Polyamide Spiral Binding for added strength and protection against abrasion

- SBPA

SBPA spiral binding is used for cable harnesses in the automobile industry and for many demanding industrial applications.

Features and Benefits


- Organises and protects cables and hoses
- Very good protection against abrasion
- Suitable for retro-fitting
- Cables branch out at any point
- Wide range of diameters and colours



SPBA spiral binding offers good protection against abrasion.

Spiral binding made of flame-retardant polyamide 6 can be found in the Engineered Solutions Catalogue.

MATERIAL	Polyamide 6 (PA6)
Operating Temperature	-60 °C to +95 °C, intermittent +130 °C
Flammability	UL94 HB



TYPE	Nominal Ø	Wall (WT)	Pitch (P)	Bundle Ø min.	Bundle Ø max.	Colour	Reel Length	Article-No.
SBPA1.5	1.5	0.4	6.0	1.6	8	Natural (NA)	30 m	161-42000
SBPA4	4	0.6	7.8	5	20	Natural (NA)	30 m	161-42100
SBPA9	9	1.0	12.5	10	100	Natural (NA)	30 m	161-42200
SBPA16	16	1.2	16.0	20	150	Natural (NA)	30 m	161-42300

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.