



Polyamide Spiral Binding for added strength and protection against abrasion

SBPA

SBPA spiral binding is used for cable harnesses in the automobile industry and for many demanding industrial applications.


Features and Benefits

- Organises and protects cables and hoses
- Very good protection against abrasion
- Suitable for retro-fitting
- Cables branch out at any point
- Wide range of diameters and colours



SPBA spiral binding made of polyamide offers excellent protection against abrasion.

MATERIAL	Polyamide 6 (PA6)
Operating Temperature	-60 °C to +95 °C, intermittent +130 °C
Flammability	UL94 HB



Spiral binding

TYPE	Nominal Ø	Wall (WT)	Pitch (P)	Bundle Ø min.	Bundle Ø max.	Colour	Reel Length	Article-No.
SBPA1.5	1.5	0.40	6.0	1.6	8.0	Natural (NA)	30 m	161-42000
SBPA4	4	0.60	7.8	5.0	20.0	Natural (NA)	30 m	161-42100
SBPA9	9	1.00	12.5	10.0	100.0	Natural (NA)	30 m	161-42200
SBPA16	16	1.20	16.0	20.0	150.0	Natural (NA)	30 m	161-42300

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content.