

# **SD Class 10**

#### **Description**

Featuring data transfer speeds of up to 30MB/s, Transcend's Class 10 SDXC/SDHC cards provide an impressive level of performance for high-megapixel digital cameras and Full-HD camcorders. With impressive write speed, these cards provide enhanced camera response for high-speed consecutive shooting as well as smooth Full HD video recording.

#### **Features**


All rights reserved. Transcend and the Transcend logo are registered trademarks of Transcend Information, Inc. Product offerings and specifications are subject to change without notice. All other products, brand names, company names and logos are trademarks of their respectiv

- Fully compliant with the SD 3.0 standard
- Class 10 speed rating guarantees fast and reliable write performance
- Easy to use, plug-and-play operation
- Efficient exFAT file system (SDXC cards only)
- Built-in Error Correcting Code (ECC) to detect and correct transfer errors
- Exclusive RecoveRx photo recovery software






### **Architecture**





# **Pin Definition**

Pin No.	SD Mode		SPI Mode	
	Name	Description	Name	Description
1	CD/DAT3	Card Detect/Data Line [Bit3]	CS	Chip Select (neg true)
2	CMD	Command/Response	DI	Data In
3	V <sub>SS1</sub>	Supply voltage ground	V <sub>SS</sub>	Supply voltage ground
4	V <sub>DD</sub>	Supply voltage	VDD	Supply voltage
5	CLK	Clock	SCLK	Clock
6	V <sub>SS2</sub>	Supply voltage ground	V <sub>SS2</sub>	Supply voltage ground
7	DAT0	Data Line [Bit0]	DO	Data out
8	DAT1	Data Line [Bit1]	RSV	Reserved
9	DAT2	Data Line [Bit2]	RSV	Reserved



# **Specifications**

Physical Specification					
Form Factor		SD			
	Length	32.00 ± 0.1			
Dimensions (mm)	Width	24.00 ± 0.1			
	Height	2.1.00 ± 0.15			

Performance				
Model P/N	Read Performance			
TS4GSDHC10				
TS8GSDHC10	Up to 20MB/S			
TS16GSDHC10				
TS32GSDHC10	$L_{\rm P}$ to 20MP/S			
TS64GSDHC10	Up to 30MB/S			
TS128GSDHC10				

Note: Maximum transfer speed recorded

\* 25  $^\circ$ C , 4GB DRAM, Windows<sup>\*</sup> 7 with Transcend RDF5, benchmark utility Crystal DiskMark , copied file 1000MB, unit MB/s

Environmental Specifications		
Operating Temperature	- 25°C to 85°C	
Storage Temperature	- 40°℃ to 85℃	
Durability	10.000 mating cycles;	
Drop test	1.5m free fall	
Regulator	CE/FCC/BSMI	



## **Order information**

Capacity	Transcend Part Number
4GB	TS4GSDHC10
8GB	TS8GSDHC10
16GB	TS16GSDHC10
32GB	TS32GSDHC10
64GB	TS64GSDXC10
128GB	TS128GSDXC10

The technical information above is based on industry standard data and has been tested to be reliable. However, Transcend makes no warranty, either expressed or implied, as to its accuracy and assumes no liability in connection with the use of this product. Transcend reserves the right to make changes to the specifications at any time without prior notice. Due to the complexity and variety of industrial applications, for special applications and environments, it is strongly suggested to contact Transcend or its authorized resellers beforehand for compatibility confirmation





#### www.transcend-info.com

TAIWAN

E-mail: sales-tw@transcend-info.com

USA Los Angeles: E-mail: sales-us@transcend-info.com

Maryland: E-mail: sales-us@transcend-info.com

*Miami:* E-mail: sales-us@transcend-info.com

Silicon Valley: E-mail: sales-us@transcend-info.com

GERMANY E-mail: sales-de@transcend-info.com

#### **Revision History**

THE NETHERLANDS E-mail: sales-nl@transcend-info.com

United Kingdom E-mail: sales-uk@transcend-info.com

JAPAN E-mail: sales-jp@transcend-info.com

KOREA E-mail: sales-kr@transcend-info.com

CHINA E-mail: sales@transcendchina.com

HONG KONG E-mail: sales-hk@transcend-info.com

Version	Date	Note
1.0	2016/04/06	The 1 <sup>st</sup> edition
1.1	2016/10/05	Revise pin definition of SPI mode



Copyright © 2016 Transcend Information, Inc. All Rights Reserved