

PARA LIGHT ELECTRONICS CO., LTD.

11F., No. 8, Jiankang Rd., Zhonghe Dist., New Taipei City 235, Taiwan, Tel: 886-2-2225-3733 Fax: 886-2-2225-4800

E-mail: para@para.com.tw www.paralighttaiwan.com

# DATA SHEET

PART NO.: L-T670LBCT -BKS

CUSTOMER'S APPROVAL:	DC	CC :	
DRAWING NO · DS-7A-07-0006	DATE · 2021-01-15	PAGE	1 of 15



Part No.: L-T670LBCT-BKS REV: B/3


### Features

- \* Top view, Wide view angle, Blue color PLCC 2 package SMD LED.
- \* EIA STD package, packing in 8mm tape on 7" diameter reels (ANSI/EIA-481-B-2001).
- \* Compatible with automatic Pick & Place equipment.
- \* Compatible with IR Reflow soldering and TTW soldering.
- \* Pb free product and acceptable lead-free process.
- \* Meet RoHS Green Product.

# Application

- **★** Backlighting (Switches, keys, displays, illuminated advertising)
- \* Emergency lighting / Signal and symbol luminaries.

# Package Outline Dimensions



#### Notes:

- 1. All dimensions are in millimeters.
- 2. Tolerance is  $\pm$  0.15mm (.004") unless otherwise noted.

DRAWING NO.: DS-7A-07-0006 DATE: 2021-01-15 PAGE 2 of 15



Part No.: L-T670LBCT-BKS REV: B/3

### • CHIP MATERIALS

Dice Material : InGaNLight Color : Blue

\* Lens Color: Water Clear

# ● Absolute Maximum Ratings(Ta=25°C)

Symbol	Parameter	Rating	Unit	
PD	Power Dissipation	75	mW	
Inc	Peak Forward Current	100	A	
Ipf	(1/10 Duty Cycle, 0.1ms Pulse Width)	100	mA	
IF	Continuous Forward Current	20	mA	
VR	Reverse Voltage	5	V	
ESD	Electrostatic Discharge Threshold(HBM) <sup>Note A</sup>	1000	V	
Topr	Operating Temperature Range	<b>-</b> 40 ∼ + 100	°C	
Tstg	Storage Temperature Range	<b>-</b> 40 ∼ + 100	$^{\circ}\mathbb{C}$	
T 11	S.H.: T. (O. C. MAY)	Reflow Soldering:260°C (for 10seconds)		
Tsld	Soldering Temperature (One times MAX.)	Hand Soldering:300°C (for 3	3 seconds)	

Note A:

HBM : Human Body Model. Seller gives no other assurances regarding the ability of to withstand ESD.

# • Electro-Optical Characteristics (Ta=25°C)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Test Condition
Luminous Intensity	IV	350	480		mcd	IF=20mA
Viewing Angle	2 θ 1/2		120		Deg	
Peak Emission Wavelength	λр		465		nm	IF=20mA
Dominant Wavelength	λD		470		nm	IF=20mA
Spectrum Radiation Bandwidth	Δλ		25		nm	IF=20mA
Forward Voltage	VF		3.0	3.6	V	IF = 20mA
Reverse Current	IR			10	μА	VR = 5V

DRAWING NO.: DS-7A-07-0006 DATE: 2021-01-15 PAGE 3 of 15



Part No.: L-T670LBCT-BKS REV: B/3

#### Notes:

- 1. Luminous intensity is measured with a light sensor and filter combination that proximities the CIE eye-response curve.
- 2.  $\theta$  1/2 is the off-axis angle at which the luminous intensity is half the axial luminous intensity.
- 3. Caution in ESD:
  - Static Electricity and surge damages the LED. It is recommended use a wrist band or anti-electrostatic glove when handling the LED. All devices, equipment and machinery must be properly grounded.
- 4. Major standard testing equipment by "Instrument System" Model: CAS140B Compact Array Spectrometer and "KEITHLEY" Source Meter Model: 2400.

# Typical Electro-Optical Characteristics Curves




Fig.1 Relative Intensity vs. Wavelength

DRAWING NO.: DS-7A-07-0006 DATE: 2021-01-15 PAGE 4 of 15



Part No.: L-T670LBCT-BKS REV: B/3

# Typical Electro-Optical Characteristics Curves

(25°C Ambient Temperature Unless Otherwise Noted)




Fig.1 Forward Current vs.Forward Voltage




Fig.2 Luminous Intensity vs.Forward Current




Fig.3 Relative Luminous Intensity vs.Forward Current




Fig.4 Luminous Intensity vs. Ambient Temperature




Fig.5 Forward Current Derating Curve




Fig.6 Relative Intensity vs.Angle

DRAWING NO.: DS-7A-07-0006 DATE: 2021-01-15 PAGE 5 of 15



Part No.: L-T670LBCT-BKS REV: B/3

### Bin Code List

Luminous Intensity(IV), Unit:mcd@20mA				
Bin Code	Min	Max		
P17	350	430		
P18	430	530		
P19	530	650		

Forward Voltage(VF), Unit:V@20mA				
Bin Code	Min	Max		
14	2.9	3.0		
15	3.0	3.1		
16	3.1	3.2		
17	3.2	3.3		
18	3.3	3.4		
19	3.4	3.5		
20	3.5	3.6		
CX	-			

Tolerance of each bin are  $\pm 10\%$ 

Tolerance of each bin are  $\pm 0.1$ Volt

Dominant Wavelength (Hue), Unit: nm@20mA				
Bin Code	Min	Max		
AC	465	470		
AD	470	475		

Tolerance of each bin are  $\pm 1$ nm

DRAWING NO.: DS-7A-07-0006 DATE: 2021-01-15 PAGE 6 of 15



Part No.: L-T670LBCT-BKS REV: B/3

# Label Explanation

CUS. PART NO: To be denominated.

CUSTOMER: To be denominated.

PART NO: Refer to P15

P16--- Luminous Intensity Code

16--- Forward Voltage Code

AC--- Dominant Wavelength

LOT NO: E L S 7 8 0001
A B C D E F

A---E: For series number

B---L: Local F: Foreign

C---S: SMD

D---Year

E---Month

F---SPEC.

#### PACKING QUANTITY OF BAG:

2000pcs for T670 series

2000pcs for T650 series

2000pcs for S020 series

DATE CODE: <u>2007</u> <u>08</u> <u>29</u>

G H I

G--- Year

H--- Month

I --- Day


DRAWING NO.: DS-7A-07-0006 DATE: 2021-01-15 PAGE 7 of 15



Part No.: L-T670LBCT-BKS

REV: B/3


# Reel Dimensions



#### Notes:

- 1. Taping Quantity: 2000pcs
- 2. The tolerances unless noted is  $\pm 0.1$  mm, Angle  $\pm 0.5^{\circ}$ , Unit: mm.

# Suggest Soldering Pad Dimensions




DRAWING NO.: DS-7A-07-0006 DATE: 2021-01-15 PAGE 8 of 15




Part No.: L-T670LBCT-BKS REV: B/3

# Package Dimensions Of Tape And Reel



Notes: All dimensions are in millimeters.

# Packaging Of Electronic Components On Continuous Tapes




DRAWING NO.: DS-7A-07-0006 DATE: 2021-01-15 PAGE 9 of 15



Part No.: L-T670LBCT-BKS REV: B/3

# Moisture Resistant Packaging



Notes: One reel in a bag, one bag in a inner box, ten inner boxes in a carton. Unit: mm.

### Cleaning

- \* If cleaning is required, use the following solutions for less than 1 minute and less than 40°C.
- \* Appropriate chemicals: isopropyl alcohol. (When using other solvents, it should be confirmed beforehand whether the solvents will dissolve the package and the resin or not.)
- \* Effect of ultrasonic cleaning on the LED resin body differs depending on such factors as ultrasonic power and the assembled condition. Before cleaning, a pre-test should be confirm whether any damage to the LEDS will occur.


DRAWING NO.: DS-7A-07-0006 DATE: 2021-01-15 PAGE 10of 15




Part No.: L-T670LBCT-BKS

REV: B/3

• Suggest Sn/Pb IR Reflow Soldering Profile Condition:



• Suggest Pb-Free IR Reflow Soldering Profile Condition:



DRAWING NO.: DS-7A-07-0006 DATE: 2021-01-15 PAGE 11 of 15



Part No.: L-T670LBCT-BKS REV: B/3

### CAUTIONS

### 1. Static Electricity:

\* Static electricity or surge voltage damages the LEDs.

It is recommended that a wrist band or an anti-electrostatic glove be used when handling the LEDs.

\* All devices, equipment and machinery must be properly grounded.

It is recommended that measures be taken against surge voltage to the equipment that mounts the LEDs.

- \* When inspecting the final products in which LEDs were assembled, it is recommended to check whether the assembled LEDs are damaged by static electricity or not. It is easy to find static-damaged LEDs by a light-on test or a VF test at a lower current (blew 1mA is recommended).
- \* Damaged LEDs will show some unusual characteristics such as the leak current remarkably increases, the forward voltage becomes lower, or the LEDs do not light at the low current.

Criteria: (VF>2.0V,at IF=0.5m A)

#### 2. Storage:

\* before opening the package:

The led should be kept at 30 c or less, 85 % RH or less. When the led is stored, a moisture proof packaging with absorbent material (silica gel) is recommended.

\* after opening the package:

The led should be kept at 30 c or less, 70 % RH or less. After unpacking, the led welding is 168 hours (7 days). If the unused led indicator is still present, it should be stored in a moisture proof package, such as a sealed container with a moisture proof material (silica gel). It is also recommended to return the led to the original moisture proof bag, and to pack the moisture-proof bag again. If the moisture absorption material (silica gel) fades or the led exceeds the storage time (the unopened led is valid for 6 months), the following conditions should be used before baking.

Baking treatment: 65 °C, more than 24 hours.

avoid rapid changes in ambient temperature in a high humidity environment where condensation may occur.3.

#### 3. Soldering:

Do not apply any stress to the LED lens during soldering while the LED is at high temperature. Recommended soldering condition.

\* Reflow Soldering:

Pre-heat 120~150°C, 120sec. MAX., Peak temperature : 240°C Max. Soldering time : 10 sec Max.

\* Soldering Iron: (Not recommended)

Temperature 350°C Max., Soldering time: 3 sec. Max. (one time only), power dissipation of iron: 20W Max. use SN60 solder of solder with silver content and don't to touch LED lens when soldering.

DRAWING NO.: DS-7A-07-0006 DATE: 2021-01-15 PAGE 12 of 15



Part No.: L-T670LBCT-BKS REV: B/3

#### 4. Lead-Free Soldering

### For Reflow Soldering:

1 · Pre-Heat Temp: 150-180℃,120sec.Max.

2 · Soldering Temp: Temperature Of Soldering Pot Over 240°C,40sec.Max.

3 ' Peak Temperature:  $260\,^\circ\!\text{C}\,$  ' 10sec.

4 · Reflow Repetition: 2 Times Max.

5 ` Suggest Solder Paste Formula : 93.3 Sn/3.1 Ag/3.1 Bi/0.5 Cu


### For Soldering Iron (Not Recommended):

1 ` Iron Tip Temp: 350°C Max.

2 Soldering Iron: 30w Max.

3 \ Soldering Time: 3 Sec. Max. One Time.

### 5. Drive Method



- (A)Recommended circuit.
- (B)The difference of brightness between LED's could be found due to the Vf-If characteristics of LED.

#### 6. Reliability

### 1. Criteria For Judging The Damage

Itana	Cyrob ol	Test Conditions Criteria for Judgeme		Judgement
Item Symbol		Test Conditions	MIN.	Max.
Forward Voltage	VF	IF=20mA	-	U.S.L.*)×1.1
Reverse Current	IR	VR=5V	-	U.S.L.*)×2.0
Luminous Intensity	IV	IF=20mA	$L.S.L^{**}) \times 0.7$	-

\*) U.S.L.: Upper Standard Level

\*\*) L.S.L: Lower Standard Level

DRAWING NO.: DS-7A-07-0006 DATE: 2021-01-15 PAGE 13 of 15



Part No.: L-T670LBCT-BKS REV: B/3

### 2. Test Items And Results

Test Item	Reference Standard	Test Condition	Note	Number of Damaged
Resistance to Soldering Heat (Reflow Soldering)	JEITA ED-4701300 301	Tsld=260℃,10sec. (Pre treatment 30℃,70%,168hrs)	2times	0/50
Solder ability (Reflow Soldering)	JEITA ED-4701300 303	Tsld=215℃,3sec. (Lead Solder)	1time over 95%	0/50
Thermal Shock	JEITA ED-4701300 307	-40°C ~ 100°C 30min. 30min.	100cycles	0/50
Temperature Cycle	JEITA ED-4701100 105	-40°C ~ 25°C~100°C~25°C 30min. 5min. 30min. 5min	100cycles	0/50
High Temperature Storage	JEITA ED-4701200- 201	Ta=100°C	1000hrs.	0/50
Temperature Humidity Storage	JEITA ED-4701100 103	Ta=60°C,RH=90%	1000hrs.	0/50
Low Temperature Storage	JEITA ED-4701200 202	Ta=-40°C	1000hrs.	0/50
Steady State Operating Life Condition		Ta=25℃,IF=20mA	1000hrs.	0/50
Steady State Operating Life of High Temperature		Ta=85℃,IF=5mA	500hrs.	0/50
Steady State Operating Life of High Humidity Heat		Ta=60°C,RH=90%,IF=15mA	500hrs.	0/50
Steady State Operating Life of Low Temperature		Ta=-30°C,IF=20mA	500hrs.	0/50
Vibration	JEITA ED-4701400 403	100~2000~100HzSweep 4min.200m/s <sup>2</sup> 3direction,4cycles	48min	0/50
Substrate Bending	JEITA ED-4702	3mm,5±1sec	1time	0/50
Stick	JEITA ED-4702	5N,10±1sec	1time	0/50

# 7.Others:

The appearance and specifications of the product may be modified for improvement without notice.

DRAWING NO.: DS-7A-07-0006 DATE: 2021-01-15 PAGE 14 of 15



DRAWING NO.: DS-7A-07-0006

# SURFACE MOUNT DEVICE LED

Part No.: L-T670LBCT-BKS REV: B/3

3. PART NO. SYSTEM;÷ XXXX: Special specification for customer  $L - \underline{T} \underline{670} \underline{X} \underline{X} \underline{T} - \underline{X} \underline{X} \underline{X} \underline{X}$ T : Taping for 7 inch reel TC: Taping for 13 inch reel Lens color C: Water Clear W: White Diffused T: Color Transparent D: Color Diffused KY: 9mil AlInGap 590nm Super Yellow KR: 9mil AlInGap 630 nm Super Red TE: 14mil AlInGap 624 nm Super Red TY: 14mil AlInGap590 nm Super Yellow LB: InGaN ITO rough 470nm Blue LG: InGaN ITO rough520nm Green W: InGaN + YAG White color 0 : Single chip 1/2 : Super thin single chip 5/6: Dual chip F: Three chip(Full color) 650: 3020 1.3T TYPE 670: 3528 1.8T **TYPE** C: PCB Top View Type 020: 3812 0.6T **TYPE** T:PLCC Top View Type S: Side View Type

DATE: 2021-01-15

PAGE 15 of 15