

TECHNICAL DATA SHEET

Stainless steel type S

General notes:

- Martensitic higher carbon steel (Material number 1.4034, DIN X46Cr13, AISI number 420)
- contains from 12.5 to 14.5 wt% chromium
- magnetizable
- can be hardened by heat treatment, forming should be done in the annealed condition
- less resistant to corrosion than the austenitic or ferritic grades
- used where strength and/or hardness are of primary concern and where the environment is relatively mild from a corrosive standpoint
- » typical applications include tweezers and cutting tools for the electronic industry, watch-makers, jewelers and laboratory and medical applications in mild aggressive chemical environments

Composition

Component	Wt.%	Component	Wt.%	Component	Wt.%
С	0.43-0.50	Si	≤1.0	Mn	≤1.0
Р	≤0.04	s	≤0.03	Cr	12.5-14.5

Mechanical properties

annealed
7.7 g/cm ³
53-54 HRC
615-625 MPa
≥300 MPa
215 GPa

Thermal properties

Coef. of lin. therm expansion	10.5 E-6/°C	20°C-100°C
Coef. of lin. therm expansion	11.5 E-6/°C	20°C-300°C
Specific heat capacity	0.46 J/(g⋅K)	
Thermal conductivity	30 W/(m⋅K)	

Electrical properties

0.55 E-4 Ohm.cm Resistivity

This document contains information based on average values as obtained from the results of laboratory tests and observations made on the material. Ideal-Tek SA declines all responsibility from an improper use of the product described in this document.

