





Practical and completely safe



- ▶ Each fuse carrier is designed to take:
 - a blow-out indicator
 - a padlock
- ▶ Cartridge totally visible
- ▶ Class II insulation along the entire length of the carrier



Pack	Cat. No.	Miniature type 5 x 20		
		Instant reaction fuse - Ceramic body Conform to IEC 60127 - NF EN 60127 - VDE 0820-1 High rupture capacity (A) For use with dimmers, Viking terminals and emergency lighting units		
		Rating (Amps)	Voltage~ (Volts)	Rupture capacity (Amps)
10	102 02	0.2		
10	102 05	0.5		
10	102 06	0.63		
10	102 10	1.0		
10	102 12	1.25		
10	102 16	1.6		
10	102 20	2.0	250	1500
10	102 25	2.5		
10	102 30	3.15		
10	102 50	5.0		
10	102 63	6.3		
10	102 96 (1)	10.0	250	500

Pack	Cat. No.	Cylindrical - without indicator			
		Rating (Amps)	Voltage~ (Volts)	Rupture capacity (Amps)	Protected section (mm ²) Copper
10	103 06 (1)	6.3 x 23 6	230	6 000	1.5
10	113 02	2			
10	113 04	4			
10	113 06	6	230	6 000	1.5
10	113 10	10			
10	116 06 (2)	10.3 x 25.8 6			
10	116 10 (2)	10	230	6 000	2.5
10	116 16 (2)	16			
10	123 01	1			
10	123 02	2			
10	123 04	4			
10	123 06	6			
10	123 08	8	400	20 000	2.5
10	123 10	10			
10	123 12	12			
10	123 16	16			
10	123 20	20			
10	126 16	10.3 x 31.5 16			
10	126 20	20	400	20 000	4
10	126 25	25			
10	133 32	10.3 x 38 32	400	20 000	6
		Neutral links			
10	123 00	8.5 x 31.5			
10	133 00	10 x 38			

(1) Overrating not described by standards
(2) Conform to BS 1361 (1971)

HRC cartridge fuses



Technical data and dimensions (p. 46)

Pack	Cat. No.	Cylindrical type gG	Pack	Cat. No.	Cylindrical type aM (motor rated)
		Conform to NF C 63-210/211 - EN 60269-1, 2 and IEC 60269-1, 2 & 2-1 Veritas approved - without indicator			Conform to NF C 60-200 - EN 60269-1 IEC 60269-1 Veritas approved - without indicator (130 XX) Without striker (140 XX - 150 XX)
		10 X 38 mm - 500 V, 100 KA HRC			10 X 38mm - 500 V, 100 KA HRC
		Rating (amp)			Rating (amp)
10	133 94	0.5	10	130 92	0.25
10	133 01	1	10	130 95	0.5
10	133 02	2	10	130 01	1
10	133 04	4	10	130 02	2
10	133 06	6	10	130 04	4
10	133 08	8	10	130 06	6
10	133 10	10	10	130 08	8
10	133 12	12	10	130 10	10
10	133 16	16	10	130 12	12
10	133 20	20	10	130 16	16
10	133 25	25			
		10.3 X 38 mm - 500 V, 20 KA HRC	10	130 20 ⁽²⁾	20
10	133 32	32	10	130 25 ⁽²⁾	25
		14 X 51mm - 500 V, 100 KA HRC			14 X 51mm - 500 V, 100 KA HRC
10	143 02	2	10	140 02	2
10	143 04	4	10	140 04	4
10	143 06	6	10	140 06	6
10	143 10	10	10	140 08	8
10	143 16	16	10	140 10	10
10	143 20	20	10	140 12	12
10	143 25	25	10	140 16	16
10	143 32	32	10	140 20	20
10	143 40	40	10	140 25	25
		14 X 51mm - 400 V, 100 KA HRC	10	140 32	32
10	143 50 ⁽¹⁾	50	10	140 40	40
		22 X 58mm - 500 V, 100 KA HRC			14 X 51mm - 400 V, 100 KA HRC
10	153 16	16	10	140 45 ⁽¹⁾	45
10	153 20	20	10	140 50 ⁽¹⁾	50
10	153 25	25			22 X 58mm - 500 V, 100 KA HRC
10	153 32	32	10	150 16	16
10	153 40	40	10	150 20	20
10	153 50	50	10	150 25	25
10	153 63	63	10	150 32	32
10	153 80	80	10	150 40	40
10	153 96	100	10	150 50	50
		22 X 58mm - 400 V, 100 KA HRC	10	150 63	63
10	153 97 ⁽¹⁾	125	10	150 80	80
			10	150 96	100
					22 X 58mm - 400 V, 100 KA HRC
			10	150 97	125
					Neutral links
			10	123 00	8.5 X 31.5
			10	133 00	10.3 X 38
			10	143 00	14 X 51
			10	153 00	22 X 58

(1) Overrating described by standards
(2) Overrating not described by standards