

# **DN2530**

# N-Channel, Depletion-Mode, Vertical DMOS FET

#### Features

- · High-input impedance
- · Low-input capacitance
- · Fast switching speeds
- · Low on-resistance
- · Free from secondary breakdown
- · Low input and output leakage

#### Applications


- · Normally-on switches
- Solid state relays
- Converters
- Linear amplifiers
- Constant current sources
- Power supply circuits
- Telecom

#### Package Types

#### Description

The DN2530 is a low-threshold, depletion-mode, normally-on transistor that utilizes an advanced vertical DMOS structure and a well-proven silicon-gate manufacturing process. This combination produces a device with the power-handling capabilities of bipolar transistors, plus the high-input impedance and positive-temperature coefficient inherent in Metal-Oxide Semiconductor (MOS) devices. Characteristic of all MOS structures, this device is free from thermal runaway and thermally-induced secondary breakdown.

Vertical DMOS Field-Effect Transistors (FETs) are ideally suited to a wide range of switching and amplifying applications where high breakdown-voltage, high-input impedance, low-input capacitance, and fast switching speeds are desired.



# 1.0 ELECTRICAL CHARACTERISTICS

# ABSOLUTE MAXIMUM RATINGS<sup>†</sup>

Drain-to-source voltage	BV <sub>DSY</sub>
Drain-to-gate voltage	
Gate-to-source voltage	20/1
Operating and Storage Temperature	

**† Notice:** Stresses above those listed under "Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational listings of this specification is not implied. Exposure to maximum rating conditions for extended periods may affect device reliability.

# DC AND AC CHARACTERISTICS

Electrical Specifications: Unless otherwise specified, for all specifications T <sub>A</sub> = +25°C									
Parameter	Symbol	Min	Тур	Max	Units	Conditions			
DC Parameters (Note 1, unless other	erwise stated)								
Drain-to-source breakdown voltage	BV <sub>DSX</sub>	300	-	-	V	V <sub>GS</sub> = -5.0V, Ι <sub>D</sub> = 100 μΑ			
Gate-to-source off voltage	V <sub>GS(OFF)</sub>	-1.0	-	-3.5	V	V <sub>DS</sub> = 25V, I <sub>D</sub> = 10 μA			
$V_{GS(OFF)}$ change with temperature	$\Delta V_{GS(OFF)}$	-	-	-4.5	mV/°C	V <sub>DS</sub> = 25V, I <sub>D</sub> = 10 μA( <b>Note 2</b> )			
Gate body leakage current	I <sub>GSS</sub>	-	-	100	nA	$V_{GS}$ = ±20V, $V_{DS}$ = 0V			
		-	-	10	μA	V <sub>DS</sub> = Max rating, V <sub>GS</sub> = -10V			
Drain-to-source leakage current	I <sub>D(OFF)</sub>	-	-	1.0	mA	V <sub>DS</sub> = 0.8 Max Rating, V <sub>GS</sub> = -10V, T <sub>A</sub> = 125°C ( <b>Note 2</b> )			
Saturated drain-to-source current	I <sub>DSS</sub>	200	-	-	mA	V <sub>GS</sub> = 0V, V <sub>DS</sub> = 25V			
Static drain-to-source on-state resistance	R <sub>DS(ON)</sub>	-	-	12	Ω	V <sub>GS</sub> = 0V, I <sub>D</sub> = 150 mA			
Change in $R_{DS(ON)}$ with temperature	$\Delta R_{DS(ON)}$	-	-	1.1	%/°C	V <sub>GS</sub> = 0V, I <sub>D</sub> = 150 mA( <b>Note 2</b> )			
AC Parameters (Note 2)									
Forward transconductance	G <sub>FS</sub>	300	-	-	mmho	V <sub>DS</sub> = 10V, I <sub>D</sub> = 150 mA			
Input capacitance	C <sub>ISS</sub>	-	-	300		V <sub>GS</sub> = -10V,			
Common source output capacitance	C <sub>OSS</sub>	-	-	30	pF	V <sub>DS</sub> = 25V,			
Reverse transfer capacitance	C <sub>RSS</sub>	-	-	5		f = 1 MHz			
Turn-on delay time	t <sub>d(ON)</sub>	-	-	10					
Rise time	t <sub>r</sub>	-	-	15	ns	V <sub>DD</sub> = 25V, I <sub>D</sub> = 150 mA,			
Turn-off delay time	t <sub>d(OFF)</sub>	-	-	15	115	$R_{GEN} = 25\Omega,$			
Fall time	t <sub>f</sub>	-	-	20	1				
Diode Parameters									
Diode forward voltage drop	$V_{SD}$	-	-	1.8	V	V <sub>GS</sub> = -10V, I <sub>SD</sub> = 150 mA (Note 1)			
Reverse recovery time	t <sub>rr</sub>	-	600	-	ns	V <sub>GS</sub> = -10V, I <sub>SD</sub> = 1.0A (Note 2)			

**Note 1:** All DC parameters are 100% tested at 25°C unless otherwise stated. Pulse test: 300 µs pulse, 2% duty cycle.

2: Specification is obtained by characterization and is not 100% tested.

#### **TEMPERATURE SPECIFICATIONS**

<b>Electrical Specifications:</b> Unless otherwise specified, for all specifications $T_A = T_J = +25^{\circ}C$									
Parameter	Symbol	mbol Min Typ Max Units		Units	Conditions				
Temperature Ranges									
Operating and Storage Temperature	T <sub>A</sub>	-55	_	150	°C				
Package Thermal Resistances									
Thermal Resistance, TO-92	θ <sub>ja</sub>	_	132	_	°C/W				
Thermal Resistance, TO-243AA	θ <sub>ja</sub>	_	133	-	°C/W				

## THERMAL CHARACTERISTICS

Package	I <sub>D</sub> (1) continuous (mA)	l <sub>D</sub> pulsed (mA)	Power Dissipation @T <sub>A</sub> = 25°C (W)	l <sub>DR</sub> (1) (mA)	I <sub>DRM</sub> (mA)
TO-92	175	500	0.74	175	500
TO-243AA (SOT-89)	200	500	1.6 ( <mark>2</mark> )	200	500

Note 1:  $I_D$  continuous is limited by max rated  $T_J$ 

2: Mounted on FR4 board, 25mm x 25mm x 1.57 mm

## 2.0 PIN DESCRIPTION

The locations of the pins are listed in Package Types and Packaging Information.

#### TABLE 2-1:PIN DESCRIPTION

Pin # TO-92	Pin # TO-243AA	Function		
2	1	GATE		
3	2, 4	DRAIN		
1	3	SOURCE		

<sup>© 2016</sup> Microchip Technology Inc.

## 3.0 FUNCTIONAL DESCRIPTION

Figure 3-1 shows the switching waveform and test circuit for DN2530. Figure 3-2 and Figure 3-3 provide typical performance curves.





FIGURE 3-1: Switching Waveforms and Test Circuit

#### **Product Summary**

BV <sub>DSX</sub> /BV <sub>DGX</sub>	R <sub>DS(ON)</sub>	I <sub>DSS</sub>
(V)	(max) (Ω)	(min) (mA)
300	12	200





© 2016 Microchip Technology Inc.





FIGURE 3-3: Typical Performance Curves (continued)

## 4.0 PACKAGING INFORMATION


#### 4.1 Package Marking Information



Leg	jend:	XXX Y YY WW NNN @3 *	Product Code or Customer-specific information Year code (last digit of calendar year) Year code (last 2 digits of calendar year) Week code (week of January 1 is week '01') Alphanumeric traceability code Pb-free JEDEC <sup>®</sup> designator for Matte Tin (Sn) This package is Pb-free. The Pb-free JEDEC designator ((e3)) can be found on the outer packaging for this package.
Not	b c	e carried haracters	nt the full Microchip part number cannot be marked on one line, it will d over to the next line, thus limiting the number of available for product code or customer-specific information. Package may or e the corporate logo.

<sup>© 2016</sup> Microchip Technology Inc.

# 3-Lead TO-243AA (SOT-89) Package Outline (N8)




Note: For the most current package drawings, see the Microchip Packaging Specification at www.microchip.com/packaging.

Symbo	ol	Α	b	b1	С	D	D1	E	E1	е	e1	н	L	
	MIN	1.40	0.44	0.36	0.35	4.40	1.62	2.29	2.00†	1.50 BSC		3.94	0.73†	
Dimensions (mm)	NOM	-	-	-	-	-	-	-	-				3.00 BSC	-
()	MAX	1.60	0.56	0.48	0.44	4.60	1.83	2.60	2.29			4.25	1.20	

JEDEC Registration TO-243, Variation AA, Issue C, July 1986. † This dimension differs from the JEDEC drawing Drawings not to scale.





**Bottom View** 

Note: For the most current package drawings, see the Microchip Packaging Specification at www.microchip.com/packaging.

Symb	lool	А	b	с	D	E	E1	e	e1	L
	MIN	.170	.014†	.014†	.175	.125	.080	.095	.045	.500
Dimensions (inches)	NOM	-	-	-	-	-	-	-	-	-
(1101100)	MAX	.210	.022†	.022†	.205	.165	.105	.105	.055	.610*

JEDEC Registration TO-92. \* This dimension is not specified in the JEDEC drawing. † This dimension differs from the JEDEC drawing.

Drawings not to scale.

# APPENDIX A: REVISION HISTORY

## **Revision A (January 2016)**

- Converted Supertex Doc #DSFP-DN2530 to Microchip DS20005451A.
- Removed 2000/Reel option for TO-92 package.

#### **PRODUCT IDENTIFICATION SYSTEM**

To order or obtain information, e.g., on pricing or delivery, refer to the factory or the listed sales office.

PART NO.	<u>xx</u> - <u>x</u> - <u>x</u>	Ex	amples:	
	ackage Environmental Media	a)	DN2530N3-G	TO-92 package, 1000/reel
	options Type	b)	DN2530N8-G	TO-243AA package, 2000/reel
Device:	DN2530 = N-Channel, Depletion-Mode, Vertical DMOS FET			
Package:	N3 = TO-92, 3-lead N8 = TO-243AA (SOT-89), 3-lead			
Environmental	G = Lead (Pb)-free/ROHS-compliant package			
Media Type:	(blank) = 1000/Reel for N3 packages = 2000/Reel for N8 packages			

<sup>© 2016</sup> Microchip Technology Inc.

#### Note the following details of the code protection feature on Microchip devices:

- · Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Microchip received ISO/TS-16949:2009 certification for its worldwide headquarters, design and wafer fabrication facilities in Chandler and Tempe, Arizona; Gresham, Oregon and design centers in California and India. The Company's quality system processes and procedures are for its PIC® MCUs and dsPIC® DSCs, KEELOQ® code hopping devices, Serial EEPROMs, microperipherals, nonvolatile memory and analog products. In addition, Microchip's quality system for the design and manufacture of development systems is ISO 9001:2000 certified.

# QUALITY MANAGEMENT SYSTEM CERTIFIED BY DNV = ISO/TS 16949=

#### Trademarks

The Microchip name and logo, the Microchip logo, AnyRate, dsPIC, FlashFlex, flexPWR, Heldo, JukeBlox, KeeLoq, KeeLoq logo, Kleer, LANCheck, LINK MD, MediaLB, MOST, MOST logo, MPLAB, OptoLyzer, PIC, PICSTART, PIC32 logo, RightTouch, SpyNIC, SST, SST Logo, SuperFlash and UNI/O are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

ClockWorks, The Embedded Control Solutions Company, ETHERSYNCH, Hyper Speed Control, HyperLight Load, IntelliMOS, mTouch, Precision Edge, and QUIET-WIRE are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, BodyCom, chipKIT, chipKIT logo, CodeGuard, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, EtherGREEN, In-Circuit Serial Programming, ICSP, Inter-Chip Connectivity, JitterBlocker, KleerNet, KleerNet logo, MiWi, motorBench, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PureSilicon, RightTouch logo, REAL ICE, Ripple Blocker, Serial Quad I/O, SQI, SuperSwitcher, SuperSwitcher II, Total Endurance, TSHARC, USBCheck, VariSense, ViewSpan, WiperLock, Wireless DNA, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

Silicon Storage Technology is a registered trademark of Microchip Technology Inc. in other countries.

GestIC is a registered trademarks of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2016, Microchip Technology Incorporated, Printed in the U.S.A., All Rights Reserved.

ISBN: 978-1-5224-0250-3



# **Worldwide Sales and Service**

#### AMERICAS

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: http://www.microchip.com/ support

Web Address: www.microchip.com

Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Austin, TX Tel: 512-257-3370

Boston Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

**Chicago** Itasca, IL Tel: 630-285-0071 Fax: 630-285-0075

**Cleveland** Independence, OH Tel: 216-447-0464 Fax: 216-447-0643

**Dallas** Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

**Detroit** Novi, MI Tel: 248-848-4000

Houston, TX Tel: 281-894-5983

Indianapolis Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608

New York, NY Tel: 631-435-6000

San Jose, CA Tel: 408-735-9110

**Canada - Toronto** Tel: 905-673-0699 Fax: 905-673-6509

#### ASIA/PACIFIC

Asia Pacific Office Suites 3707-14, 37th Floor Tower 6, The Gateway

Harbour City, Kowloon Hong Kong Tel: 852-2943-5100 Fax: 852-2401-3431

Australia - Sydney Tel: 61-2-9868-6733 Fax: 61-2-9868-6755

**China - Beijing** Tel: 86-10-8569-7000 Fax: 86-10-8528-2104

**China - Chengdu** Tel: 86-28-8665-5511 Fax: 86-28-8665-7889

China - Chongqing Tel: 86-23-8980-9588 Fax: 86-23-8980-9500

China - Dongguan Tel: 86-769-8702-9880

**China - Hangzhou** Tel: 86-571-8792-8115 Fax: 86-571-8792-8116

**China - Hong Kong SAR** Tel: 852-2943-5100 Fax: 852-2401-3431

**China - Nanjing** Tel: 86-25-8473-2460 Fax: 86-25-8473-2470

**China - Qingdao** Tel: 86-532-8502-7355 Fax: 86-532-8502-7205

**China - Shanghai** Tel: 86-21-5407-5533 Fax: 86-21-5407-5066

China - Shenyang Tel: 86-24-2334-2829 Fax: 86-24-2334-2393

**China - Shenzhen** Tel: 86-755-8864-2200 Fax: 86-755-8203-1760

**China - Wuhan** Tel: 86-27-5980-5300 Fax: 86-27-5980-5118

**China - Xian** Tel: 86-29-8833-7252 Fax: 86-29-8833-7256 ASIA/PACIFIC

**China - Xiamen** Tel: 86-592-2388138 Fax: 86-592-2388130

China - Zhuhai Tel: 86-756-3210040 Fax: 86-756-3210049

India - Bangalore Tel: 91-80-3090-4444 Fax: 91-80-3090-4123

India - New Delhi Tel: 91-11-4160-8631 Fax: 91-11-4160-8632

India - Pune Tel: 91-20-3019-1500

**Japan - Osaka** Tel: 81-6-6152-7160 Fax: 81-6-6152-9310

**Japan - Tokyo** Tel: 81-3-6880- 3770 Fax: 81-3-6880-3771

**Korea - Daegu** Tel: 82-53-744-4301 Fax: 82-53-744-4302

Korea - Seoul Tel: 82-2-554-7200 Fax: 82-2-558-5932 or 82-2-558-5934

Malaysia - Kuala Lumpur Tel: 60-3-6201-9857 Fax: 60-3-6201-9859

Malaysia - Penang Tel: 60-4-227-8870 Fax: 60-4-227-4068

Philippines - Manila Tel: 63-2-634-9065 Fax: 63-2-634-9069

**Singapore** Tel: 65-6334-8870 Fax: 65-6334-8850

**Taiwan - Hsin Chu** Tel: 886-3-5778-366 Fax: 886-3-5770-955

**Taiwan - Kaohsiung** Tel: 886-7-213-7828

Taiwan - Taipei Tel: 886-2-2508-8600 Fax: 886-2-2508-0102

Thailand - Bangkok Tel: 66-2-694-1351 Fax: 66-2-694-1350

#### EUROPE

Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393

Denmark - Copenhagen Tel: 45-4450-2828 Fax: 45-4485-2829

France - Paris Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79

Germany - Dusseldorf Tel: 49-2129-3766400

Germany - Karlsruhe Tel: 49-721-625370

**Germany - Munich** Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

**Italy - Milan** Tel: 39-0331-742611 Fax: 39-0331-466781

Italy - Venice Tel: 39-049-7625286

Netherlands - Drunen Tel: 31-416-690399 Fax: 31-416-690340

Poland - Warsaw Tel: 48-22-3325737

**Spain - Madrid** Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

Sweden - Stockholm Tel: 46-8-5090-4654

**UK - Wokingham** Tel: 44-118-921-5800 Fax: 44-118-921-5820

07/14/15