

# Small, Low Power, 3-Axis $\pm 2 g$ Accelerometer

# ADXL327

#### **FEATURES**

3-axis sensing Small, low profile package 4 mm × 4 mm × 1.45 mm LFCSP Low power: 350 μA typical Single-supply operation: 1.8 V to 3.6 V 10,000 g shock survival Excellent temperature stability Bandwidth adjustment with a single capacitor per axis RoHS/WEEE lead-free compliant

#### **APPLICATIONS**


Cost-sensitive, low power, motion- and tilt-sensing applications Mobile devices Gaming systems Disk drive protection Image stabilization Sports and health devices

#### **GENERAL DESCRIPTION**

The ADXL327 is a small, low power, complete 3-axis accelerometer with signal conditioned voltage outputs. The product measures acceleration with a minimum full-scale range of  $\pm 2$  g. It can measure the static acceleration of gravity in tilt-sensing applications, as well as dynamic acceleration, resulting from motion, shock, or vibration.

The user selects the bandwidth of the accelerometer using the  $C_X$ ,  $C_Y$ , and  $C_Z$  capacitors at the X<sub>OUT</sub>, Y<sub>OUT</sub>, and Z<sub>OUT</sub> pins. Bandwidths can be selected to suit the application with a range of 0.5 Hz to 1600 Hz for X and Y axes and a range of 0.5 Hz to 550 Hz for the Z axis.

The ADXL327 is available in a small, low profile, 4 mm  $\times$  4 mm  $\times$  1.45 mm, 16-lead, plastic lead frame chip scale package (LFCSP\_LQ).



### FUNCTIONAL BLOCK DIAGRAM

Rev. 0

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.

 One Technology Way, P.O. Box 9106, Norwood, MA 02062-9106, U.S.A.

 Tel: 781.329.4700
 www.analog.com

 Fax: 781.461.3113
 ©2009 Analog Devices, Inc. All rights reserved.

# ADXL327\* Product Page Quick Links

Last Content Update: 11/01/2016

### Comparable Parts

View a parametric search of comparable parts

### Evaluation Kits

• ADXL327 Breakout Board

### Documentation 🖵

### **Application Notes**

- AN-1057: Using an Accelerometer for Inclination Sensing
- AN-688: Phase and Frequency Response of iMEMS® Accelerometers and Gyros

#### Data Sheet

• ADXL327: Small, Low Power, 3-Axis ±2 g Accelerometer Data Sheet

### Design Resources 🖵

- ADXL327 Material Declaration
- PCN-PDN Information
- Quality And Reliability
- Symbols and Footprints

### Discussions 🖵

View all ADXL327 EngineerZone Discussions

### Sample and Buy

Visit the product page to see pricing options

### Technical Support

Submit a technical question or find your regional support number

\* This page was dynamically generated by Analog Devices, Inc. and inserted into this data sheet. Note: Dynamic changes to the content on this page does not constitute a change to the revision number of the product data sheet. This content may be frequently modified.

# TABLE OF CONTENTS

Features
Applications1
General Description
Functional Block Diagram 1
Revision History
Specifications
Absolute Maximum Ratings 4
ESD Caution 4
Pin Configuration and Function Descriptions
Typical Performance Characteristics
Theory of Operation10
Mechanical Sensor10

### **REVISION HISTORY**

8/09—Revision 0: Initial Version

Performance10
Applications Information1
Power Supply Decoupling1
Setting the Bandwidth Using $C_X$ , $C_Y$ , and $C_Z$ 1
Self Test 1
Design Trade-Offs for Selecting Filter Characteristics: The Noise/BW Trade-Off1
Use with Operating Voltages Other Than 3 V 1
Axes of Acceleration Sensitivity 12
Layout and Design Recommendations1
Outline Dimensions 14
Ordering Guide14

### **SPECIFICATIONS**

 $T_A = 25^{\circ}$ C,  $V_S = 3$  V,  $C_X = C_Y = C_Z = 0.1 \mu$ F, acceleration = 0 g, unless otherwise noted. All minimum and maximum specifications are guaranteed. Typical specifications are not guaranteed.

Parameter	Conditions	Min	Тур	Max	Unit
SENSOR INPUT	Each axis				
Measurement Range		±2	±2.5		g
Nonlinearity	Percent of full scale		±0.2		%
Package Alignment Error			±1		Degrees
Interaxis Alignment Error			±0.1		Degrees
Cross Axis Sensitivity <sup>1</sup>			±1		%
SENSITIVITY (RATIOMETRIC) <sup>2</sup>	Each axis				
Sensitivity at Xout, Yout, Zout	$V_S = 3 V$	378	420	462	mV/ <i>g</i>
Sensitivity Change Due to Temperature <sup>3</sup>	$V_S = 3 V$		±0.01		%/°C
ZERO g BIAS LEVEL (RATIOMETRIC)					
0 g Voltage at Х <sub>оит</sub> , Ү <sub>оит</sub>	$V_s = 3 V$	1.3	1.5	1.7	V
0 g Voltage at Zout	$V_S = 3 V$	1.2	1.5	1.8	V
0 g Offset vs. Temperature			±1		mg/°C
NOISE PERFORMANCE					
Noise Density Xout, Yout, Zout			250		µg/√Hz rms
FREQUENCY RESPONSE <sup>4</sup>					
Bandwidth Xout, Yout <sup>5</sup>	No external filter		1600		Hz
Bandwidth Zout <sup>5</sup>	No external filter		550		Hz
R <sub>FILT</sub> Tolerance			32 ± 15%		kΩ
Sensor Resonant Frequency			5.5		kHz
SELF TEST <sup>6</sup>					
Logic Input Low			+0.6		V
Logic Input High			+2.4		V
ST Actuation Current			+60		μA
Output Change at Xout	Self test 0 to 1	-210	-450	-850	mV
Output Change at Yout	Self test 0 to 1	+210	+450	+850	mV
Output Change at ZOUT	Self test 0 to 1	+210	+770	+1400	mV
OUTPUT AMPLIFIER					
Output Swing Low	No load		0.1		v
Output Swing High	No load		2.8		V
POWER SUPPLY					
Operating Voltage Range		1.8		3.6	V
Supply Current	$V_s = 3 V$		350		μΑ
Turn-On Time <sup>7</sup>	No external filter		1		ms
TEMPERATURE					
Operating Temperature Range		-40		+85	°C

<sup>1</sup> Defined as coupling between any two axes.

<sup>2</sup> Sensitivity is essentially ratiometric to V<sub>s</sub>.

<sup>3</sup> Defined as the output change from ambient-to-maximum temperature or ambient-to-minimum temperature.

<sup>4</sup> Actual frequency response controlled by user-supplied external filter capacitors (C<sub>x</sub>, C<sub>Y</sub>, C<sub>Z</sub>).

<sup>5</sup> Bandwidth with external capacitors =  $1/(2 \times \pi \times 32 \text{ k}\Omega \times \text{C})$ . For C<sub>x</sub>, C<sub>Y</sub> = 0.003  $\mu$ F, bandwidth = 1.6 kHz. For C<sub>z</sub> = 0.01  $\mu$ F, bandwidth = 500 Hz. For C<sub>x</sub>, C<sub>Y</sub>, C<sub>z</sub> = 10  $\mu$ F, bandwidth = 0.5 Hz.

 $^{\rm 6}$  Self test response changes cubically with Vs.

 $^7$  Turn-on time is dependent on C<sub>x</sub>, C<sub>Y</sub>, C<sub>z</sub> and is approximately 160 × C<sub>x</sub> or C<sub>Y</sub> or C<sub>z</sub> + 1 ms, where C<sub>x</sub>, C<sub>Y</sub>, C<sub>z</sub> are in  $\mu$ F.

### **ABSOLUTE MAXIMUM RATINGS**

#### Table 2.

Parameter	Rating
Acceleration (Any Axis, Unpowered)	10,000 g
Acceleration (Any Axis, Powered)	10,000 g
Vs	–0.3 V to +3.6 V
All Other Pins	$(COM - 0.3 V)$ to $(V_{s} + 0.3 V)$
Output Short-Circuit Duration (Any Pin to Common)	Indefinite
Temperature Range (Powered)	–55°C to +125°C
Temperature Range (Storage)	–65°C to +150°C


Stresses above those listed under Absolute Maximum Ratings may cause permanent damage to the device. This is a stress rating only; functional operation of the device at these or any other conditions above those indicated in the operational section of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

#### **ESD CAUTION**



**ESD** (electrostatic discharge) sensitive device. Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore, proper ESD precautions should be taken to avoid performance degradation or loss of functionality.


### **PIN CONFIGURATION AND FUNCTION DESCRIPTIONS**




Pin No.	Mnemonic	Description
1	NC	No Connect (or Optionally Ground)
2	ST	Self Test
3	СОМ	Common
4	NC	No Connect
5	СОМ	Common
6	СОМ	Common
7	СОМ	Common
8	Zout	Z Channel Output
9	NC	No Connect (or Optionally Ground)
10	Yout	Y Channel Output
11	NC	No Connect
12	Xout	X Channel Output
13	NC	No Connect
14	Vs	Supply Voltage (1.8 V to 3.6 V)
15	Vs	Supply Voltage (1.8 V to 3.6 V)
16	NC	No Connect
EP	Exposed pad	Not internally connected. Solder for mechanical integrity.

### **TYPICAL PERFORMANCE CHARACTERISTICS**

N > 1000 for all typical performance plots, unless otherwise noted.








Figure 12. X-Axis Zero g Bias vs. Temperature, Eight Parts Soldered to PCB




Figure 13. Y-Axis Zero g Bias vs. Temperature, Eight Parts Soldered to PCB





Figure 14. Z-Axis Zero g Bias vs. Temperature, Eight Parts Soldered to PCB









Figure 10. Y-Axis Zero g Bias Temperature Coefficient,  $V_S = 3 V$ 










Figure 22. Typical Turn-On Time,  $V_S = 3 V$  $C_X = C_Y = C_Z = 0.0047 \, \mu F$ 

### THEORY OF OPERATION

The ADXL327 is a complete 3-axis acceleration measurement system. The ADXL327 has a measurement range of  $\pm 2 g$  minimum. It contains a polysilicon surface micromachined sensor and signal conditioning circuitry to implement an open-loop acceleration measurement architecture. The output signals are analog voltages that are proportional to acceleration. The accelerometer can measure the static acceleration of gravity in tilt sensing applications, as well as dynamic acceleration, resulting from motion, shock, or vibration.

The sensor is a polysilicon surface micromachined structure built on top of a silicon wafer. Polysilicon springs suspend the structure over the surface of the wafer and provide a resistance against acceleration forces. Deflection of the structure is measured using a differential capacitor that consists of independent fixed plates and plates attached to the moving mass. The fixed plates are driven by 180° out-of-phase square waves. Acceleration deflects the moving mass and unbalances the differential capacitor resulting in a sensor output whose amplitude is proportional to acceleration. Phase-sensitive demodulation techniques are then used to determine the magnitude and direction of the acceleration.

The demodulator output is amplified and brought off-chip through a 32 k $\Omega$  resistor. The user then sets the signal bandwidth of the device by adding a capacitor. This filtering improves measurement resolution and helps prevent aliasing.

### **MECHANICAL SENSOR**

The ADXL327 uses a single structure for sensing the X, Y, and Z axes. As a result, the three axes sense directions are highly orthogonal with little cross-axis sensitivity. Mechanical misalignment of the sensor die to the package is the chief source of cross-axis sensitivity. Mechanical misalignment can, of course, be calibrated out at the system level.

#### PERFORMANCE

Rather than using additional temperature compensation circuitry, innovative design techniques ensure that high performance is built-in to the ADXL327. As a result, there is neither quantization error nor nonmonotonic behavior, and temperature hysteresis is very low (typically <3 mg over the  $-25^{\circ}$ C to  $+70^{\circ}$ C temperature range).

### APPLICATIONS INFORMATION POWER SUPPLY DECOUPLING

For most applications, a single 0.1  $\mu$ F capacitor, C<sub>DC</sub>, placed close to the ADXL327 supply pins adequately decouples the accelerometer from noise on the power supply. However, in applications where noise is present at the 50 kHz internal clock frequency (or any harmonic thereof), additional care in power supply bypassing is required because this noise can cause errors in acceleration measurement. If additional decoupling is needed, a 100  $\Omega$  (or smaller) resistor or ferrite bead can be inserted in the supply line. Additionally, a larger bulk bypass capacitor (1  $\mu$ F or greater) can be added in parallel to C<sub>DC</sub>. Ensure that the connection from the ADXL327 ground to the power supply ground is low impedance because noise transmitted through ground has a similar effect as noise transmitted through V<sub>s</sub>.

#### SETTING THE BANDWIDTH USING Cx, Cy, AND Cz

The ADXL327 has provisions for band limiting the  $X_{OUT}$ ,  $Y_{OUT}$ , and  $Z_{OUT}$  pins. Capacitors must be added at these pins to implement low-pass filtering for antialiasing and noise reduction. The 3 dB bandwidth equation is

 $f_{-3 \text{ dB}} = 1/(2\pi(32 \text{ k}\Omega) \times C_{(X, Y, Z)})$ 

or more simply

 $f_{-3 \text{ dB}} = 5 \ \mu F / C_{(X, Y, Z)}$ 

The tolerance of the internal resistor (R<sub>FILT</sub>) typically varies as much as  $\pm 15\%$  of its nominal value (32 k $\Omega$ ), and the bandwidth varies accordingly. A minimum capacitance of 0.0047  $\mu$ F for C<sub>x</sub>, C<sub>y</sub>, and C<sub>z</sub> is recommended in all cases.

Table 4.	Filter Ca	pacitor	Selection,	Cx.	Cy, and	d Cz
1 4010 11	I HILLI Ou	pacitor	oureenon,	<b>О</b> л,	01, 411	

Bandwidth (Hz)	Capacitor (μF)		
1	4.7		
10	0.47		
50	0.10		
100	0.05		
200	0.027		
500	0.01		

#### SELF TEST

The ST pin controls the self test feature. When this pin is set to V<sub>s</sub>, an electrostatic force is exerted on the accelerometer beam. The resulting movement of the beam allows the user to test whether the accelerometer is functional. The typical change in output is -1.08 g (corresponding to -450 mV) in the X axis, +1.08 g (+450 mV) on the Y axis, and +1.83 g (+770 mV) on the Z axis. This ST pin can be left open circuit or connected to common (COM) in normal use.

Never expose the ST pin to voltages greater than  $V_S + 0.3$  V. If this cannot be guaranteed due to the system design (for instance, there are multiple supply voltages), then a low  $V_F$  clamping diode between ST and  $V_S$  is recommended.

### DESIGN TRADE-OFFS FOR SELECTING FILTER CHARACTERISTICS: THE NOISE/BW TRADE-OFF

The selected accelerometer bandwidth ultimately determines the measurement resolution (smallest detectable acceleration). Filtering can be used to lower the noise floor to improve the resolution of the accelerometer. Resolution is dependent on the analog filter bandwidth at  $X_{OUT}$ ,  $Y_{OUT}$ , and  $Z_{OUT}$ .

The output of the ADXL327 has a typical bandwidth greater than 500 Hz. The user must filter the signal at this point to limit aliasing errors. The analog bandwidth must be no more than half the analog-to-digital sampling frequency to minimize aliasing. The analog bandwidth can be further decreased to reduce noise and improve resolution.

The ADXL327 noise has the characteristics of white Gaussian noise, which contributes equally at all frequencies and is described in terms of  $\mu g/\sqrt{Hz}$  (the noise is proportional to the square root of the accelerometer bandwidth). The user should limit bandwidth to the lowest frequency needed by the application to maximize the resolution and dynamic range of the accelerometer.

With the single-pole roll-off characteristic, the typical noise of the ADXL327 is determined by

*rms* Noise = Noise Density  $\times$  ( $\sqrt{BW \times 1.6}$ )

Often, the peak value of the noise is desired. Peak-to-peak noise can only be estimated by statistical methods. Table 5 is useful for estimating the probabilities of exceeding various peak values, given the rms value.

Peak-to-Peak Value	% of Time That Noise Exceeds Nominal Peak-to-Peak Value
$2 \times rms$	32
$4 \times rms$	4.6
б×rms	0.27
8 × rms	0.006

#### Table 5. Estimation of Peak-to-Peak Noise

#### USE WITH OPERATING VOLTAGES OTHER THAN 3 V

The ADXL327 is tested and specified at  $V_S = 3$  V; however, it can be powered with  $V_S$  as low as 1.8 V or as high as 3.6 V. Note that some performance parameters change as the supply voltage is varied.

The ADXL327 output is ratiometric; therefore, the output sensitivity (or scale factor) varies proportionally to the supply voltage. At  $V_s = 3.6$  V, the output sensitivity is typically 500 mV/g. At  $V_s = 2$  V, the output sensitivity is typically 289 mV/g.

The zero *g* bias output is also ratiometric; therefore, the zero *g* output is nominally equal to  $V_s/2$  at all supply voltages.

The output noise is not ratiometric but is absolute in volts; therefore, the noise density decreases as the supply voltage increases. This is because the scale factor (mV/g) increases while the noise voltage remains constant. At V<sub>s</sub> = 3.6 V, the X- and Y-axis noise density is typically 200  $\mu g/\sqrt{Hz}$ , while at V<sub>s</sub> = 2 V, the X- and Y-axis noise density is typically 300  $\mu g/\sqrt{Hz}$ .

Self test response in *g* is roughly proportional to the square of the supply voltage. However, when ratiometricity of sensitivity is factored in with supply voltage, the self test response in volts is roughly proportional to the cube of the supply voltage.

For example, at V<sub>S</sub> = 3.6 V, the self test response for the ADXL327 is approximately -780 mV for the X axis, +780 mV for the Y axis, and +1330 mV for the Z axis. At V<sub>S</sub> = 2 V, the self test response is approximately -130 mV for the X axis, +130 mV for the Y axis, and -220 mV for the Z axis.

The supply current decreases as the supply voltage decreases. Typical current consumption at  $V_s = 3.6$  V is 375  $\mu$ A, and typical current consumption at  $V_s = 2$  V is 300  $\mu$ A.

#### **AXES OF ACCELERATION SENSITIVITY**




Figure 23. Axes of Acceleration Sensitivity (Corresponding Output Voltage Increases When Accelerated Along the Sensitive Axis)




Figure 24. Output Response vs. Orientation to Gravity

#### LAYOUT AND DESIGN RECOMMENDATIONS

The recommended soldering profile is shown in Figure 25, followed by a description of the profile features in Table 6. The recommended PCB layout or solder land drawing is shown in Figure 26.




Figure 25. Recommended Soldering Profile

#### Table 6. Recommended Soldering Profile

Profile Feature	Sn63/Pb37	Pb-Free
Average Ramp Rate $(T_L \text{ to } T_P)$	3°C/sec maximum	3°C/sec maximum
Preheat		
Minimum Temperature (T <sub>SMIN</sub> )	100°C	150°C
Maximum Temperature (T <sub>SMAX</sub> )	150°C	200°C
Time (T <sub>SMIN</sub> to T <sub>SMAX</sub> ), ts	60 sec to 120 sec	60 sec to 180 sec
T <sub>SMAX</sub> to T <sub>L</sub>		
Ramp-Up Rate	3°C/sec maximum	3°C/sec maximum
Time Maintained Above Liquidous (TL)		
Liquidous Temperature (T <sub>L</sub> )	183°C	217°C
Time (t <sub>L</sub> )	60 sec to 150 sec	60 sec to 150 sec
Peak Temperature (T <sub>P</sub> )	240°C + 0°C/–5°C	260°C + 0°C/-5°C
Time Within 5°C of Actual Peak Temperature (t <sub>P</sub> )	10 sec to 30 sec	20 sec to 40 sec
Ramp-Down Rate	6°C/sec maximum	6°C/sec maximum
Time 25°C to Peak Temperature	6 minutes maximum	8 minutes maximum





Figure 26. Recommended PCB Layout

# **OUTLINE DIMENSIONS**



Dimensions shown in millimeters

#### **ORDERING GUIDE**

Model	Measurement Range	Specified Voltage	Temperature Range	Package Description	Package Option
ADXL327BCPZ <sup>1</sup>	±2 g	3 V	-40°C to +85°C	16-Lead LFCSP_LQ	CP-16-5a
ADXL327BCPZ-RL <sup>1</sup>	±2 g	3 V	-40°C to +85°C	16-Lead LFCSP_LQ	CP-16-5a
ADXL327BCPZ-RL7 <sup>1</sup>	±2 g	3 V	-40°C to +85°C	16-Lead LFCSP_LQ	CP-16-5a
EVAL-ADXL327Z <sup>1</sup>				<b>Evaluation Board</b>	

<sup>1</sup> Z = RoHS Compliant Part.

# NOTES

### NOTES

Analog Devices offers specific products designated for automotive applications; please consult your local Analog Devices sales representative for details. Standard products sold by Analog Devices are not designed, intended, or approved for use in life support, implantable medical devices, transportation, nuclear, safety, or other equipment where malfunction of the product can reasonably be expected to result in personal injury, death, severe property damage, or severe environmental harm. Buyer uses or sells standard products for use in the above critical applications at Buyer's own risk and Buyer agrees to defend, indemnify, and hold harmless Analog Devices from any and all damages, claims, suits, or expenses resulting from such unintended use.

©2009 Analog Devices, Inc. All rights reserved. Trademarks and registered trademarks are the property of their respective owners. D07949-0-8/09(0)



www.analog.com

Rev. 0 | Page 16 of 16