


STPS2H100

Datasheet

100 V, 2 A power Schottky rectifier



Features

- Negligible switching losses
- High junction temperature capability
- Low leakage current
- Good trade-off between leakage current and forward voltage drop
- Avalanche capability specified •
- ECOPACK2 component

- Switching diode
- Battery charger
- SMPS
- DC / DC converter
- Telecom power
- LED lighting

Description

This Schottky rectifier is designed for high frequency miniature switched mode power supplies such as adaptors and on board DC/DC converters.

Packaged in SMA, SMA Flat, SMB, SMB Flat and SMA Flat Notch, the STPS2H100 is ideal for use in lighting and telecom power applications.

Product status link				
STPS	STPS2H100			
Product summary				
Symbol Value				
I _{F(AV)}	2 A			
V _{RRM}	100 V			
T _j (max.) 175 °C				
V _F (max.)	0.65 V			

Applications

- •
- •

DS1452 - Rev 10 - October 2019 Downloaded from Arrow.com. lectronics sales office

1 Characteristics

57

Table 1. Absolute ratings (limiting values at 25 °C, unless otherwise specified	Table 1. Absolute ratings (limiting va	alues at 25 °C, unless	otherwise specified)
---	--	------------------------	----------------------

Symbol		Parameter				
V _{RRM}	Repetitive peak reverse volta	100	V			
		SMA	T _I = 130 °C, δ = 0.5			
	(AV) Average forward current	SMB	T _I = 135 °C, δ = 0.5	2	А	
I _{F(AV)}		SMA Flat, SMA Flat Notch	T _I = 145 °C, δ = 0.5	2		
		SMB Flat $T_I = 150 ^{\circ}\text{C}, \delta$				
I _{FSM}	Surge non repetitive forward	current	t _p = 10 ms sinusoidal	75	Α	
P _{ARM}	Repetitive peak avalanche power $t_p = 10 \ \mu s, T_j = 125 \ ^{\circ}C$			173	W	
T _{stg}	Storage temperature range			-65 to +175	°C	
Tj	Maximum operating junction temperature ⁽¹⁾			175	°C	

1. $(dP_{tot'}/dT_j) < (1/R_{th(j-a)})$ condition to avoid thermal runaway for a diode on its own heatsink.

Table 2. Thermal resistance parameters

Symbol		Parameter		
R	SMA	30		
	SMA Flat, SMA Flat Notch		20	°C/W
r∿th(j-l)	R _{th(j-l)} Junction to lead SMB SMB Flat	SMB	25	C/VV
		SMB Flat	15	

For more information, please refer to the following application note :

AN5088 : Rectifiers thermal management, handling and mounting recommendations

Table 3. Static electrical characteristics

Symbol	Parameter	Test conditions		Min.	Тур.	Max.	Unit
I_(1)	I _R ⁽¹⁾ Reverse leakage current	T _j = 25 °C	V _R = V _{RRM}	-		1.00	μA
IR. 7		T _j = 125 °C	VR - VRRM	-	0.40	1.00	mA
		T _j = 25 °C	I _F = 2 A	-		0.79	
V _F ⁽²⁾	Forward voltage drap	T _j = 125 °C		-	0.60	0.65	V
VF ⁽⁻⁾	Forward voltage drop	T _j = 25 °C	1 - 1 0	-		0.88	v
		T _j = 125 °C	I _F = 4 A	-	0.69	0.74	

1. Pulse test: $t_p = 5 ms$, $\delta < 2\%$

2. Pulse test: $t_p = 380 \ \mu s, \ \delta < 2\%$

To evaluate the conduction losses, use the following equation:

 $P = 0.56 \text{ x } I_{F(AV)} + 0.045 \text{ x } I_{F}^{2}(RMS)$



For more information, please refer to the following application notes related to the power losses :

- AN604: Calculation of conduction losses in a power rectifier
- AN4021: Calculation of reverse losses on a power diode

1.1 **Characteristics (curves)**







Figure 3. Average forward current versus ambient temperature (δ = 0.5, SMB Flat)
















Figure 10. Reverse leakage current versus reverse voltage applied (typical values)



DS1452 - Rev 10 Downloaded from Arrow.com.

57/









Figure 14. Thermal resistance junction to ambient versus copper surface under each lead (SMA)







Figure 16. Thermal resistance junction to ambient versus copper surface under each lead (SMB)






Figure 17. Thermal resistance junction to ambient versus copper surface under each lead (SMB Flat)

2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

2.1 SMA Flat package information

- Epoxy meets UL94, V0
- Lead-free package

Figure 18. SMA Flat package outline





Table 4. SMA Flat package mechanical data

	Dimensions						
Ref.	Millimeters			Inc	ly)		
	Min.	Тур.	Max.	Min.	Тур.	Max.	
А	0.90		1.10	0.035		0.044	
b	1.25		1.65	0.049		0.065	
с	0.15		0.40	0.005		0.016	
D	2.25		2.95	0.088		0.117	
Е	4.80		5.60	0.188		0.221	
E1	3.95		4.60	0.155		0.182	
L	0.75		1.50	0.029		0.060	
L1		0.50			0.020		
L2		0.50			0.020		

DS14	52 - Rev 10
Downloaded from	Arrow.com.








SMA Flat Notch package information 2.2


Epoxy meets UL94, V0 •

57

- Cooling method: by conduction (C)
- Band indicates cathode

Figure 20. SMA Flat Notch package outline






2 2

Table 5. SMA Flat Notch package mechanical data

	Dimensions							
Ref.		Millimeters		Inches (for reference only)				
	Min.	Тур.	Max.	Min.	Тур.	Max.		
A1	0.90		1.10	0.035		0.044		
A1		0.05			0.002			
b	1.25		1.65	0.049		0.065		
С	0.15		0.40	0.005		0.016		
D	2.25		2.90	0.088		0.115		
E	5.00		5.35	0.196		0.211		
E1	3.95		4.60	0.155		0.182		
G		2.00			0.079			
G1		0.85			0.033			
L	0.75		1.20	0.029				
L1		0.45			0.018			
L2		0.45			0.018			
L3		0.05			0.002			
V			8°			8°		
V1			8°			8°		






2.3 SMA package information

- Epoxy meets UL94, V0
- Lead-free package









Table 6. SMA package mechanical data

	Dimensions					
Ref.	Millir	neters	Incl	hes		
	Min.	Max.	Min.	Max.		
A1	1.90	2.45	0.075	0.097		
A2	0.05	0.20	0.002	0.008		
b	1.25	1.65	0.049	0.065		
С	0.15	0.40	0.006	0.016		
D	2.25	2.90	0.089	0.114		
E	4.80	5.35	0.189	0.211		
E1	3.95	4.60	0.156	0.181		
L	0.75	1.50	0.030	0.059		

DS145	52 - Rev 10
Downloaded from	Arrow.com.


Figure 23. SMA recommended footprint in mm (inches)




2.4 SMB package information

- Epoxy meets UL94, V0
- Lead-free package

Figure 24. SMB package outline









Table 7. SMB package mechanical data

	Dimensions					
Ref.	Millir	neters	Inches (for re	ference only)		
	Min.	Max.	Min.	Max.		
A1	1.90	2.45	0.0748	0.0965		
A2	0.05	0.20	0.0020	0.0079		
b	1.95	2.20	0.0768	0.0867		
С	0.15	0.40	0.0059	0.0157		
D	3.30	3.95	0.1299	0.1556		
E	5.10	5.60	0.2008	0.2205		
E1	4.05	4.60	0.1594	0.1811		
L	0.75	1.50	0.0295	0.0591		



2.5 SMB Flat package information

- Epoxy meets UL94, V0
- Lead-free package

57

Figure 26. SMB Flat package outline




Table 8. SMB Flat mechanical data

Ref.	Millimeters			Inches (for reference only)			
	Min.	Тур.	Max.	Min.	Тур.	Max.	
А	0.90	ĺ	1.10	0.035		0.043	
b	1.95		2.20	0.077		0.087	
С	0.15		0.40	0.006		0.016	
D	3.30		3.95	0.130		0.156	
E	5.10		5.60	0.201		0.220	
E1	4.05		4.60	0.159		0.181	
L	0.75		1.50	0.030		0.059	
L1		0.40			0.016		
L2		0.60			0.024		




Figure 27. Footprint recommendations, dimensions in mm (inches)

3 Ordering Information

57

Order code	Marking	Package	Weight	Base qty.	Delivery mode
STPS2H100A	S21	SMA	0.068 g	5000	Tape and reel
STPS2H100AF	F21	SMA Flat	0.035 g	10 000	Tape and reel
STPS2H100AFN	A21	SMA Flat Notch	0.039 g	10 000	Tape and reel
STPS2H100U	G21	SMB	0.107 g	2500	Tape and reel
STPS2H100UF	FG21	SMB Flat	0.050 g	5000	Tape and reel

Table 9. Ordering information

Revision history

Table 1	0. Document	revision	history
---------	-------------	----------	---------

Date	Version	Changes	
Jul-2003	4A	Last update.	
Aug-2004	5	SMA package dimensions update. Reference A1 max. changed from 2.70 (0.106 inches) to 2.03 mm (0.080 inches).	
08-Feb-2007	6	Reformatted to current standards. Added ECOPACK statement. Added SMBflat package.	
15-Feb-2010	7	Updated weight for SMBflat in Table 9.	
24-Jun-2013	8	Added SMAflat package	
17-May-2018	9	Removed figure 6. Updated Table 1. Absolute ratings (limiting values at 25 °C, unless otherw specified) and Section Description. Minor text changes to improve readability.	
08-Oct-2019	10	Added Section 2.2 SMA Flat Notch package information.	



IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2019 STMicroelectronics – All rights reserved