

STB3N62K3, STD3N62K3, STF3N62K3 STP3N62K3, STU3N62K3

N-channel 620 V, 2.2 Ω , 2.7 A SuperMESH3TM Power MOSFET D²PAK, DPAK, TO-220FP, TO-220, IPAK

Features

Туре	V _{DSS}	R _{DS(on)} max	I _D	P _D
STB3N62K3	620 V	< 2.5 Ω	2.7 A	45 W
STD3N62K3	620 V	< 2.5 Ω	2.7 A	45 W
STF3N62K3	620 V	< 2.5 Ω	2.7 A ⁽¹⁾	20 W
STP3N62K3	620 V	< 2.5 Ω	2.7 A	45 W
STU3N62K3	620 V	< 2.5 Ω	2.7 A	45 W

- 1. Limited by package
- 100% avalanche tested
- Extremely high dv/dt capability
- Very low intrinsic capacitances
- Improved diode reverse recovery characteristics
- Zener-protected

Application

■ Switching applications

Description

The new SuperMESH3™ series is obtained through the combination of a further fine tuning of ST's well established strip-based PowerMESH™ layout with a new optimization of the vertical structure. In addition to reducing on-resistance significantly versus previous generation, special attention has been taken to ensure a very good dv/dt capability and higher margin in breakdown voltage for the most demanding application.

Table 1. Device summary





Figure 1. Internal schematic diagram



Order codes	Marking	Package	Packaging
STB3N62K3	3N62K3	D²PAK	Tape and reel
STD3N62K3	3N62K3	DPAK	Tape and reel
STF3N62K3	3N62K3	TO-220FP	Tube
STP3N62K3	3N62K3	TO-220	Tube
STU3N62K3	3N62K3	IPAK	Tube

August 2009 Doc ID 14894 Rev 2 1/20

Contents

1	Electrical ratings 3
2	Electrical characteristics 5
	2.1 Electrical characteristics (curves)
3	Test circuits
4	Package mechanical data
5	Package mechanical data
6	Revision history

1 Electrical ratings

Table 2. Absolute maximum ratings

			Value		
Symbol	Parameter	TO-220 D ² PAK	DPAK IPAK	TO-220FP	Unit
V _{DS}	Drain-source voltage (V _{GS} = 0)		620		V
V _{GS}	Gate- source voltage		± 30		V
I _D	Drain current (continuous) at T _C = 25 °C	2.7	7	2.7 ⁽¹⁾	Α
I _D	Drain current (continuous) at T _C = 100 °C	1.7		1.7 ⁽¹⁾	Α
I _{DM} ⁽²⁾	Drain current (pulsed) 10.8		10.8 ⁽¹⁾	Α	
P _{TOT}	Total dissipation at T _C = 25 °C	45		20	W
	Derating factor	0.3	0.36 0.16		W/°C
V _{ESD(G-S)}	Gate source ESD (HBM-C = 100 pF, R = 1.5 k Ω)		2500		V
dv/dt (3)	Peak diode recovery voltage slope		9		V/ns
V _{ISO}	sulation withstand voltage (RMS) from all ree leads to external heat sink 1 s; Tc = 25 °C)		2500	V	
T _{stg}	Storage temperature		-55 to 15	0	°C
T _j	Max. operating junction temperature	150			°C

^{1.} Limited by package

Table 3. Thermal data

Symbol	Parameter	TO-220	D ² PAK	DPAK	IPAK	TO-220FP	Unit
R _{thj-case}	Thermal resistance junction-case max	2.78			6.25	°C/W	
R _{thj-pcb}	Thermal resistance junction-pcb max		50	50 -			°C/W
R _{thj-amb}	Thermal resistance junction-amb max	62.5 100		00	62.5	°C/W	
T _I	Maximum lead temperature for soldering purpose			300			Ô

^{2.} Pulse width limited by safe operating area

^{3.} $I_{SD} \leq 2.7 \text{ A}, \text{ di/dt } \leq 200 \text{ A/}\mu\text{s}, V_{DD} = 80\% V_{(BR)DSS}$

Table 4. Avalanche characteristics

Symbol	Parameter	Max value	Unit
I _{AR}	Avalanche current, repetitive or not-repetitive (pulse width limited by T_j max)	2.7	Α
E _{AS}	Single pulse avalanche energy (starting $T_j = 25$ °C, $I_D = I_{AR}$, $V_{DD} = 50$ V)	100	mJ

2 Electrical characteristics

(T_C = 25 °C unless otherwise specified)

Table 5. On /off states

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
V _{(BR)DSS}	Drain-source breakdown voltage	$I_D = 1 \text{ mA}, V_{GS} = 0$	620			V
I _{DSS}		V_{DS} = Max rating V_{DS} = Max rating, T_{C} =125 °C			1 50	μ Α μ Α
I _{GSS}	Gate-body leakage current (V _{DS} = 0)	V _{GS} = ± 20 V			± 10	μА
V _{GS(th)}	Gate threshold voltage	$V_{DS} = V_{GS}$, $I_D = 50 \mu A$	3	3.75	4.5	V
R _{DS(on}	Static drain-source on resistance	$V_{GS} = 10 \text{ V}, I_D = 1.4 \text{ A}$		2.2	2.5	Ω

Table 6. Dynamic

	,					
Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
g _{fs} (1)	Forward transconductance	V _{DS} = 15 V, I _D = 1.4 A	-	2.1	-	S
C _{iss} C _{oss} C _{rss}	Input capacitance Output capacitance Reverse transfer capacitance	$V_{DS} = 25 \text{ V, f} = 1 \text{ MHz, V}_{GS} = 0$	-	385 55 6	-	pF pF pF
C _{OSS eq} ⁽¹⁾	Equivalent output capacitance	$V_{GS} = 0$, $V_{DS} = 0$ to 496 V	1	32.3	-	pF
R _G	Intrinsic gate resistance	f = 1 MHz open drain	-	10	-	Ω
Q _g Q _{gs} Q _{gd}	Total gate charge Gate-source charge Gate-drain charge	V_{DD} = 496 V, I_D = 2.7 A, V_{GS} = 10 V (see <i>Figure 17</i>)	-	13 2.5 7.5	-	nC nC nC

^{1.} $C_{oss\ eq}$ is defined as a constant equivalent capacitance giving the same charging time as C_{oss} when V_DS increases from 0 to 80% V_{DSS}

Table 7. Switching times

Symbol	Parameter	Test conditions	Min.	Тур.	Max	Unit
t _{d(on)} t _r t _{d(off)} t _f	Turn-on delay time Rise time Turn-off-delay time Fall time	$V_{DD} = 310 \text{ V}, I_{D} = 1.7 \text{ A},$ $R_{G} = 4.7 \Omega, V_{GS} = 10 \text{ V}$ (see <i>Figure 16</i>)	-	9 6.8 22 15.6	-	ns ns ns ns



Table 8. Source drain diode

Symbol	Parameter	Test conditions	Min.	Тур.	Max.	Unit
I _{SD}	Source-drain current Source-drain current (pulsed)		-		2.7 10.8	A A
V _{SD} (2)	Forward on voltage	$I_{SD} = 2.7 \text{ A}, V_{GS} = 0$	-		1.6	V
t _{rr} Q _{rr} I _{RRM}	Reverse recovery time Reverse recovery charge Reverse recovery current	I _{SD} = 2.7 A, di/dt = 100 A/μs V _{DD} = 60 V (see <i>Figure 21</i>)	-	190 825 9		ns nC A
t _{rr} Q _{rr} I _{RRM}	Reverse recovery time Reverse recovery charge Reverse recovery current	I_{SD} = 2.7 A, di/dt = 100 A/µs V_{DD} = 60 V, T_j = 150 °C (see <i>Figure 21</i>)	-	255 1100 10		ns nC A

^{1.} Pulse width limited by safe operating area

Table 9. Gate-source Zener diode

Symbol	Parameter	Test conditions	Min	Тур	Max	Unit
BV _{GSO} ⁽¹⁾	Gate-source breakdown voltage	Igs=± 1 mA (open drain)	30			٧


The built-in back-to-back Zener diodes have specifically been designed to enhance not only the device's ESD capability, but also to make them safely absorb possible voltage transients that may occasionally be applied from gate to source. In this respect the Zener voltage is appropriate to achieve an efficient and cost-effective intervention to protect the device's integrity. These integrated Zener diodes thus avoid the usage of external components

^{2.} Pulsed: Pulse duration = 300 μ s, duty cycle 1.5%

2.1 Electrical characteristics (curves)

Figure 2. Safe operating area for TO-220, IPAK, DPAK, D²PAK

Figure 3. Thermal impedance for TO-220, IPAK, DPAK, D²PAK







Figure 4. Safe operating area for TO-220FP

Figure 5. Thermal impedance for TO-220FP








Figure 6. Output characteristics

Figure 7. Transfer characteristics





577

Doc ID 14894 Rev 2

7/20

Figure 8. Normalized BV_{DSS} vs temperature Figure 9. Static drain-source on resistance




Figure 10. Gate charge vs gate-source voltage Figure 11. Capacitance variations






Figure 12. Normalized gate threshold voltage Figure 13. Normalized on resistance vs vs temperature temperature




8/20 Doc ID 14894 Rev 2

Figure 14. Source-drain diode forward characteristics

Figure 15. Maximum avalanche energy vs temperature





5/

3 Test circuits

Figure 16. Switching times test circuit for resistive load

Figure 17. Gate charge test circuit




Figure 18. Test circuit for inductive load switching and diode recovery times

Figure 19. Unclamped Inductive load test circuit





Figure 20. Unclamped inductive waveform

Figure 21. Switching time waveform



10/20 Doc ID 14894 Rev 2


4 Package mechanical data

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK[®] packages, depending on their level of environmental compliance. ECOPACK[®] specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.



TO-220 mechanical data


Dim		mm			inch	
Dim	Min	Тур	Max	Min	Тур	Max
А	4.40		4.60	0.173		0.181
b	0.61		0.88	0.024		0.034
b1	1.14		1.70	0.044		0.066
С	0.48		0.70	0.019		0.027
D	15.25		15.75	0.6		0.62
D1		1.27			0.050	
E	10		10.40	0.393		0.409
е	2.40		2.70	0.094		0.106
e1	4.95		5.15	0.194		0.202
F	1.23		1.32	0.048		0.051
H1	6.20		6.60	0.244		0.256
J1	2.40		2.72	0.094		0.107
L	13		14	0.511		0.551
L1	3.50		3.93	0.137		0.154
L20		16.40			0.645	
L30		28.90			1.137	
Ø₽	3.75		3.85	0.147		0.151
Q	2.65		2.95	0.104		0.116






TO-220FP mechanical d	data	
-----------------------	------	--

Dim	Dim. mm.			inch		
Dilli.	Min.	Тур	Max.	Min.	Тур.	Max.
Α	4.40		4.60	0.173		0.181
В	2.5		2.7	0.098		0.106
D	2.5		2.75	0.098		0.108
E	0.45		0.70	0.017		0.027
F	0.75		1.00	0.030		0.039
F1	1.15		1.50	0.045		0.067
F2	1.15		1.50	0.045		0.067
G	4.95		5.20	0.195		0.204
G1	2.40		2.70	0.094		0.106
Н	10		10.40	0.393		0.409
L2		16			0.630	
L3	28.6		30.6	1.126		1.204
L4	9.80		10.60	0.385		0.417
L5	2.9		3.6	0.114		0.141
L6	15.90		16.40	0.626		0.645
L7	9		9.30	0.354		0.366
Dia	3		3.2	0.118		0.126




TO-251 (IPAK) mechanical data

DIM	mm.			
DIM.	min.	typ	max.	
Α	2.20		2.40	
A1	0.90		1.10	
b	0.64		0.90	
b2			0.95	
b4	5.20		5.40	
С	0.45		0.60	
c2	0.48		0.60	
D	6.00		6.20	
E	6.40		6.60	
е		2.28		
e1	4.40		4.60	
Н		16.10		
L	9.00		9.40	
(L1)	0.80		1.20	
L2		0.80		
V1		10 °		




TO-252 ((DPAK)	mechanical	data
----------	--------	------------	------

DIM.	mm.				
DIWI.	min.	typ	max.		
Α	2.20		2.40		
A1	0.90		1.10		
A2	0.03		0.23		
b	0.64		0.90		
b4	5.20		5.40		
С	0.45		0.60		
c2	0.48		0.60		
D	6.00		6.20		
D1		5.10			
E	6.40		6.60		
E1		4.70			
е		2.28			
e1	4.40		4.60		
Н	9.35		10.10		
L	1				
L1		2.80			
L2		0.80			
L4	0.60		1		
R		0.20			
V2	0 °		8 °		



D²PAK (TO-263) mechanical data


Dim		mm			inch		
Dim	Min	Тур	Max	Min	Тур	Max	
Α	4.40		4.60	0.173		0.181	
A1	0.03		0.23	0.001		0.009	
b	0.70		0.93	0.027		0.037	
b2	1.14		1.70	0.045		0.067	
С	0.45		0.60	0.017		0.024	
c2	1.23		1.36	0.048		0.053	
D	8.95		9.35	0.352		0.368	
D1	7.50			0.295			
Е	10		10.40	0.394		0.409	
E1	8.50			0.334			
е		2.54			0.1		
e1	4.88		5.28	0.192		0.208	
Н	15		15.85	0.590		0.624	
J1	2.49		2.69	0.099		0.106	
L	2.29		2.79	0.090		0.110	
L1	1.27		1.40	0.05		0.055	
L2	1.30		1.75	0.051		0.069	
R		0.4			0.016		
V2	0°		8°	0°		8°	




16/20 Doc ID 14894 Rev 2

5 Package mechanical data


DPAK FOOTPRINT




TAPE AND REEL SHIPMENT



D²PAK FOOTPRINT



TAPE AND REEL SHIPMENT



^{*} on sales type

6 Revision history

Table 10. Document revision history

Date	Revision	Changes	
10-Jul-2008	1	First release	
17-Aug-2009	2	Modified: marking of the <i>Table 1</i>	

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZED ST REPRESENTATIVE, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2009 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Philippines - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com

20/20 Doc ID 14894 Rev 2

